


1.5 A DARLINGTON SWITCHES



Dwg. No. A-9765A

ABSOLUTE MAXIMUM RATINGS at +25°C Free-Air Temperature for Any One Driver (unless otherwise noted)

Output Voltage, V_{CEX}	See Guide
Output Sustaining Voltage, $V_{CE(SUS)}$	See Guide
Output Current, I_{OUT} (Note 1)	1.75 A
Input Voltage, V_{IN}	See Guide
Input Current, I_B (Note 2)	25 mA
Supply Voltage, V_S (ULN2068B/LB & 2069B/LB) ...	10 V
Total Package Power Dissipation, P_D	See Graph
Operating Temperature Range, T_A	-20°C to +85°C
Storage Temperature Range, T_S	-55°C to -150°C

1. Allowable combinations of output current, number of outputs conducting, and duty cycle are shown on the following pages.
2. Input current may be limited by maximum allowable input voltage.

High-voltage, high-current Darlington arrays ULN2064B/LB through ULN2069B/LB are designed for interface between low-level logic and a variety of peripheral loads such as relays, solenoids, dc and stepper motors, magnetic print hammers, multiplexed LED and incandescent displays, heaters, and similar loads. Output OFF voltage ratings of 50 V and 80 V are available. These quad drivers can drive resistive loads to 480 watts (1.5 A x 80 V, 26% duty cycle). For inductive loads, sustaining voltages of 35 V and 50 V at 100 mA are specified.

Quad drivers ULN2064B, ULN2064LB, ULN2065B, ULN2065LB, ULN2068B, ULN2068LB, ULN2069B, and ULN2069LB are intended for use with TTL, low-speed TTL, and 5 V MOS logic. The ULN2065B/LB and ULN2069B/LB are selected for the 80 V minimum output breakdown specification. The ULN2068B/LB and ULN2069B/LB have pre-driver stages and are recommended for applications requiring high gain (low input-current loading). Quad-driver arrays are supplied with heat-sink contact tabs in 16-pin plastic DIPs (suffix 'B') and 20-lead surface-mountable wide-body SOICs (suffix 'LB').


FEATURES

- TTL, DTL, MOS, CMOS Compatible Inputs
- Transient-Protected Outputs
- Loads to 480 Watts
- Heat-Sink Contact Tabs
- Automotive Capable

Always order by complete part number, e.g., **ULN2064B**.

2064 THRU 2069 1.5 A DARLINGTON SWITCHES

SELECTION GUIDE



Dwg. GP-049-3

Part Number*	Max. V_{CEX}	Min. $V_{CE(SUS)}$	Max. V_{IN}	Application
ULN2064B ULN2064LB	50 V	35 V	15 V	TTL, DTL, Schottky TTL, and 5 V CMOS
ULN2065B ULN2065LB	80 V	50 V	15 V	
ULN2068B ULN2068LB	50 V	35 V	15 V	TTL, DTL, Schottky TTL, and 5 V CMOS
ULN2069B ULN2069LB	80 V	50 V	15 V	

* Suffix 'B' is a 16-pin DIP; 'LB' is a 20-lead SOIC.

TEST FIGURES




FIGURE 1




FIGURE 2




FIGURE 3




FIGURE 4




FIGURE 5




FIGURE 6




FIGURE 7





FIGURE 8

2064 THRU 2069


1.5 A DARLINGTON

SWITCHES


PARTIAL SCHEMATIC



Dwg. No. A-10,353C



Dwg. No. A-9765A






Dwg. No. A-14,326

ELECTRICAL CHARACTERISTICS at +25°C (unless otherwise noted).

Characteristic	Symbol	Test Fig.	Applicable Devices	Test Conditions	Limits		
					Min.	Max.	Units
Output Leakage Current	I_{CEX}	1	ULN2064B/LB	$V_{CE} = 50 \text{ V}$	—	100	μA
				$V_{CE} = 50 \text{ V}, T_A = 70^\circ\text{C}$	—	500	μA
			ULN2065B/LB	$V_{CE} = 80 \text{ V}$	—	100	μA
				$V_{CE} = 80 \text{ V}, T_A = 70^\circ\text{C}$	—	500	μA
Output Sustaining Voltage	$V_{CE(SUS)}$	2	ULN2064B/LB	$I_C = 100 \text{ mA}, V_{IN} = 0.4 \text{ V}$	35	—	V
			ULN2065B/LB	$I_C = 100 \text{ mA}, V_{IN} = 0.4 \text{ V}$	50	—	V
Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$	3	All	$I_C = 500 \text{ mA}, I_B = 625 \mu\text{A}$	—	1.1	V
				$I_C = 750 \text{ mA}, I_B = 935 \mu\text{A}$	—	1.2	V
				$I_C = 1.0 \text{ A}, I_B = 1.25 \text{ mA}$	—	1.3	V
				$I_C = 1.25 \text{ A}, I_B = 2.0 \text{ mA}$	—	1.4	V
			ULN2065B/LB	$I_C = 1.5 \text{ A}, I_B = 2.25 \text{ mA}$	—	1.5	V
Input Current	$I_{IN(ON)}$	4	All	$V_{IN} = 2.4 \text{ V}$	1.4	4.3	mA
				$V_{IN} = 3.75 \text{ V}$	3.3	9.6	mA
Input Voltage	$V_{IN(ON)}$	5	All	$V_{CE} = 2.0 \text{ V}, I_C = 1.0 \text{ A}$	—	2.0	V
			ULN2064B/LB	$V_{CE} = 2.0 \text{ V}, I_C = 1.25 \text{ A}$	—	2.5	V
			ULN2065B/LB	$V_{CE} = 2.0 \text{ V}, I_C = 1.5 \text{ A}$	—	2.5	V
Turn-On Delay	t_{PLH}	—	All	$0.5 E_{in} \text{ to } 0.5 E_{out}$	—	1.0	μs
Turn-Off Delay	t_{PHL}	—	All	$0.5 E_{in} \text{ to } 0.5 E_{out}$	—	1.5	μs
Clamp Diode Leakage Current	I_R	6	ULN2064B/LB	$V_R = 50 \text{ V}$	—	50	μA
				$V_R = 50 \text{ V}, T_A = 70^\circ\text{C}$	—	100	μA
			ULN2065B/LB	$V_R = 80 \text{ V}$	—	50	μA
				$V_R = 80 \text{ V}, T_A = 70^\circ\text{C}$	—	100	μA
Clamp Diode Forward Voltage	V_F	7	All	$I_F = 1.0 \text{ A}$	—	1.75	V
				$I_F = 1.5 \text{ A}$	—	2.0	V

2064 THRU 2069 1.5 A DARLINGTON SWITCHES

PARTIAL SCHEMATIC



ELECTRICAL CHARACTERISTICS at +25°C, $V_S = 5.0$ V (unless otherwise noted).





Characteristic	Symbol	Test Fig.	Applicable Devices	Test Conditions	Limits		
					Min.	Max.	Units
Output Leakage Current	I_{CEX}	1	ULN2068B/LB	$V_{CE} = 50$ V	—	100	μ A
				$V_{CE} = 50$ V, $T_A = 70^\circ\text{C}$	—	500	μ A
			ULN2069B/LB	$V_{CE} = 80$ V	—	100	μ A
				$V_{CE} = 80$ V, $T_A = 70^\circ\text{C}$	—	500	μ A
Output Sustaining Voltage	$V_{CE(SUS)}$	2	ULN2068B/LB	$I_C = 100$ mA, $V_{IN} = 0.4$ V	35	—	V
			ULN2069B/LB	$I_C = 100$ mA, $V_{IN} = 0.4$ V	50	—	V
Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$	3	All	$I_C = 500$ mA, $V_{IN} = 2.75$ V	—	1.1	V
				$I_C = 750$ mA, $V_{IN} = 2.75$ V	—	1.2	V
				$I_C = 1.0$ A, $V_{IN} = 2.75$ V	—	1.3	V
				$I_C = 1.25$ A, $V_{IN} = 2.75$ V	—	1.4	V
			ULN2069B/LB	$I_C = 1.5$ A, $V_{IN} = 2.75$ V	—	1.5	V
Input Current	$I_{IN(ON)}$	4	All	$V_{IN} = 2.75$ V	—	550	μ A
				$V_{IN} = 3.75$ V	—	1000	μ A
Input Voltage	$V_{IN(ON)}$	5	ULN2068B/LB	$V_{CE} = 2.0$ V, $I_C = 1.25$ A	—	2.75	V
			ULN2069B	$V_{CE} = 2.0$ V, $I_C = 1.5$ A	—	2.75	V
Supply Current	I_S	8	All	$I_C = 500$ mA, $V_{IN} = 2.75$ V	—	6.0	mA
Turn-On Delay	t_{PLH}	—	All	$0.5 E_{in}$ to $0.5 E_{out}$	—	1.0	μ s
Turn-Off Delay	t_{PHL}	—	All	$0.5 E_{in}$ to $0.5 E_{out}$, $I_C = 1.25$ A	—	1.5	μ s
Clamp Diode Leakage Current	I_R	6	ULN2068B/LB	$V_R = 50$ V	—	50	μ A
				$V_R = 50$ V, $T_A = 70^\circ\text{C}$	—	100	μ A
			ULN2069B/LB	$V_R = 80$ V	—	50	μ A
				$V_R = 80$ V, $T_A = 70^\circ\text{C}$	—	100	μ A
Clamp Diode Forward Voltage	V_F	7	All	$I_F = 1.0$ A	—	1.75	V
				$I_F = 1.5$ A	—	2.0	V

2064 THRU 2069

1.5 A DARLINGTON


SWITCHES

PEAK COLLECTOR CURRENT AS A FUNCTION OF DUTY CYCLE (Dual in-line packaged devices)




2064 THRU 2069 1.5 A DARLINGTON SWITCHES

PEAK COLLECTOR CURRENT AS A FUNCTION OF DUTY CYCLE (Dual in-line packaged devices)




Dwg. No. A-10,399C




Dwg. No. A-10,401C

PEAK COLLECTOR CURRENT AS A FUNCTION OF DUTY CYCLE (SOIC packaged devices)



Dwg. GP-045





Dwg. GP-045-1

2064 THRU 2069



1.5 A DARLINGTON

SWITCHES

INPUT CURRENT AS A FUNCTION OF INPUT VOLTAGE AT +25°C




COLLECTOR CURRENT AS A FUNCTION OF INPUT CURRENT AT +25°C



2064 THRU 2069 1.5 A DARLINGTON SWITCHES

TYPICAL APPLICATION



Dwg. No. B-1365


COMMON-CATHODE LED DRIVERS

(Types ULN2068B and ULN2068LB are also applicable)


2064 THRU 2069 1.5 A DARLINGTON SWITCHES

ULN2064B, ULN2065B, ULN2068B, and ULN2069B

Dimensions in Inches (controlling dimensions)




Dimensions in Millimeters (for reference only)



- NOTES:
1. Exact body and lead configuration at vendor's option within limits shown.
 2. Lead spacing tolerance is non-cumulative
 3. Lead thickness is measured at seating plane or below.
 4. Webbed lead frame. Leads 4, 5, 12, and 13 are internally one piece.

2064 THRU 2069 1.5 A DARLINGTON SWITCHES

ULN2064LB, ULN2065LB, ULN2068LB, and ULN2069LB



- NOTES:
1. Exact body and lead configuration at vendor's option within limits shown.
 2. Lead spacing tolerance is non-cumulative
 3. Lead thickness is measured at seating plane or below.
 4. Webbed lead frame. Leads 4 through 7 and 14 through 17 are internally one piece.

2064 THRU 2069 1.5 A DARLINGTON SWITCHES

Allegro MicroSystems, Inc. reserves the right to make, from time to time, such departures from the detail specifications as may be required to permit improvements in the design of its products. Components made under military approvals will be in accordance with the approval requirements.

The information included herein is believed to be accurate and reliable. However, Allegro MicroSystems, Inc. assumes no responsibility for its use; nor for any infringements of patents or other rights of third parties which may result from its use.

2064 THRU 2069 1.5 A DARLINGTON SWITCHES

POWER SINK DRIVERS SELECTION GUIDE

IN ORDER OF 1) OUTPUT CURRENT, 2) OUTPUT VOLTAGE, 3) NUMBER OF DRIVERS

Output Ratings *			Features					Part Number [†]
mA	V	#	Serial Input	Latched Drivers	Diode Clamp	Saturated Outputs	Internal Protection	
100	20	8	—	—	—	X	—	2595
	30	32	X	X	—	—	—	5833
	40	32	X	X	—	X	—	5832
250	135	7	—	—	X	—	—	7003
300	45	1	Hall Sensor/Driver		X	—	X	5140
	50	7	—	—	X	—	—	2003
	50	8	—	—	X	—	—	2803
	50	8	—	—	X	X	—	2596
	60	2	Hall Sensor/Driver		—	X	—	5275
	60	4	—	—	X	X	X	2557
	95	7	—	—	X	—	—	2023
	95	8	—	—	X	—	—	2823
350	50	4	—	X	X	—	—	5800
	50	7	—	—	X	—	—	2004
	50	8	—	—	X	—	—	2804
	50	8	—	X	X	—	—	5801
	50	8	X	X	—	—	—	5821
	80	8	X	X	—	—	—	5822
	50	8	X	X	X	—	—	5841
	80	8	X	X	X	—	—	5842
	95	7	—	—	X	—	—	2024
	95	8	—	—	X	—	—	2824
450	30	28	Dual 4 to 14-Line Decoder/Driver			—	—	6817
600	60	4	—	—	—	X	X	2547
	60	4	—	—	X	X	X	2549
700	60	4	—	—	X	X	X	2543 and 2559
750	50	8	—	—	X	X	—	2597
900	14	2	Hall Sensor/Driver		X	X	X	3625
	26	2	Hall Sensor/Driver		X	X	X	3626
1000	46	4	Stepper Motor Controller/Driver			MOS	—	7024 and 7029
1200	46	4	Microstepping Controller/Driver			MOS	—	7042
1250	50	4	Stepper Motor Translator/Driver			—	X	5804
	50	4	—	—	X	—	—	2064 and 2068
1500	80	4	—	—	X	—	—	2065 and 2069
1600	50	9	X	X	—	—	X	5829
1800	50	4	—	—	X	—	—	2544
	50	4	—	—	X	—	—	2540
3000	46	4	Stepper Motor Controller/Driver			MOS	—	7026
4000	50	4	—	—	X	—	—	2878
	80	4	—	—	X	—	—	2879

* Current is maximum specified test condition, voltage is maximum rating. See specification for sustaining voltage limits or over-current protection voltage limits.

† Complete part number includes additional characters to indicate operating temperature range and package style.



115 Northeast Cutoff, Box 15036
Worcester, Massachusetts 01615-0036 (508) 853-5000