





PRODUCT NO.

10126116-XYHLF

LEAD FREE OPTION
NOTE 6, 7 & 8
NO. OF POSITIONS
SEE TABLE
PIN PLATING
BASE P/N



mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 1302	ISO 406	ISO 1101	HEADER
ltr	ec	ndr	date	tolerances unless otherwise specified	title
A	NEW	ZK	06/14/13	angles linear	FRICION LATCH HEADER
				0°±2'	SINGLE ROW, R/A
				dr ZK HU 06/14/13	dwg no
				enr ZK HU 06/14/13	10126116
				chr RICK BIAN 06/14/13	sheet 1 of 2
				appd RICK BIAN 06/14/13	A3
sheet	revision	A	A		type Product Customer Drawing
index	sheet	1	2		

PDS: Rev :A

STATUS: Released

Printed: Jun 27, 2013



FCIconnect.com

Copyright FCI

PRODUCT NO.	NO.OF POS.	DIM K	DIM L	TAIL LENGTH DIM M
10126116-X03	1 X 3	.300/7.62	.200/5.08	.120/3.05
-X04	1 X 4	.400/10.16	.300/7.62	
-X05	1 X 5	.500/12.70	.400/10.16	
-X06	1 X 6	.600/15.24	.500/12.70	
-X07	1 X 7	.700/17.78	.600/15.24	
-X08	1 X 8	.800/20.32	.700/17.78	
-X09	1 X 9	.900/22.86	.800/20.32	
-X10	1 X 10	1.000/25.40	.900/22.86	
-X11	1 X 11	1.100/27.94	1.000/25.40	
-X12	1 X 12	1.200/30.48	1.100/27.94	
-X13	1 X 13	1.300/33.02	1.200/30.48	
-X14	1 X 14	1.400/35.56	1.300/33.02	
10126116-X15	1 X 15	1.500/38.10	1.400/35.56	.120/3.05
10126116-X43	1 X 3	.300/7.62	.200/5.08	.190/4.83

PIN PLATING CODES	
-1YY	30u"/.76u Au MIN. ON 50u"/1.27u Ni
-2YY	15u/.38u Au MIN. ON 50u"/1.27u Ni

NOTES:

1. MOLDING MAT'L: GLASS REINFORCED PCT OR MINRAL FILLED LCP, COLOR: BLACK
FLAME RETARDANT PER UL-94V-0
MAXIMUM OPERATING TEMPERATURE 130° C.
2. PIN MATERIAL: 3/4 HD PHOS. BRZ.
3. NO SLOTS ON 1 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.
4. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.
5. COMPANY LOGO MAY APPEAR IN THIS AREA.
6. ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
7. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADER	
ltr ecn nchr date		tolerances unless otherwise specified						title	
A		angles		linear		INCH/MM		FRICTION LATCH HEADER	
		0°±2'		XXX±.01/XXX±.03 XXX±.005/XXX±.013 XXX±.0020/XXX±.005		scale 3:1		SINGLE ROW, R/A	
		dr		ZK HU		06/14/13		dwg no	
		engr		ZK HU		06/14/13		sheet 2 of 2	
		chr		RICK BIAN		06/14/13		size	
		appd		RICK BIAN		06/14/13		A3	
sheet index		revision sheet						type Product Customer Drawing	