













PRODUCT NUMBER
10029449-X01XLF



SECTION
A-A

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family HDMI			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title HDMI TYPE A RECEPTACLE			
W	ELX-N-34628	Jason	2019-08-27	angles	.X±.3	scale 4:1				
				linear	.XX±.15					
				0'±x'	.XXX±.05					
				dr	TONY LENG	2017-05-22	dwg no		sheet 1 of 5	size
				engr	Jason Wang	2019-08-27	10029449			A3
				chr	-	-	type Product Customer Drawing			
				appd	TIM YAO	2019-08-27				
sheet index	revision	W								
	sheet	1								

PRODUCT NUMBER
10029449-002XLF



mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HDMI				
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title HDMI TYPE A RECEPTACLE					
					angles	linear	.X±.3 .XX±.15 .XXX±.05		scale 4:1 		dwg no sheet2 of 5 size 10029449 A3				
					0'±x'										
				dr	TONY LENG	2017-05-22									
				engr	Jason Wang	2019-08-27									
					chr	-	-								
					appd	TIM YAO	2019-08-27								
sheet index		revision sheet		w	2						type Product Customer Drawing				

PRODUCT NO.	CONTACT AREA PLATING	SHIELD FIGURE	PACKING
10029449-001TLF	30u" GXT MINIMUM	WITHOUT FLANGE	TRAY
10029449-001RLF	30u" GXT MINIMUM	WITHOUT FLANGE	TAPE AND REEL
10029449-101TLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	TRAY
10029449-101RLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	TAPE AND REEL
10029449-002TLF	30u" GXT MINIMUM	WITH FLANGE	TRAY
10029449-002RLF	30u" GXT MINIMUM	WITH FLANGE	TAPE AND REEL
10029449-002FLF	GOLD FLASH 3u" MIN	WITH FLANGE	TAPE AND REEL

NOTE:

1.MATERIAL:

1-1 HOUSING: GLASS FIBER HIGH-TEMP. RESIN.(UL94V-0)

1-2 CONTACT: BRASS

1-3 SHELL: STEEL

2.FINISH

2-1 CONTACT: Ni UNDER PLATED ALL OVER 50u" MIN

CONTACT AREA SEE TABLE

2-2 SHELL: Ni 100u" MIN

3.PACKAGING:


PACKAGING SPECIFICATION GS-14-939

4.PRODUCT SPEC:

PRODUCT SPECIFICATION GS-12-309

5.RoHS STANDARD SPECIFICATION ACCORDING TO FCI GS-22-008






6.PARTS MEET REFLOW APPLICATION PEAK TEM. 260°C, 10 SECONDS MAX.



RECOMMENDED PCB PATTERN LAYOUT
(t=1.6mm)

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family HDMI
ltr	ecn no	dr	date	tolerances unless otherwise specified	linear	mm	title HDMI TYPE A RECEPTACLE
				angles	.X±.3		
				0'±x'	.XX±.15		
					.XXX±.05	scale 4:1	
				dr	TONY LENG	2017-05-22	dwg no
				engr	Jason Wang	2019-08-27	sheet 3 of 5
				chr	-	-	size A3
				appd	TIM YAO	2019-08-27	type Product Customer Drawing
sheet index	revision sheet	W	3				

PRODUCT NO.	CONTACT AREA PLATING	SHIELD FIGURE	DIM "A"	PACKING
10029449-111RLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	2.02±0.20	TAPE AND REEL
10029449-111FLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	2.02±0.20	TAPE AND REEL, OPPOSITE DIRECTION
10029449-113RLF	GOLD FLASH 3u" MIN	WITHOUT FLANGE	0.90±0.20	TAPE AND REEL



SECTION S-S
SCALE 1:1

NOTE:

1.MATERIAL:


HOUSING: HIGH TEMP.THERMOPLASTIC, UL 94V-0
COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE
SHIELD: BRASS

2.FINISH:

SEE NOTES.

3.TERMINAL RETENTION FORCE TO BE 0.3kgf MIN.



4.TERMINAL CUT-OFF BURR TO BE 0.05MAX.



RECOMMENDED PCB LAYOUT
CONNECTOR SIDE





mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family HDMI
ltr	ecn no	dr	date	tolerances unless otherwise specified	linear	mm	title HDMI TYPE A RECEPTACLE
				angles	.X±.3		
				0'±x'	.XX±.15		
				dr TONY LENG	.XXX±.05	scale 2:1	
				engr Jason Wang			dwg no sheet4 of 5 size
				chr -			10029449 A3
				appd TIM YAO	2019-08-27		type Product Customer Drawing
sheet index	revision sheet	W	4				

PRODUCT NO.	CONTACT AREA PLATING	SHIELD FIGURE	PACKING
10029449-112TLF	GOLD FLASH 3u" MIN	WITH FLANGE	TRAY
10029449-112RLF	GOLD FLASH 3u" MIN	WITH FLANGE	TAPE AND REEL



RECOMMENDED PCB LAYOUT(t=1.60±0.15)
COMPONENT SIDE

NOTE:
1.MECHANICAL CHARACTERISTICS
INSERTION FORCE: 44.1N MAX
WITHDRAWAL FORCE: 9.8N MIN, 39.2N MAX
MATING CYCLE:10000 CYCLES
CONTACT PULL OUT FORCE: 1.96N/PIN MIN
2.ELECTRICAL CHARACTERISTICS
RATING CURRENT: 0.5A
RATING VOLTAGE: 40V
CONTACT RESISTANCE: 10 MILLOHMS OHMS MAX
(EXCLUDING CONDUCTOR RESISTANCE)
INSULATION RESISTANCE:
a, UNMATED: 100M OHMS MIN AT 500 VDC
b, MATED: 10M OHMS MIN AT 150 VDC
DIELECTRIC WITHSTANDING VOLTAGE: 300V AC/1MINUTE
OPERATING TEMPERATURE: -20°C--+85°C
STORAGE TEMPERATURE: -20°C--+65°C



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 1101	product family HDMI
ltr	ecn	no	dr	date	tolerances unless otherwise specified	mm	title
					angles linear	mm	HDMI TYPE A RECEPTACLE
					0'±x'	scale 2:1	
					dr TONY LENG	2017-05-22	dwg no
					engr Jason Wang	2019-08-27	sheet5 of 5
					chr -	-	size
					appd TIM YAO	2019-08-27	10029449
sheet index				revision sheet	W		type Product Customer Drawing
				5			