


- BASE PART NO.

[illegible]

1		2		3	4		5	6	
PRODUCT NUMBER		MATING LENGTH		PIN PLATING CODES:					
		DIM H	DIM H	10129380-9YYXXXLFL1u"/0.025u MIN Au OVER 50u"/1.27u MIN Ni					
		ENGLISH	METRIC						
10129380-YYY001XLF		0.230	5.84						
10129380-YYY002XLF		0.318	8.08						
NOTES:									
1. MATERIAL									
BODAY MATERIAL: HIGH TEMPERATURE THERMOPLASTIC.									
FLAME UL94-V0, BLACK.									
PIN MATERIAL: COPPER ALLOY.									
2. ANY NUMBER OF POSITIONS N FROM 2 TO 20.									
PRODUCT MAYBE CUTTING TO POSITION,									
THE CUTTING PLASH IS 0.02[0.51] MAX.									
3. PACKING STYLE DEFINITION.									
B: PACKED WITH POLY BAG									
T: PACKED WITH TUBE									
A: PACKED WITH TAPE AND REEL WITH PICK UP CAP									
C: PACKED WITH TAPE AND REEL WITHOUT PICK UP CAP									
4. TWO SIDES OF PIN TIPS NOT PLATED, TYPICAL BOTH ENDS.									
5. 2LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION BEFORE REFLOW.									
6. THE OAL DON'T EXCEED 1 INCH / 25.4MM.									
7. ADD LF AT THE END OF PART NUMBER IS FOR LEAD FREE.									
8. THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER									
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.									
9. THE PRODUCT WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE									
FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.									
10. PRODUCT SPECIFICATION: GS-12-1223.									
mat'l. code		surface		tolerance		projection		product family	
SEE NOTES 1		ISO 1302 ✓		ISO 406 ISO 1101				ECONOSTIK	
ltr ecn nodr date		tolerances unless otherwise specified						title	
B		angles		linear		INCH/MM		ECONOSTIK HEADER	
		0°±2°		.XX±.01/.XX±.03 .XXX±.008/.XX±.020 .XXXX±.0040/.XXX±.0.100		scale 2:1		.100/2.54cc SR SMT	
		dtr		ZK HU		04/23/14		dwg no sheet2 of 2 size	
		engr		ZK HU		04/23/14		10129380 A3	
		chr		RICK BIAN		04/23/14		type Product Customer Drawing	
		appd		RICK BIAN		04/23/14			
sheet index		revision sheet							