



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS	SIGNAL					POWER					
		6	5	4	3	2	1	P5	P4	P3	P2	P1
51756-001-- NOTE: 3	D	E	E	E	E	E	E	X	PA	PA	PA	PA
	C	E	E	E	E	E	E					
	B	E	E	E	E	E	E					
	A	E	E	E	E	E	E					



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
E	[N/A]	SIGNAL
PA	[1.07]	POWER
X	OMITTED	OMITTED

mat'l code				SEE NOTE		tolerances unless otherwise specified		CUSTOMER		CONFIDENTIAL			
lir	ecn no.	dr	date	linear	0.X ±0.3 0.XX ±0.10 0.XXX ±0.050 0° ±2°	JM GUO 22/06/06 SLUO 22/06/06 BEER FU 22/06/06 JOSEPH HSIA 22/06/06	22/06/06 22/06/06 22/06/06 22/06/06	projection MM scale 1:1	COPY title 5P + 24S VERTICAL STB RECEPTACLE WITHOUT GUIDE POST product family PwrBlade size A dwg no 51756-001	www.fciconnect.com			
A	DG06-0245	JMG	22/06/06							code 213 sheet 1 of 4			
sheet index		revision sheet	A 1	A 2	A 3	A 4				cage code 22526			

Pro/E

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER

51756-001--
NOTE: 3



CONFIDENTIAL

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI			
lir	ecn no.	dr	date					www.fciconnect.com			
A				linear	0.X ±0.3	projection	COPY	title 5P + 24S VERTICAL STB RECEPTACLE WITHOUT GUIDE POST			
					0.XX ±0.10						
				angles	0.XXX ±0.050						
					0° ±2°			product family PwrBlade code 213 size 51756-001 sheet 2 of 4			
				dr	JM GUO	22/06/06	MM				
				engr	SLUO	22/06/06	scale				
				chr	BEER FU	22/06/06	1:1				
				appd	JOSEPH HSIA	22/06/06					
sheet index	revision sheet										

cage code 22526

Pro/E

PDM: Rev:A

STATUS: Released


Printed: Dec 20, 2010

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51756-001--
NOTE: 3



CONFIDENTIAL

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com	
lfr	ecr no.	dr	date	linear	0.X ±0.3		COPY		
A					0.XX ±0.10		projection		
				angles	0.XXX ±0.050				
					0° ±2°				
				dr	JM GUO	22/06/06			
				enrg	SLUO	22/06/06			
				chr	BEER FU	22/06/06	scale 1:1		
				appd	JOSEPH HSIA	22/06/06			
sheet index	revision sheet								

cage code 22526

Pro/E

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010



PRODUCT NUMBER

51756-001--
NOTE: 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH
ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- 2 HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING SPEC.
51756-001, 51756-001LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.
- 4 MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON
THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.

PCB NOTES:
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 8 MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
- 9 $\varnothing .0453 \pm .0010$ [1.151 $\pm$ 0.025] DRILLED HOLES PLATED WITH
.0003 [0.008] MIN SnPb OVER .001 [0.03]
TO .003 [0.08] Cu PLATING TO ACHIEVE
 $\varnothing .040 \pm .003$ [1.02 $\pm$.07] HOLE.
- 10 "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- 11 CONNECTOR KEEP-OUT ZONE.

CONFIDENTIAL

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI			
lfr	ecn no.	dr	date			COPY		www.fciconnect.com			
A				linear	0.X $\pm$ 0.3	projection		title			
					0.XX $\pm$ 0.10			5P + 24S			
				angles	0.XXX $\pm$ 0.050			VERTICAL STB RECEPTACLE WITHOUT GUIDE POST			
					0° $\pm$ 2°						
				dr	JM GUO 22/06/06	MM		product family PwrBlade			
				engr	SLUO 22/06/06	scale		size			
				chr	BEER FU 22/06/06	1:1		dwg no			
				appd	JOSEPH HSIA 22/06/06			A 51756-001			
sheet index		revision sheet						code			
								213			
								sheet 4 of 4			

cage code 22526

Pro/E

PDM: Rev:A

STATUS: Released

Printed: Dec 20, 2010