





PART NO.
20021212



SECTION A-A



RECOMMENDED PCB LAYOUT

SCALE 5.000

NOTES:

- 1.MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.
TERMINAL: COPPER ALLOY
- 2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260~C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER OR VAPOR PHASE REFLOW OVEN.
- 3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 4.PRODUCT SPEC: GS-12-629
- 5.PACKAGE SPEC: GS-14-1420



mat'l. code				surface			tolerance	projection	product family		
				ISO 1302			ISO 406	ISO 1101	MINITEK127®		
ltr	ecn no	dr	date	tolerances unless otherwise specified					title		
F	ELX-N-23548	TIM	03/21/16	angles			.0±.30	mm	SHROUDED HDR RA TH		
				linear			.00±.20				
				0°±2°			.000±.10	scale 1:1			
				dr	ZK HU	08/07/12			dwg no		
				engr	ZK HU	08/07/12			sheet 1 of 2		
				chr	BIAN RICK	08/07/12			20021212		
				appd	BIAN RICK	08/07/12			A3		
sheet	revision	F	F						type Product Customer Drawing		
index	sheet	1	2								

PART NO.	PDS.	DIM"x"	DIM"y"	DIM"z"
20021212-XXX06XXLF	2 X 3	6.99	4.45	2.54
20021212-XXX08XXLF	2 X 4	8.26	5.72	3.81
20021212-XXX10XXLF	2 X 5	9.53	6.99	5.08
20021212-XXX12XXLF	2 X 6	10.80	8.26	6.35
20021212-XXX14XXLF	2 X 7	12.07	9.53	7.62
20021212-XXX16XXLF	2 X 8	13.34	10.80	8.89
20021212-XXX18XXLF	2 X 9	14.61	12.07	10.16
20021212-XXX20XXLF	2 X 10	15.88	13.34	11.43
20021212-XXX22XXLF	2 X 11	17.15	14.61	12.70
20021212-XXX24XXLF	2 X 12	18.42	15.88	13.97
20021212-XXX26XXLF	2 X 13	19.69	17.15	15.24
20021212-XXX28XXLF	2 X 14	20.96	18.42	16.51
20021212-XXX30XXLF	2 X 15	22.23	19.69	17.78
20021212-XXX32XXLF	2 X 16	23.50	20.96	19.05
20021212-XXX34XXLF	2 X 17	24.77	22.23	20.32
20021212-XXX36XXLF	2 X 18	26.04	23.50	21.59
20021212-XXX38XXLF	2 X 19	27.31	24.77	22.86
20021212-XXX40XXLF	2 X 20	28.58	26.04	24.13
20021212-XXX42XXLF	2 X 21	29.85	27.31	25.40
20021212-XXX44XXLF	2 X 22	31.12	28.58	26.67
20021212-XXX46XXLF	2 X 23	32.39	29.85	27.94
20021212-XXX48XXLF	2 X 24	33.66	31.12	29.21
20021212-XXX50XXLF	2 X 25	34.93	32.39	30.48
20021212-XXX52XXLF	2 X 26	36.20	33.66	31.75
20021212-XXX54XXLF	2 X 27	37.47	34.93	33.02
20021212-XXX56XXLF	2 X 28	38.74	36.20	34.29
20021212-XXX58XXLF	2 X 29	40.01	37.47	35.56
20021212-XXX60XXLF	2 X 30	41.28	38.74	36.83
20021212-XXX62XXLF	2 X 31	42.55	40.01	38.10
20021212-XXX64XXLF	2 X 32	43.82	41.28	39.37
20021212-XXX66XXLF	2 X 33	45.09	42.55	40.64
20021212-XXX68XXLF	2 X 34	46.36	43.82	41.91
20021212-XXX70XXLF	2 X 35	47.63	45.09	43.18
20021212-XXX72XXLF	2 X 36	48.90	46.36	44.45
20021212-XXX74XXLF	2 X 37	50.17	47.63	45.72
20021212-XXX76XXLF	2 X 38	51.44	48.90	46.99
20021212-XXX78XXLF	2 X 39	52.71	50.17	48.26
20021212-XXX80XXLF	2 X 40	53.98	51.44	49.53
20021212-XXX82XXLF	2 X 41	55.25	52.71	50.80
20021212-XXX84XXLF	2 X 42	56.52	53.98	52.07
20021212-XXX86XXLF	2 X 43	57.79	55.25	53.34
20021212-XXX88XXLF	2 X 44	59.06	56.52	54.61
20021212-XXX90XXLF	2 X 45	60.33	57.79	55.88

PART NO.	PDS.	DIM"x"	DIM"y"	DIM"z"
20021212-XXX92XXLF	2 X 46	61.60	59.06	57.15
20021212-XXX94XXLF	2 X 47	62.87	60.33	58.42
20021212-XXX96XXLF	2 X 48	64.14	61.60	59.69
20021212-XXX98XXLF	2 X 49	65.41	62.87	60.96
20021212-XXXA0XXLF	2 X 50	66.68	64.14	62.23

20021212 - X X X XX X X LF

- LEAD FREE
- PLATING OPTIONAL
 - 1: GOLD FLASH AT CONTACT, 127um MIN. MATTE TIN AT TAIL
 - 2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL
 - 4: 0.25um Au MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
 - 5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL
 - 6: 0.38um GXT MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
 - 7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL
 - 8: 0.76um GXT MIN. AT CONTACT, 127um MIN.MATTE TIN AT TAIL
 - 9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL
- PACKING STYLE
 - T: TUBE
- PIN NO. SEE TABLE
- MATING LENGTH(DIM"A")
 - 0: 3.05MM,HOUSING:STANDARD
 - 1: 3.05MM,HOUSING:FILL 4 HOLES ON BOTH WALLS(40PIN ONLY,SEE VIEW 1)
- TAIL LENGTH(DIM"B")
 - 0: 2.30MM (FOR 1.6MM PCB)
 - 1: 1.60MM (FOR 1.0MM PCB)
 - 2: 2.70MM (FOR 2.0MM PCB)
- RESERVE CODE
 - 0: STANDARD



VIEW 1:20021212-XX140XXLF

mat'l. code				surface ☒ ISO 1302 ☐ ISO 406 ☐ ISO 1101		tolerance unless otherwise specified		projection ☒ 1:1 ☐ mm		product family MINITEK127®		
ltr	ecn no	dr	date	angles		linear		mm		title		
F				0°±2'		.0±.30 .00±.20 .000±.10		scale 1:1		SHROUDED HDR RA TH		
				dr	ZK HU	08/07/12			dwg no		sheet 2 of 2	size
				engr	ZK HU	08/07/12			20021212		A3	
				chr	BIAN RICK	08/07/12			type		Product Customer Drawing	
				app	BIAN RICK	08/07/12						
sheet index	revision sheet											