





mat'l. code			surface ☒ tolerance		projection		product family				
			ISO1302 ✓ ISO1101 ISO406				MINITEK				
ltr	ecn	nodr	date		tolerances unless otherwise specified		title				
A	T09-1117	S.LIN	09/15/09	angle line 0°±2'	0.X±0.38		1.27X1.27MM BTB RECEPTACLE SMT BOTTOM ENTYR				
B	T10-0020	S.LIN	01/20/10		0.XX±0.25						
C	T10-0120	S.LIN	07/30/10		0.XXX±0.10					scale 8:1	
D	ELXT004402	S.LIN	07/11/11	dr	STERLING LIN	09/15/09		dwg no		sheet 1 of 1	size
E	BLX-N-010370	ZK	01/16/12	engr	STERLING LIN	09/15/09		20021323		A4	
F	BLX-N-011532	ZK	05/07/12	chr	GRAY HSIEH	09/15/09					
G	BLX-N-011756	ZK	05/28/12	appd	JOSEPH	09/15/09		type		Product Customer Drawing	
sheet		revision									
index		sheet		1							

1. MATERIAL,
HOUSING: HIGH TEMP PLASTIC, UL94-V0,BLACK
TERMINAL: COPPER ALLOY , T=0.15MM
CAP: STAINLESS STEEL, T=0.1MM
2. FINISH:
TERMINAL: GOLD AT CONTACT,
G/F OVER 1.27um(50u")MIN Ni OVER ALL
3. SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1420
4. THE HSG. WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMP. FOR 10 SEC. IN A CONVECTION INFRA-RED
OR VAPOR PHASE REFLOW.
5. PRODUCT NUMBERING:
20021323 - X 0 0 XX X X LF

PLATING:
1:GOLD FLASH ALL OVER
4:0.25um(10U")GOLD AT CONTACT
8:0.76um(30U")GOLD AT CONTACT
9:1u" GOLD OVER 30u" PdNi AT CONTACT

— PACKING
D: TUBE + CAP
T: TUBE
C: REEL + CAP (8,10,20,22,30,40,42,70P)
— PIN COUNT
4,6,8,...,80
(EVERY EVEN PIN)
— 0: WITHOUT POST
1: WITH POST