





Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	POWER			
	E1	P1	P2	E2
51952-114	PA	PA		
NOTE ③				



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ± 0.3	COPY		www.fciconnect.com	
A	DG07-0048	JMG	02/05/07		0.XX ± 0.13	projection		title	
				angles	0.XXX ± 0.051			2P	
				dr	0° ± 2°			VERTICAL SOLDER HEADER	
				enr	JM GUO 02/05/07	MIM		product family PwrBlade	
				chr	RYAN YUAN 02/05/07			code	
				appd	BEER FU 02/05/07	scale		213	
					JOSEPH HSIA 02/05/07	1:1		sheet	
sheet index	revision sheet	A	A	A	A			1 of 4	
		1	2	3	4				

Pro/E



cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51952-114--
NOTE 3




mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	www.fciconnect.com	
A					0.XX ±0.13				
					0.XXX ±0.051				
				angles	0° ±2°	MIM	scale	title 2P VERTICAL SOLDER HEADER	
				dr	JM GUO 02/05/07				
				enr	RYAN YUAN 02/05/07				
				chr	BEER FU 02/05/07	1:1	A	product family PwrBlade	
				appd	JOSEPH HSIA 02/05/07				
sheet index		revision sheet						size dwg no 51952-114	
								code 213	
								sheet 2 of 4	
				Pro/E				cage code 22526	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51952-114--
NOTE 3



mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
litr	ecn no.	dr	date	linear	0.X ± 0.3	COPY		www.fciconnect.com	
A				linear	0.XX ± 0.13	projection		title 2P	
				angles	0.XXX ± 0.051			VERTICAL SOLDER HEADER	
				dr	0° ± 2°			product family PwrBlade	
				enrg	JM GUO 02/05/07			code 213	
				chr	RYAN YUAN 02/05/07			size dwg no	
				appd	BEER FU 02/05/07			A 51952-114	
					JOSEPH HSIA 02/05/07	scale		sheet 3 of 4	
sheet index	revision sheet								

Pro/E

cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51952-114-- NOTE 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- (2) HOUSING MATERIAL: UL 94 V-0 GLASS FILLED
HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. PLATING:
51952-114 ,51952-114LF PLATING SPEC. WAS SHOWN IN THE PRINT OF 10064183.
- (4) MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.
- PCB NOTES:
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.
- (9) $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER .001 [0.03]
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
- (10) "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- (11) CONNECTOR KEEP-OUT ZONE.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI			
ltr	ecn no.	dr	date			COPY		www.fciconnect.com			
A				linear	$0.X \pm 0.3$	projection		title			
					$0.XX \pm 0.13$			2P			
				angles	$0.XXX \pm 0.051$			VERTICAL SOLDER HEADER			
					$0^\circ \pm 2^\circ$						
				dr	JM GUO 02/05/07			product family		PwrBlade	code
				enrg	RYAN YUAN 02/05/07			size	dwg no		213
				chr	BEER FU 02/05/07			A		51952-114	sheet
				appd	JOSEPH HSIA 02/05/07	scale	1:1				4 of 4
sheet index	revision sheet										

Pro/E

cage code 22526