





RECOMMENDED PANEL CUT-OUT




PRODUCT NO	NUMBER OF POS.	LOADED POSITION	HSG COLOR	PLATING
61885-0661	6	ALL POS.	BLACK	5u" Au + high performance lubricant
61885-0641		2,3,4,5		
61885-0621		3,4		
61885-0661LF		ALL POS.		
61885-0641LF		2,3,4,5		
61885-0621LF		3,4		




LEAD FREE PRODUCT NO.

NOTES:


1. RECOMMENDED P.C.B. THICKNESS 1.60 MM
2. HOUSING MAT'L: NYLON 66, 25% GLASS REINFORCED, COLOR: SEE TABLE
3. CONTACTS: PHOS BRONZE ALLOY UNS-C51000, Ø 0.460 ROUND WIRE, PLATING SEE TABLE.
- ④ METAL SHELL MATERIAL:
COPPER ALLOY, 0.20MM THICK.
FINISH: FOR 61885-XXXX TIN-LEAD 100 u" THICK .
FOR 61885-XXXXLF PURE TIN 80 u" THICK .
5. PACKAGING PER GES-14-361, USING TUBE
6. IF LF P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED INS GS-22-008
7. IF LF P/N THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.60mm MINIMUM THICK CIRCUIT BOARD
8. IF LF P/N PACKAGING MEETS GS-14-920 SPECIFICATION



RECOMMENDED P.C.B. LAOUT



POS. NO. CONFIGURATION



mat'l. code	surface ISO1302	tolerance ISO1101 ISO406	projection ISO 1101	product family MOD JACK
l'recn nodr	date	tolerances unless otherwise specified	mm	title
C T80510 MW	11/18/98	0.X±0.3	mm	LOW PROFILE PCB III 6 POS
D T03-0443 WL	10/06/03	0.XX±0.15	mm	MOD JACK, FULLY SHIELDED
E N04-0125 YS	12/15/04	0.XXX±0.05	scale 2.0	
F ELX-N-011021 SH MM	03/25/12	dr C M HSU	03/27/97	dwg no sheet 1 of 1 size
		engr TONY CHIEN	03/27/97	61885 A4
		chr TONY CHIEN	03/27/97	
		appd JENN TSAO	03/27/97	type Product Customer Drawing
sheet index	revision sheet 1			