






PRODUCT NO	TERMINAL BODY		LEAD FREE
	MATERIAL	PLATING OR GOLD DOT	OPTION
65829-001	0.25/.010 THK 1/4 HD CU NI ALLOY UNS C72500	.002/.001 MIN THK GOLD DOT	---
65829-002	0.25/.010 THK 1/4 HD BRASS ALLOY UNS C26000	1.02μ/40μ" GOLD AT CONTACT REMAINDER GOLD FLASH OVER 1.27μ/50μ" NICKEL	---
65829-003	0.25/.010 BRASS ALLOY	.76μ/30μ" Au or GXT AT CONTACT OVER 1.27μ/50μ" NICKEL	NOTE 5,6



SECTION XX



- NOTES:
- WHITE LINES AS SHOWN FOR POLARIZATION.
 - HOUSING MAT'L: PLAIN POLYESTER, OPT. PLAIN NORYL, FLAME RETARDANT PER UL-94V-0 COLOR BLACK.
 - TERMINAL BODY MAT'L: SEE TABLE
 - SPRING MAT'L: 0.122/.0048 TH'K BE CU ALLOY, UNS C17200. HEAT TREATED PLATING: GOLD FLASH.
 - ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
 - THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 - THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.

mat'l. code		surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection ISO 1101	product family JUMPER
l	tr	ec	n	d	r
E	ADDED	EBY	4/9/86	date	tolerances unless otherwise specified
F	M05-0205	MHT	9/30/05	angles	linear .X±.01/.3
G	M06-0238	MN	06/16/06	0°±2'	linear .XX±.05/.13
H	M06-0389	AGS	10/4/06	dr	linear .XXX±.0020/.051
J	SLX-H-011384	J.Z	2012-04-24	engr	scale 10:1
				chr	
				appd	
sheet	revision				
index	sheet	1			
				title	
				2X2 MINI JUMPER ASS'Y .100 X .100	
				dwg no	sheet of 1 size
				65829	A3
				type Product Customer Drawing	