



PRODUCT NO	PLATING
63429-1Y2	0.38um/15u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)
63429-2Y2	0.76um/30u" GOLD GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)
63429-3Y2	2.54um/100u" TIN/LEAD OVER 1.27um/50u" Ni
63429-4Y2	GOLD FLASH ON CONTACT AREA OVER 1.27um/50u" Ni

PRODUCT NO	PLATING
63429-1Y2LF SEE NOTE 6	0.38um/15u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)
63429-2Y2LF SEE NOTE 6	0.76um/30u" GOLD OR GXT ON CONTACT AREA OVER 1.27um/50u" Ni (SEE NOTE 7)
63429-4Y2LF SEE NOTE 6	GOLD FLASH ON CONTACT AREA OVER 1.27um/50u" Ni



NOTE:

1.MATERIAL

HOUSING & COLOR: REFER TO TABLE.

FLAME RETARDANT PER UL 94V-0

TERMINAL : PHOSPHOR BRONZE

2.PLATING : REFER TO TABLE

3.TECHNICAL REQUIREMENTS:

INSERTION FORCE : 12 NEWTONS (2.7 LB) MAX. PER CONNECTOR.
WITHDRAWL FORCE : 2 NEWTONS (0.45 LB) MIN. PER CONNECTOR.
(MATE WITH 0.635MM SQ. PIN 2.54MM PITCH HEADER)


4.THE HOUSING WILL WITHSTAND EXPOSURE TO 200°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION,INFRA-RED OR VAPOR PHASE REFLOW OVEN.

5.THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION,INFRA-RED OR VAPOR PHASE REFLOW OVEN.

6.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

7. PLATING OPTION:

MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.



spec ref	dr	Louis Ng	2010/10/11	projection	MM	size	A3	scale	6:1
tolerance std	eng	Zheng-Kun Hu	2014/09/19	chr	-	ecn no	ELX-N-18461-1	rel level	Released
ISO 406 ISO 1101	appr	Feagle Pan	2014/09/24	product family	JUMPER	rel level	Released	rev	J
surface	linear	0.X	±0.35	FCI	JUMPER	dwg no	63429	cat. no.	-
ISO 1302	angular	0°	±3°	www.fci.com	Product - Customer Drw	sheet 1 of 1			