




PRODUCT NUMBER
SEE TABLE

Co. LOGO WILL APPEAR ON THIS SURFACE IF HOUSING HAS A MINIMUM OF 8 POSITIONS. Co. LOGO AND PART NUMBER WILL APPEAR ON THIS SURFACE IF HOUSING HAS A MINIMUM OF 16 POSITIONS.

CAVITIES WILL BE MARKED STARTING WITH THE FIRST POSITION AND CONTINUING EVERY FOURTH POSITION AS SHOWN. CHARACTERS ARE TO BE .06 HIGH. NO PRINTING WILL OCCUR ON A HOUSING WITH LESS THAN 8 POSITIONS.



mat'l. code SEE NOTE 1				surface	tolerance	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			PV HOUSINGS
G	v80287	LSS	1995-03-31	angles	linear	INCH/MM	title
H	v60479	EPK	1995-04-04				MAXI LATCH HOUSING DR
J	v90981	RGD	1999-06-21	0'±2'		Scale 2:1	.125 [3.18] X .125 [3.18]CC
K	v03-1333	PJ	2004-01-14	dr	L. SANDERS	1995-03-31	dwg no
L	v05-0713	DAI	2005-07-29	engr	L. FYE	1995-03-31	sheet 1 of 3
M	v06-0454	HTB	2006-05-25	chr	T. BREWBAKER	1995-03-31	size
N	v07-0493	HTB	2007-07-27	appd	L. FYE	1995-03-31	A3
sheet	revision	N	N	N			type
index	sheet	1	2	3			Product Customer Drawing

PRODUCT NUMBER
SEE TABLE




FIG 4

NOTES:

- ①. MOLDING MATERIAL: MODIFIED POLYPHENYLENE ETHER, FLAME RETARDANT PER UL-94V-0, COLOR: BLACK.
2. PIN LENGTH TO BE .250 [6.35] MIN. RECOMMENDED PIN LENGTH IS .265±.015 [6.720 ±.380]
- ③. TO LATCH TERMINAL—PUSH AS SHOWN IN FIGURE #1, BE SURE THAT LATCH SNAPS DOWN. MINIMUM PULL-OUT FORCE OF TERMINAL WILL BE 6.5 LBS[2.9Kg]. (WHEN PULLED AS SHOWN).
- ④. TO REMOVE TERMINAL—PUSH TERMINAL FORWARD. LIFT LATCH WITH HANDTOOL. AS SHOWN IN FIG. #2 & 3. DAMAGE TO LATCH CAN OCCUR IF LIFTED MORE THAN 25° ANGLE TO TOP OF HOUSING.
- ⑤. MAX. WIRE CRIMP AND WIRE STRANDS ARE SHOWN IN FIGURE #4. IF THIS IS EXCEEDED, LATCHING WILL NOT BE SATISFACTORY SEE MAXI PV™ TERMINAL SPECIFICATION TA-213 FOR CORRECT CRIMP HEIGHT FOR EACH DIFFERENT WIRE SIZE.
6. THIS HOUSING IS INTENDED FOR USE MAXI PV™ TERMINAL WITH 18-32 GAGE WIRE MEETING SPECIFICATION SHOWN IN FIGURE # 4.
7. PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
8. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.




FIG 1




FIG 2




FIG 3

mat'l. code SEE NOTE 1				surface	tolerance	projection	product family PV HOUSINGS		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
N				angles	linear	INCH/MM	MAXI LATCH HOUSING DR		
				0°±2°		scale 2:1	.125 [3.18] X .125 [3.18]CC		
				dr	L. SANDERS	1995-03-31	dwg no		
				engr	L. FYE	1995-03-31	sheet 2 of 3		
				chr	T. BREWBAKER	1995-03-31	65410		
				appd	L. FYE	1995-03-31	A3		
sheet	revision						type		
index	sheet						Product Customer Drawing		



FCJconnect.com

Copyright FCJ

PRODUCT NUMBER	NO OF POS	DIM J MAX	DIM K	STAMPING NOTES
65410-004LF	2 X 2	.267/6.78	.125/3.18	DON'T STAMP
65410-006LF	2 X 3	.392/9.96	.250/6.35	DON'T STAMP
65410-008LF	2 X 4	.517/13.13	.375/9.53	LOGO
65410-010LF	2 X 5	.642/16.31	.500/12.70	LOGO
65410-012LF	2 X 6	.767/19.48	.625/15.88	LOGO
65410-014LF	2 X 7	.892/22.68	.750/19.65	LOGO
65410-016LF	2 X 8	1.017/25.83	.875/22.23	LOGO & PART NO.
65410-018LF	2 X 9	1.142/29.01	1.000/25.40	LOGO & PART NO.
65410-020LF	2 X 10	1.267/32.18	1.125/28.58	LOGO & PART NO.
65410-022LF	2 X 11	1.392/35.36	1.250/31.75	LOGO & PART NO.
65410-024LF	2 X 12	1.517/38.53	1.375/34.93	LOGO & PART NO.
65410-026LF	2 X 13	1.642/41.71	1.500/38.10	LOGO & PART NO.
65410-028LF	2 X 14	1.767/44.88	1.625/41.38	LOGO & PART NO.
65410-030LF	2 X 15	1.892/48.07	1.750/45.05	LOGO & PART NO.
65410-032LF	2 X 16	2.017/51.23	1.875/47.63	LOGO & PART NO.
65410-034LF	2 X 17	2.142/54.41	2.000/50.80	LOGO & PART NO.
65410-036LF	2 X 18	2.267/57.58	2.125/53.98	LOGO & PART NO.
65410-038LF	2 X 19	2.392/60.76	2.250/57.15	LOGO & PART NO.
65410-040LF	2 X 20	2.517/63.93	2.375/60.33	LOGO & PART NO.
65410-042LF	2 X 21	2.642/67.11	2.500/63.50	LOGO & PART NO.
65410-044LF	2 X 22	2.767/70.28	2.625/66.68	LOGO & PART NO.
65410-046LF	2 X 23	2.892/73.46	2.750/69.85	LOGO & PART NO.
65410-048LF	2 X 24	3.017/76.63	2.875/73.03	LOGO & PART NO.
65410-050LF	2 X 25	3.143/79.81	3.000/76.20	LOGO & PART NO.
65410-052LF	2 X 26	3.267/82.98	3.125/79.38	LOGO & PART NO.
65410-054LF	2 X 27	3.392/86.16	3.250/82.55	LOGO & PART NO.
65410-056LF	2 X 28	3.517/89.33	3.375/85.73	LOGO & PART NO.
65410-057LF	DISCONTINUED			

mat'l. code SEE NOTE 1				surface ☒		tolerance		projection		product family PV HOUSINGS	
ltr	ecn no	dr	date	tolerances unless otherwise specified						title	
N				angles	linear	.XX+.01/.X+.3		INCH/MM		MAXI LATCH HOUSING DR	
						.XXX+.005/.XXX+.13				.125 [3.18] X .125 [3.18]CC	
				0'±2"		.XXXX+.0020/.XXX+.051		scale 1:1		dwg no	
				dr	L. SANDERS	1995-03-31				sheet 3 of 3	
				engr	L. FYE	1995-03-31				size	
				chr	T. BREWBAKER	1995-03-31				A3	
				appd	L. FYE	1995-03-31				type	
sheet	revision									Product Customer Drawing	
index	sheet										