




PRODUCT NUMBER
SEE TABLE

Co. LOGO WILL APPEAR ON THIS SURFACE IF HOUSING HAS A MINIMUM OF 8 POSITIONS. Co. LOGO AND PART NUMBER WILL APPEAR ON THIS SURFACE IF HOUSING HAS A MINIMUM OF 16 POSITIONS.

CAVITIES WILL BE MARKED STARTING WITH THE FIRST POSITION AND CONTINUING EVERY FOURTH POSITION AS SHOWN. CHARACTERS ARE TO BE .06 HIGH. NO PRINTING WILL OCCUR ON A HOUSING WITH LESS THAN 8 POSITIONS.



mat'l. code				surface	tolerance	projection	product family
SEE NOTE 1				✓		⊕	PV HOUSINGS
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
G	v80287	LSS	1995-03-31	angles	linear	XX±.01/XX±.3	MAXI LATCH HOUSING DR .125 [3.18] X .125 [3.18]CC
H	v60479	EPK	1995-04-04			XXX±.005/XX±.13	
J	v90981	RGD	1999-06-21	0'±2'		XXXX±.0020/XXX±.051	
K	v03-1333	PJ	2004-01-14	dr			
L	v05-0713	DAI	2005-07-29	engr			FCJ sheet 1 of 3 size 65410 A3
M	v06-0454	HTB	2006-05-25	chr			
N	v07-0493	HTB	2007-07-27	appd			
sheet	revision	N	N	N			type Product Customer Drawing
index	sheet	1	2	3			

PRODUCT NUMBER
SEE TABLE




FIG 4

NOTES:

- ①. MOLDING MATERIAL: MODIFIED POLYPHENYLENE ETHER, FLAME RETARDANT PER UL-94V-0, COLOR: BLACK.
2. PIN LENGTH TO BE .250 [6.35] MIN. RECOMMENDED PIN LENGTH IS .265±.015 [6.720 ±.380]
- ③. TO LATCH TERMINAL—PUSH AS SHOWN IN FIGURE #1, BE SURE THAT LATCH SNAPS DOWN. MINIMUM PULL-OUT FORCE OF TERMINAL WILL BE 6.5 LBS[2.9Kg]. (WHEN PULLED AS SHOWN).
- ④. TO REMOVE TERMINAL—PUSH TERMINAL FORWARD. LIFT LATCH WITH HANDTOOL. AS SHOWN IN FIG. #2 & 3. DAMAGE TO LATCH CAN OCCUR IF LIFTED MORE THAN 25° ANGLE TO TOP OF HOUSING.
- ⑤. MAX. WIRE CRIMP AND WIRE STRANDS ARE SHOWN IN FIGURE #4. IF THIS IS EXCEEDED, LATCHING WILL NOT BE SATISFACTORY SEE MAXI PV™ TERMINAL SPECIFICATION TA-213 FOR CORRECT CRIMP HEIGHT FOR EACH DIFFERENT WIRE SIZE.
6. THIS HOUSING IS INTENDED FOR USE MAXI PV™ TERMINAL WITH 18-32 GAGE WIRE MEETING SPECIFICATION SHOWN IN FIGURE # 4.
7. PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
8. THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO MANUFACTURING SOLDER PROCESSES.




FIG 1




FIG 2




FIG 3

mat'l. code SEE NOTE 1				surface ☒		tolerance		projection 		product family PV HOUSINGS			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
N				angles	linear	XX*.01/X*.3		INCH/MM	MAXI LATCH HOUSING DR .125 [3.18] X .125 [3.18]CC				
						XXX*.005/XX*.13							
						XXXX*.0020/XXX*.051							
				0°±2°		XXXX*.0020/XXX*.051		scale 2:1					
				dr	L. SANDERS	1995-03-31			dwg no		sheet 2 of 3	size	
				engr	L. FYE	1995-03-31			65410		A3		
				chr	T. BREWBAKER	1995-03-31							
				appd	L. FYE	1995-03-31							
sheet index		revision sheet								type Product Customer Drawing			



FCJconnect.com

Copyright FCJ

PRODUCT NUMBER	NO OF POS	DIM J MAX	DIM K	STAMPING NOTES
65410-004LF	2 X 2	.267/6.78	.125/3.18	DON'T STAMP
65410-006LF	2 X 3	.392/9.96	.250/6.35	DON'T STAMP
65410-008LF	2 X 4	.517/13.13	.375/9.53	LOGO
65410-010LF	2 X 5	.642/16.31	.500/12.70	LOGO
65410-012LF	2 X 6	.767/19.48	.625/15.88	LOGO
65410-014LF	2 X 7	.892/22.68	.750/19.65	LOGO
65410-016LF	2 X 8	1.017/25.83	.875/22.23	LOGO & PART NO.
65410-018LF	2 X 9	1.142/29.01	1.000/25.40	LOGO & PART NO.
65410-020LF	2 X 10	1.267/32.18	1.125/28.58	LOGO & PART NO.
65410-022LF	2 X 11	1.392/35.36	1.250/31.75	LOGO & PART NO.
65410-024LF	2 X 12	1.517/38.53	1.375/34.93	LOGO & PART NO.
65410-026LF	2 X 13	1.642/41.71	1.500/38.10	LOGO & PART NO.
65410-028LF	2 X 14	1.767/44.88	1.625/41.38	LOGO & PART NO.
65410-030LF	2 X 15	1.892/48.07	1.750/45.05	LOGO & PART NO.
65410-032LF	2 X 16	2.017/51.23	1.875/47.63	LOGO & PART NO.
65410-034LF	2 X 17	2.142/54.41	2.000/50.80	LOGO & PART NO.
65410-036LF	2 X 18	2.267/57.58	2.125/53.98	LOGO & PART NO.
65410-038LF	2 X 19	2.392/60.76	2.250/57.15	LOGO & PART NO.
65410-040LF	2 X 20	2.517/63.93	2.375/60.33	LOGO & PART NO.
65410-042LF	2 X 21	2.642/67.11	2.500/63.50	LOGO & PART NO.
65410-044LF	2 X 22	2.767/70.28	2.625/66.68	LOGO & PART NO.
65410-046LF	2 X 23	2.892/73.46	2.750/69.85	LOGO & PART NO.
65410-048LF	2 X 24	3.017/76.63	2.875/73.03	LOGO & PART NO.
65410-050LF	2 X 25	3.143/79.81	3.000/76.20	LOGO & PART NO.
65410-052LF	2 X 26	3.267/82.98	3.125/79.38	LOGO & PART NO.
65410-054LF	2 X 27	3.392/86.16	3.250/82.55	LOGO & PART NO.
65410-056LF	2 X 28	3.517/89.33	3.375/85.73	LOGO & PART NO.
65410-057LF	DISCONTINUED			

mat'l. code SEE NOTE 1				surface ✓		tolerance tolerances unless otherwise specified		projection INCH/MM		product family PV HOUSINGS	
ltr	ecn no	dr	date	angles		linear		scale 1:1		title MAXI LATCH HOUSING DR .125 [3.18] X .125 [3.18]CC	
N										dwg no 65410	
										sheet 3 of 3	
										size A3	
										type Product Customer Drawing	
sheet	revision										
index	sheet										