





PRODUCT NO.
SEE TABLE



mat'l. code				surface	tolerance	projection	product family
—				ISO 1502	ISO 406 ISO 1101	INCH/MM	CARD CONN
lir	ecm no	dr	date	tolerances unless otherwise specified		INCH/MM	title
J	V61635	MDF	11/21/96	angles	linear		
K	V70999	LSS	12/11/97			scale 4:1	GUIDE PIN CARD CONNECTOR
L	V02386	AZ	10/05/00	0°±2°			dwg no
M	M05-0181	MHT	8/22/05	dr	L. SANDERS	12/11/97	sheet 1 of 6
N	M06-0117	AEA	6/26/06	engr	H. SUNDY	12/11/97	size
P	M07-0137	MHT	2/26/07	chr	H. SUNDY	12/11/97	A3
R	M09-0093	MHT	6/22/09	appd	H. SUNDY	12/11/97	type
sheet	revision	R	R	R	R	R	Product Customer Drawing
index	sheet	1	2	3	4	5	



1. HOUSING MATERIAL.
FILLED HIGH TEMPERATURE NYLON
NOTES. PER UL 94V-0
COLOR. BLACK
2. TERMINAL MATERIAL.
BODY. BRASS. .010/.25 THICK.
SPRING. BE-CU. HEAT TREATED
BODY PLATING.
40 MICROINCH / 1.02 MICRON GOLD
OVER 50 MICROINCH / 1.27 MICRON NICKEL IN CONTACT AREA.
SOLDER TAIL. 100u"/2.54u" PURE TIN (NOTE 8) OVER 50u"/1.27 Ni.
SPRING PLATING. GOLD FLASH
3. APPLICATION INFORMATION.
A. RECOMMENDED MOUNTING HOLE PATTERN IS SHOWN IN FIG. 1.
B. ALL MATING PINS TO BE .025/.64 SQUARE ON TRUE CENTER OF GIVEN TERMINAL SPACINGS WITHIN .015/.38 DIA.
C. SUGGESTED MATING PIN LENGTH .350±.020/8.89±.51.
- ④ TERMINAL MATERIAL:
BODY. BRASS. .010/.25 THICK.
SPRING. BE-CU. HEAT TREATED
BODY PLATING.
40 MICROINCH / 1.02 MICRON GOLD
OVER 50 MICROINCH / 1.27 MICRON NICKEL IN CONTACT AREA.
SOLDER TAIL: GOLD FLASH OVER 50u"/1.27u Ni.1.27 Ni.
SPRING PLATING. GOLD FLASH
- ⑤ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑥ THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
7. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.
- ⑧ THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WISKER GROWTH IN ALL INTERCONNECT REQUIREMENTS

mat'l. code		surface	tolerance	projection	product family
-		ISO 1302	ISO 406		CARD CONN
ISO 1101		ISO 1101	ISO 1101		
ltr	ecr no	dr	date	title	
R				GUIDE PIN	
				CARD CONNECTOR	
				dwg no	sheet 2 of 6 size
				67477	A3
				type Product Customer Drawing	
sheet	revision				
index	sheet				

FCI
FConnect

Copyright FCI

1		2		3		4		5		6	
PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION						
67477-001	2X1	.00/.0	.358/9.09	NO	NOTE 6,7	UNASSIGNED					
-002	2X2	.10/2.5	.458/11.63	NO		OBSOLETE					
-003	2X3	.20/5.0	.558/14.17	NO		OBSOLETE					
-004	2X4	.30/7.6	.658/16.71	NO		OBSOLETE					
-005	2X5	.40/10.1	.758/19.25								
-006	2X6	.50/12.7	.858/21.79								
-007	2X7	.60/15.2	.958/24.33								
-008	2X8	.70/17.7	1.058/26.87								
-009	2X9	.80/20.3	1.158/29.41								
-010	2X10	.90/22.8	1.258/31.95								
-011	2X11	1.00/25.4	1.358/34.49								
-012	2X12	1.10/27.9	1.458/37.03								
-013	2X13	1.20/30.4	1.558/39.57								
-014	2X14	1.30/33.0	1.658/42.11								
-015	2X15	1.40/35.5	1.758/44.65								
-016	2X16	1.50/38.1	1.858/47.19								
-017	2X17	1.60/40.6	1.958/49.73								
-018	2X18	1.70/43.1	2.058/52.27								
-019	2X19	1.80/45.7	2.158/54.81								
-020	2X20	1.90/48.2	2.258/57.35								
-021	2X21	2.00/50.8	2.358/59.89								
-022	2X22	2.10/53.3	2.458/62.43								
-023	2X23	2.20/55.8	2.558/64.97								
-024	2X24	2.30/58.4	2.658/67.51								
-025	2X25	2.40/60.9	2.758/70.05								
-026	2X26	2.50/63.5	2.858/72.59								
-027	2X27	2.60/66.0	2.958/75.13								
-028	2X28	2.70/68.5	3.058/77.67								
-029	2X29	2.80/71.1	3.158/80.21								
-030	2X30	2.90/73.6	3.258/82.75								
-031	2X31	3.00/76.2	3.358/85.29								
-032	2X32	3.10/78.7	3.458/87.83								
-033	2X33	3.20/81.2	3.558/90.37								
-034	2X34	3.30/83.8	3.658/92.91								
-035	2X35	3.40/86.3	3.758/95.45								
-036	2X36	3.50/88.9	3.858/97.99								
-037	2X37	3.60/91.4	3.958/100.53								
-038	2X38	3.70/93.9	4.058/103.07								
-039	2X39	3.80/96.5	4.158/105.61								
67477-040	2X40	3.90/99.0	4.258/108.15	NO	NOTE 6,7						

mat'l. code				surface		tolerance		projection		product family	
-				ISO 1302		ISO 406 ISO 1101				CARD CONN	
lir		ecn no		dr		date		tolerances unless otherwise specified		title	
R								.xxx±.01/.3		INCH/MM	
								.xxx ±.005/.13		scale 4:1	
								.xxxx ±.0020/.05		dwg no	
								dr L. SANDERS 12/11/97		sheet 3 of 6 size	
								enr H. SUNDY 12/11/97		67477 A3	
								chr H. SUNDY 12/11/97		type Product Customer Drawing	
								appd H. SUNDY 12/11/97			
sheet		revision									
index		sheet									

form: A3

1

2

3

4

5

6

PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION
67477-041	2X41	4.00/101.6	4.358/110.69	NO	NOTE 6,7
-042	2X42	4.10/104.1	4.458/113.23		
-043	2X43	4.20/106.6	4.558/115.77		
-044	2X44	4.30/109.2	4.658/118.31		
-045	2X45	4.40/111.7	4.758/120.85		
-046	2X46	4.50/114.3	4.858/123.39		
-047	2X47	4.60/116.8	4.958/125.93		
-048	2X48	4.70/119.3	5.058/128.47		
-049	2X49	4.80/121.9	5.158/131.01		
-050	2X50	4.90/124.4	5.258/133.55		
-051	2X51	5.00/127.0	5.358/136.09		
-052	2X52	5.10/129.5	5.458/138.63		
-053	2X53	5.20/132.0	5.558/141.17		
-054	2X54	5.30/134.6	5.658/143.71		
-055	2X55	5.40/137.1	5.758/146.25		
-056	2X56	5.50/139.7	5.858/148.79		
-057	2X57	5.60/142.2	5.958/151.33		
-058	2X58	5.70/144.7	6.058/153.87		
-059	2X59	5.80/147.3	6.158/156.41		
-060	2X60	5.90/149.8	6.258/158.95		
-061	2X61	6.00/152.4	6.358/161.49		
-062	2X62	6.10/154.9	6.458/164.03		
-063	2X63	6.20/157.4	6.558/166.57		
-064	2X64	6.30/160.0	6.658/169.11		
67477-065	2X65	6.40/162.5	6.758/171.65	NO	
-066 THRU					NOTE 6,7
-100					

OBSOLETE

mat'l. code				surface ISO 1302		tolerance ISO 406 ISO 1101		projection 		product family CARD CONN	
ltr	ecr no	dr	date	tolerances unless otherwise specified							
R				angles	linear	.XX±.01/.3		INCH/MM 		title GUIDE PIN CARD CONNECTOR dwg no 67477 sheet 4 of 6 size A3 type Product Customer Drawing	
						.xxx ±.005/.13					
				0'±2'		.xxx ±.0020/.05		scale 4:1			
				dr	L. SANDERS	12/11/97					
				engr	H. SUNDY	12/11/97					
				chr	H. SUNDY	12/11/97					
				appd	H. SUNDY	12/11/97					
sheet index	revision sheet										

PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION
67477-501	2X1	.00/.0	.358/9.09	YES	NOTE 6,7
-502	2X2	.10/2.5	.458/11.63	YES	UNASSIGNED
-503	2X3	.20/5.0	.558/14.17	YES	OBSOLETE
-504	2X4	.30/7.6	.658/16.71	YES	OBSOLETE
-505	2X5	.40/10.1	.758/19.25		OBSOLETE
-506	2X6	.50/12.7	.858/21.79		
-507	2X7	.60/15.2	.958/24.33		
-508	2X8	.70/17.7	1.058/26.87		
-509	2X9	.80/20.3	1.158/29.41		
-510	2X10	.90/22.8	1.258/31.95		
-511	2X11	1.00/25.4	1.358/34.49		
-512	2X12	1.10/27.9	1.458/37.03		
-513	2X13	1.20/30.4	1.558/39.57		
-514	2X14	1.30/33.0	1.658/42.11		
-515	2X15	1.40/35.5	1.758/44.65		
-516	2X16	1.50/38.1	1.858/47.19		
-517	2X17	1.60/40.6	1.958/49.73		
-518	2X18	1.70/43.1	2.058/52.27		
-519	2X19	1.80/45.7	2.158/54.81		
-520	2X20	1.90/48.2	2.258/57.35		
-521	2X21	2.00/50.8	2.358/59.89		
-522	2X22	2.10/53.3	2.458/62.43		
-523	2X23	2.20/55.8	2.558/64.97		
-524	2X24	2.30/58.4	2.658/67.51		
-525	2X25	2.40/60.9	2.758/70.05		
-526	2X26	2.50/63.5	2.858/72.59		
-527	2X27	2.60/66.0	2.958/75.13		
-528	2X28	2.70/68.5	3.058/77.67		
-529	2X29	2.80/71.1	3.158/80.21		
-530	2X30	2.90/73.6	3.258/82.75		
-531	2X31	3.00/76.2	3.358/85.29		
-532	2X32	3.10/78.7	3.458/87.83		
-533	2X33	3.20/81.2	3.558/90.37		
-534	2X34	3.30/83.8	3.658/92.91		
-535	2X35	3.40/86.3	3.758/95.45		
-536	2X36	3.50/88.9	3.858/97.99		
-537	2X37	3.60/91.4	3.958/100.53		
-538	2X38	3.70/93.9	4.058/103.07		
-539	2X39	3.80/96.5	4.158/105.61		
67477-540	2X40	3.90/99.0	4.258/108.15	YES	NOTE 6,7

mat'l. code		surface ISO 1902 ☒ ISO 406 ISO 1901		tolerance ISO 406 ISO 1901		projection 		product family CARD CONN	
ltr	ecr no	dr	date	tolerances unless otherwise specified				title	
R				angles	linear	.XXX ±.01/.3 .XXX ±.005/.13 O' ±2'		GUIDE PIN CARD CONNECTOR	
						scale 4:1		dwg no	
				dr	L. SANDERS	12/11/97			sheet 5 of 6
				engr	H. SUNDY	12/11/97			size
				chr	H. SUNDY	12/11/97			A3
				appd	H. SUNDY	12/11/97			
sheet	revision							type Product Customer Drawing	
index	sheet								

PRODUCT NO.	NO. OF POS.	DIM. A	DIM. B	INSULATION PLUG	LEAD FREE OPTION
67477-541	2X41	4.00/101.6	4.358/110.69	YES	NOTE 6,7
-542	2X42	4.10/104.1	4.458/113.23		
-543	2X43	4.20/106.6	4.558/115.77		
-544	2X44	4.30/109.2	4.658/118.31		
-545	2X45	4.40/111.7	4.758/120.85		
-546	2X46	4.50/114.3	4.858/123.39		
-547	2X47	4.60/116.8	4.958/125.93		
-548	2X48	4.70/119.3	5.058/128.47		
-549	2X49	4.80/121.9	5.158/131.01		
-550	2X50	4.90/124.4	5.258/133.55		
-551	2X51	5.00/127.0	5.358/136.09		
-552	2X52	5.10/129.5	5.458/138.63		
-553	2X53	5.20/132.0	5.558/141.17		
-554	2X54	5.30/134.6	5.658/143.71		
-555	2X55	5.40/137.1	5.758/146.25		
-556	2X56	5.50/139.7	5.858/148.79		
-557	2X57	5.60/142.2	5.958/151.33		
-558	2X58	5.70/144.7	6.058/153.87		
-559	2X59	5.80/147.3	6.158/156.41		
-560	2X60	5.90/149.8	6.258/158.95		
-561	2X61	6.00/152.4	6.358/161.49		
-562	2X62	6.10/154.9	6.458/164.03		
-563	2X63	6.20/157.4	6.558/166.57		
-564	2X64	6.30/160.0	6.658/169.11		
67477-565	2X65	6.40/162.5	6.758/171.65	YES	
-566 THRU					NOTE 6,7
-600					

OBSOLETE



FCI
FCIconnect.com

Copyright FCI

mat'l. code		surface ISO 1502		tolerance ISO 406 ISO 1101	projection	product family CARD CONN		
ltr	ecr no	dr	date		title			
R					GUIDE PIN CARD CONNECTOR			
		angles	linear	.XX±.01/.3 .XXX ±.005/.13	INCH/MM			
		0'±2"		XXXX ±.0020/.05	scale 4:1			
		dr	L. SANDERS 12/11/97		FCI			
		engr	H. SUNDY 12/11/97				dwg no	sheet 6 of 6
		chr	H. SUNDY 12/11/97				67477	A3
		appd	H. SUNDY 12/11/97		type		Product Customer Drawing	
sheet index	revision	sheet						