

1			2			3			4			5			6		
PRODUCT No. NOTE 9,10	No. OF POS.	"A" SPACES	DIM B	DIM C	DIM D	DIM E	DIM F	PLATING CODE	SEE NOTE 2 (1)								
68645-001	6	2	.200/5.080	.500/12.700	.150/3.810	_____	.130/3.300										
-002	8	3	.300/7.620	.600/15.240	.150/3.810	_____	.130/3.300										
-003	10	4	.400/10.160	.700/17.780	.250/6.350	_____	.130/3.300										
-004	12	5	.500/12.700	.800/20.320	.250/6.350	_____	.130/3.300										
-005	14	6	.600/15.240	.900/22.860	.350/8.890	_____	.130/3.300										
-006	16	7	.700/17.780	1.000/25.400	.350/8.890	_____	.130/3.300										
-007	18	8	.800/20.320	1.100/27.940	.450/11.430	_____	.130/3.300										
-008	20	9	.900/22.860	1.200/30.480	.150/3.810	.850/21.590	.130/3.300										
-009	22	10	1.000/25.400	1.300/33.020	.150/3.810	.950/24.130	.130/3.300										
-010	24	11	1.100/27.940	1.400/35.560	.150/3.810	1.050/26.670	.130/3.300										
-011	26	12	1.200/30.480	1.500/38.100	.150/3.810	1.150/29.210	.130/3.300										
-012	28	13	1.300/33.020	1.600/40.640	.150/3.810	1.250/31.750	.130/3.300										
-013	30	14	1.400/35.560	1.700/43.180	.150/3.810	1.350/34.290	.130/3.300										
-014	32	15	1.500/38.100	1.800/45.720	.150/3.810	1.450/36.830	.130/3.300										
-015	34	16	1.600/40.640	1.900/48.260	.150/3.810	1.550/39.370	.130/3.300										
-016	36	17	1.700/43.180	2.000/50.800	.150/3.810	1.650/41.910	.130/3.300										
-017	38	18	1.800/45.720	2.100/53.340	.150/3.810	1.750/44.450	.130/3.300										
-018	40	19	1.900/48.260	2.200/55.880	.150/3.810	1.850/46.990	.130/3.300										
-019	42	20	2.000/50.800	2.300/58.420	.150/3.810	1.950/49.530	.130/3.300										
-020	44	21	2.100/53.340	2.400/60.960	.150/3.810	2.050/52.070	.130/3.300										
-021	46	22	2.200/55.880	2.500/63.500	.150/3.810	2.150/54.610	.130/3.300										
-022	48	23	2.300/58.420	2.600/66.040	.150/3.810	2.250/57.150	.130/3.300										
-023	50	24	2.400/60.960	2.700/68.580	.150/3.810	2.350/59.690	.130/3.300										
-024	52	25	2.500/63.500	2.800/71.120	.150/3.810	2.450/62.230	.130/3.300										
-025	54	26	2.600/66.040	2.900/73.660	.150/3.810	2.550/64.770	.130/3.300										
-026	56	27	2.700/68.580	3.000/76.200	.150/3.810	2.650/67.310	.130/3.300										
-027	58	28	2.800/71.120	3.100/78.740	.150/3.810	2.750/69.850	.130/3.300										
-028	60	29	2.900/73.660	3.200/81.280	.150/3.810	2.850/72.390	.130/3.300										
-029	62	30	3.000/76.200	3.300/83.820	.150/3.810	2.950/74.930	.130/3.300										
68645-030	64	31	3.100/78.740	3.400/86.360	.150/3.810	3.050/77.470	.130/3.300										

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS							
ltr		ecn no		dr		date		tolerances unless otherwise specified		linear		INCH/MM		title			
E								angles		XX±.01/XX±0.3		scale 8:1		RIGHT ANGLE HEADER FOR			
								0°±2°		.XXX±.005/.XXX±0.13				FLAT CABLE RECEPTACLE			
										.XXX±.0020/.XXX±0.051				dwg no			
								dr		COPENHEAVED		7/10/84		sheet3 of 4 size			
								enr		P.M. SMITH		4/10/85		68645			
								chr		-		-		A3			
								appd		CA WILLIAMS		4/12/85		type Product Customer Drawing			
sheet index		revision sheet															

