






mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
ltr	ecn no	dr	date	linear	.XX ±.01/X ±.3	projection	title	product family	code
A	V81283	EPK	10/19/98		.XXX ±.005/XX ±.13		RIGHT ANGLE 2 ROW GUIDE PIN HEADER	HEADERS	-
B	V90145	DLH	4/7/99		.XXX ±.0020/XXX ±.051				
				angles	° ±2°	INCH/MM scale 2:1	A	69922	sheet 1 of 3
				dr	E KROPIEWICKI 10/19/98				
				enr	H. SUNDY 10/19/98				
				chr	H. SUNDY 10/19/98				
				appd	H. SUNDY 10/19/98	2:1	A	69922	sheet 1 of 3
sheet index	revision	B	B	A					
	sheet	1	2	3					



NOTES:

- THIS LENGTH OF PIN TO BE FREE OF NICKS, TOOL MARKS, AND PLASTIC SLIVERS.
- PIN RETENTION TO BE 3.00 Lbs/1.36 Kgs MIN PER PIN IN EITHER DIRECTION.
- TERMINAL PLATING : SEE PRODUCT TABLE
- MOLDING MAT'L : MIN 20% GLASS FILLED POLYESTER PER UL-94-V0, COLOR: BLACK.
- DIM D =
(NO. OF COLUMNS - 1) TIMES .100 [ENGLISH].
(NO. OF COLUMNS - 1) TIMES 2.54 [METRIC].
- XXX REPRESENTS NO. OF COLUMNS.
(i.e. 2x5 PART IS -005).
-001 THRU -004 ARE NOT AVAILABLE.
-005 THRU -100 ARE AVAILABLE.
- TERMINAL MATERIAL - 3/4 HARD PHOS BRONZE ALLOY UNS C51000.
- "R" SUFFIX ON PART DASH NUMBER INDICATES RETENTION PINS (KINKED).
ON PARTS UP TO 2 X 14, RETENTIVE PINS LOCATED ON THE CENTER TWO COLUMNS. ON PARTS 2 X 15 AND ABOVE, RETENTIVE PINS LOCATED ONE COLUMN FROM THE END. (2 PAIR OF PINS ON EACH END)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	BERG ELECTRONICS		
ltr	ecr no	dr	date	linear	angles				
B				.XX ±.01/.3	0° ±2°	projection	title RIGHT ANGLE 2 ROW GUIDE PIN HEADER		
				.XXX ±.005/.13					
				.XXX ±.0020/.050			product family HEADERS size dwg no 69922		code
						scale 2:1			sheet 2 of
				dr E KROPIEWNICK 10/19/98			cage code 22526		
				engr H. SUNDY 10/19/98					
				chr H. SUNDY 10/19/98					
				appd H. SUNDY 10/19/98					
sheet index	revision sheet								



PRODUCT NO NOTE 6	SIZE NOTE 6	DIM D	DIM F	DIM E	OVERALL LENGTH DIM L	P L A T I N G
69922-XXX	2 x XXX	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	15u"/.38u GXT™ OVER 50u"/1.27u Ni
69923-XXX						30u"/.76u GXT™ OVER 50u"/1.27u Ni
69924-XXX						15u"/.38u MIN Au OVER 50u"/1.27 MIN Ni
69925-XXX						30u"/.76u MIN Au OVER 50u"/1.27 MIN Ni
69926-XXX						DUPLEX 30u"/.76u Au & 100u"/2.54u MIN 60/40 SnPb OVER 50u"/1.27 Ni
69927-XXX	2 x XXX	NOTE 5	.37/9.4 + DIM D	.40/10.2 + DIM D	.48/12.2 + DIM D	120u"/3.05u 93/7 SnPb OVER 50u"/1.27u Ni

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	BERG ELECTRONICS			
ltr	ecn no	dr	date	linear	.xx ±.01/.x ±.3	projection 	title RIGHT ANGLE 2 ROW GUIDE PIN HEADER			
A					.xxx ±.005/.xx ±.13					
					.xxx ±.0020/.xxx ±.051					
				angles	0° ±2°		product family HEADERS size dwg no A 69922			
				dr	E KROPIEWNICKI 10/19/98					
				enr	H. SUNDY 10/19/98					
				chr	H. SUNDY 10/19/98	scale 1:1	code - sheet 3 of			
				appd	H. SUNDY 10/19/98					
sheet index	revision sheet									