




This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.





PRODUCT NUMBER
SEE TABLE



mat'l code				SEE NOTES				tolerances unless otherwise specified				CUSTOMER				FCI			
ltr	ecn no.	dr	date																
BY	V06-0498	DCH	2006-05-31																
CA	DG07-0487	Cenh	12/05/07																
CB	DG08-0188	TER	2008-11-25																
CC	DG08-0346	Cenh	2008-12-12																
CD	DG09-0256	TER	2009-08-19																
-	-	-	-																
BX	V05-1030	LP	11/18/05																
sheet index	revision sheet	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD	CD
		1	2	3	4	5	6	7	8	9	10	11							

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY (SIGNAL PRESS-FIT)		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.30
2	5.75	4.30
3	6.50	4.30
4	7.25	4.30
5	5.00	13.60
6	5.75	13.60
7	6.50	13.60
8	7.25	13.60
19	8.00	4.30
20	8.00	13.60

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com			
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3	COPY			title METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT		
CD					0. XX $\pm$ 0.13	projection					
					.XXX $\pm$.051						
				angles	0° $\pm$ 2°					 MM scale 1:1	product family METRAL code 213 sheet 2
				dr	T.BRUNGARD	01/27/00					
				enrg	M.STRAWSE	01/27/00					
				chr	M.STRAWSE	01/27/00					
				appd	M.STRAWSE	02/29/00	size A	dwg no 70298			
sheet index	revision sheet										

cage code 22526

Pro/E

PDM: Rev:CD

STATUS: Released

Printed: Sep 16, 2009



PRODUCT NUMBER	DESCRIPTION	PLATING IN PRESS FIT TAIL AREA	PERFORMANCE LEVEL OF PLATING IN CONTACT AREA
70298-AYY	STANDARD	Au FLASH	TELCORDIA CO (SEE NOTE 9)
70298-NIYY	STANDARD	TIN-LEAD	TELCORDIA CO (NXT)
70298--N5YY	STANDARD	TIN-LEAD	TECORDIA UE (NXT)
70298--IYY	STANDARD	TIN-LEAD	TELCORDIA CO
70298--2YY	STANDARD	TIN-LEAD	TELECOM CLASS
70298-3YY	STANDARD	TIN-LEAD	IEC CLASS I
70298-5YY	STANDARD	TIN-LEAD	TELCORDIA UE
70298-AYYLF	LEAD FREE	Au FLASH	TELCORDIA CO SEE NOTES 10 AND 11
70298-NIYYLF	LEAD FREE	TIN	TELCORDIA CO (NXT), IEC CLASS I, SEE NOTES 9 AND 10
70298-N5YYLF	LEAD FREE	TIN	TECORDIA UE (NXT) SEE NOTES 9 AND 10
70298-IYYLF	LEAD FREE	TIN	TELCORDIA CO, IEC CLASS I, SEE NOTES 9 AND 10
70298-2YYLF	LEAD FREE	TIN	TELECOM CLASS, SEE NOTES 9 AND 10
70298-5YYLF	LEAD FREE	TIN	TELCORDIA UE, SEE NOTES 9 AND 10

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON: PRESS-FIT TAIL AREA SEE PRODUCT.
NUMBER TABLE, PLATING ON CONTACT AREA CONFORMS
TO PERFORMANCE LEVEL SHOWN IN TABLE ON SHEET3.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
- PRODUCT SPECIFICATION:
GS-12-180
APPLICATION SPECIFICATION:
BUS-20-073
- AFTER INSERTION INTO CIRCUIT BOARD WITH QUALIFIED TOOL.
- A PLATING HAS Au FLASH IN PRESS FIT AREA (LEAD FREE).
- THE PRODUCTS WHERE THE PART NUMBERS ENDS IN
LF MEET THE EUROPEAN UNION DIRECTIVE AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-12-008.
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS
CONTAINING 70298-NI--- OR 70298-N5--- WILL WITHSTAND
EXPOSURE TO 260 DEGREES C FOR 60 SECONDS IN A
CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN
PART NUMBERS 70298-NI--- AND 70298-N5--- WILL
NOT WITHSTAND REFLOW AND THE Au CONTACT SURFACE
OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140
DEGREES C FOR NO LONGER THAN 15 SECONDS IN A WAVE
SOLDER APPLICATION.

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT
CD					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°	MM	scale	product family	METRAL
				dr	T.BRUNGARD 01/27/00				
				enrg	M.STRAWSE 01/27/00				
				chr	M.STRAWSE 01/27/00	A	size	dwg no	213
				appd	M.STRAWSE 02/29/00				
sheet	revision								
index	sheet								

cage code 22526

Pro/E

PDM: Rev:CD

STATUS: Released

Printed: Sep 16, 2009



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X01 AND 70298-X01LF	D	1	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X02 AND 70298-X02LF	D	-	1	1	1	-	1	-	1	-	1
	C	1	-	1	-	1	-	1	-	1	-
	B	-	1	1	1	-	1	-	1	-	1
	A	3	-	3	-	1	-	1	-	1	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X03 AND 70298-X03LF	D	2	2	2	2	2	1	1	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	3	3	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X04 AND 70298-X04LF	D	-	-	-	-	-	-	-	-	-	-
	C	1	1	1	1	1	1	2	1	1	1
	B	1	1	1	1	1	1	2	1	1	1
	A	1	1	1	1	1	1	2	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X05 AND 70298-X05LF	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	1	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X06 AND 70298-X06LF	D	1	2	2	2	2	1	1	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X07 AND 70298-X07LF	D	2	2	2	2	2	2	2	4	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X08 AND 70298-X08LF	D	2	2	2	2	2	2	2	2	1	2
	C	2	2	2	2	2	2	2	2	1	2
	B	2	2	2	2	2	2	2	2	1	2
	A	2	2	2	2	2	2	2	2	1	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X09 AND 70298-X09LF	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X10 AND 70298-X10LF	D	2	2	2	2	2	2	2	4	2	2
	C	2	2	2	2	2	2	2	4	2	2
	B	2	2	2	2	2	2	2	4	2	2
	A	2	2	2	2	2	2	2	4	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X11 AND 70298-X11LF	D	4	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X12 AND 70298-X12LF	D	1	1	1	1	1	4	1	4	3	1
	C	1	1	1	4	1	1	1	4	3	1
	B	1	4	1	1	1	1	1	4	3	1
	A	1	1	1	1	1	4	1	4	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X13 AND 70298-X13LF	D	1	4	1	1	1	1	4	1	1	1
	C	1	1	1	1	4	1	1	1	1	1
	B	1	1	4	1	1	1	1	4	1	1
	A	1	1	1	1	1	4	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X14 AND 70298-X14LF	D	1	1	1	1	1	3	3	1	3	1
	C	1	1	1	1	1	3	3	1	3	1
	B	1	1	1	1	1	1	1	1	1	1
	A	4	4	4	4	4	4	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X15 AND 70298-X15LF	D	1	1	1	1	1	4	1	4	3	1
	C	1	1	1	4	1	1	1	4	3	1
	B	1	4	1	1	1	1	1	4	3	1
	A	1	1	1	1	1	4	1	4	3	3

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	title	www.fciconnect.com
CD					0.XX ±0.13				
					.XXX ±.051				
				angles	0° ±2°				
				dr	T.BRUNGARD 01/27/00				
				enrg	M.STRAWSE 01/27/00				
					chr	M.STRAWSE 01/27/00			
					appd	M.STRAWSE 02/29/00			
sheet index		revision sheet							



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X16 AND 70298-X16LF	D	1	4	1	1	1	1	4	1	1	1
	C	1	1	1	1	4	1	1	1	1	4
	B	1	1	4	1	1	1	4	1	1	1
	A	4	4	1	1	1	4	1	1	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X17 AND 70298-X17LF	D	4	4	3	2	2	2	2	2	2	2
	C	1	4	3	2	2	2	2	2	2	2
	B	4	3	3	2	2	2	2	2	2	2
	A	4	3	3	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X18 AND 70298-X18LF	D	19	3	3	3	3	3	7	7	7	7
	C	19	3	3	3	3	3	7	7	7	7
	B	19	3	3	3	3	3	7	7	7	7
	A	19	3	3	3	3	3	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X19 AND 70298-X19LF	D	2	2	2	2	2	2	-	-	-	2
	C	2	2	2	2	2	2	-	-	-	2
	B	2	2	2	2	2	2	-	-	-	2
	A	2	2	2	2	2	2	-	-	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X20 AND 70298-X20LF	D	-	2	-	2	-	2	-	2	-	2
	C	2	-	2	-	2	-	2	-	2	-
	B	-	2	-	2	-	2	-	2	-	2
	A	2	-	2	-	2	-	2	-	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X21 AND 70298-X21LF	D	1	1	1	1	1	1	1	1	1	19
	C	1	1	1	1	1	1	1	1	1	19
	B	1	1	1	1	1	1	1	1	1	19
	A	1	1	4	1	1	1	1	1	1	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X22 AND 70298-X22LF	D	1	1	1	1	1	1	1	1	3	1
	C	1	1	1	1	1	1	1	1	3	1
	B	1	1	1	1	1	1	1	1	3	1
	A	1	1	1	1	1	1	1	1	3	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X23 AND 70298-X23LF	D	2	3	2	2	2	2	1	1	1	3
	C	2	3	2	2	2	2	1	1	1	3
	B	2	3	2	2	2	2	1	1	1	3
	A	2	3	2	2	2	2	1	1	1	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X24 AND 70298-X24LF	D	1	1	1	1	1	1	1	1	2	2
	C	2	1	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X25 AND 70298-X25LF	D	-	2	-	2	-	2	-	2	-	2
	C	-	-	-	-	-	-	-	-	-	-
	B	-	-	-	-	-	-	-	-	-	-
	A	-	2	-	2	-	2	-	2	-	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X26 AND 70298-X26LF	D	-	6	-	6	-	6	-	6	-	6
	C	-	-	-	-	-	-	-	-	-	-
	B	-	-	-	-	-	-	-	-	-	-
	A	-	6	-	6	-	6	-	6	-	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X27 AND 70298-X27LF	D	3	3	-	3	3	-	3	3	-	3
	C	3	3	-	3	3	-	3	3	-	3
	B	-	-	-	-	-	-	-	-	-	-
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X28 AND 70298-X28LF	D	1	2	2	2	2	3	1	3	2	2
	C	1	2	2	2	2	3	1	3	2	2
	B	1	2	2	2	2	3	1	3	2	2
	A	1	2	2	2	2	3	1	3	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X29 AND 70298-X29LF	D	2	3	2	2	2	3	2	2	2	3
	C	2	3	2	2	2	3	2	2	2	3
	B	2	3	2	2	2	3	2	2	2	3
	A	2	3	2	2	2	3	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X30 AND 70298-X30LF	D	2	2	3	2	3	2	2	2	2	3
	C	2	2	3	2	3	2	2	2	2	3
	B	2	2	3	2	3	2	2	2	2	3
	A	2	2	3	2	3	2	2	2	2	3

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fciconnect.com	
CD				linear	0.XX ±0.13	projection		title	
				angles	.XXX ±.051			METRAL SIGNAL HEADER	
				dr	T.BRUNGARD 01/27/00			2 MOD, 4 ROW PRESS-FIT	
				enrg	M.STRAWSE 01/27/00	product family		METRAL	
				chr	M.STRAWSE 01/27/00	size		dwg no	
				appd	M.STRAWSE 02/29/00	A		70298	
sheet index	revision sheet					scale		213	
						1:1		sheet 5	
						cage code		22526	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X31 AND 70298-X31LF	D	2	2	3	2	3	3	2	2	2	3
	C	2	2	3	2	3	3	2	2	2	3
	B	2	2	3	2	3	3	2	2	2	3
	A	2	2	3	2	3	3	2	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X32 AND 70298-X32LF	D	2	2	2	1	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X33 AND 70298-X33LF	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	4	4	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X34 AND 70298-X34LF	D	1	9	3	3	3	3	1	9	3	3
	C	1	9	3	3	3	3	1	9	3	3
	B	1	9	3	3	3	3	1	9	3	3
	A	1	9	3	3	3	3	1	9	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X35 AND 70298-X35LF	D	1	9	3	3	3	3	1	9	3	3
	C	1	9	3	3	3	3	1	9	3	3
	B	1	9	3	3	3	3	1	9	3	3
	A	1	9	3	3	3	3	1	9	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X36 AND 70298-X36LF	D	3	3	3	-	3	-	3	-	3	-
	C	3	3	3	-	3	-	3	-	3	-
	B	3	3	3	-	3	-	3	-	3	-
	A	3	3	3	-	3	-	3	-	3	-

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X37 AND 70298-X37LF	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	2	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X38 AND 70298-X38LF	D	2	3	3	3	3	3	3	3	3	3
	C	4	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X39 AND 70298-X39LF	D	7	7	7	7	7	7	7	7	7	7
	C	7	7	7	7	7	7	7	7	7	7
	B	7	7	7	7	7	7	7	7	7	7
	A	7	8	7	7	7	7	7	7	7	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X40 AND 70298-X40LF	D	3	3	3	3	3	3	3	3	3	3
	C	3	3	3	3	3	3	3	3	3	3
	B	3	3	3	3	3	3	3	3	3	3
	A	3	3	3	4	4	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X41 AND 70298-X41LF	D	2	1	1	1	1	1	1	1	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X42 AND 70298-X42LF	D	3	3	3	3	3	3	3	3	4	4
	C	3	3	3	3	3	3	3	3	4	4
	B	3	3	3	3	3	3	3	3	4	4
	A	3	3	3	3	3	3	3	3	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X43 AND 70298-X43LF	D	1	1	1	3	3	3	3	1	1	1
	C	1	1	1	3	3	3	3	1	1	1
	B	1	1	1	3	3	3	3	1	1	1
	A	1	1	1	3	3	3	3	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X44 AND 70298-X44LF	D	2	2	2	1	1	3	1	1	1	1
	C	2	2	2	1	1	3	1	1	1	1
	B	2	2	2	1	1	3	1	1	1	1
	A	2	2	2	1	1	3	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X45 AND 70298-X45LF	D	2	2	1	1	1	1	1	1	1	2
	C	2	2	1	1	1	1	1	1	1	2
	B	2	2	1	1	1	1	1	1	1	2
	A	2	2	1	1	1	1	1	1	1	2

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI www.fciconnect.com	
lfr	ecn no.	dr	date	linear	0.X ±0.3			projection		title METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT	
CD					0.XX ±0.13						
					.XXX ±.051						
				angles	0° ±2°				product family METRAL	code 213	
				dr	T.BRUNGARD 01/27/00						
				enrg	M.STRAWSE 01/27/00						
				chr	M.STRAWSE 01/27/00						
				appd	M.STRAWSE 02/29/00			size A	dwg no 70298	sheet 6	
sheet index	revision sheet										



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X46 AND 70298-X46LF	D	3	2	2	3	1	2	3	2	2	3
	C	3	2	2	3	1	2	3	2	2	3
	B	3	2	2	3	1	2	3	2	2	3
	A	3	2	2	3	1	2	3	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X47 AND 70298-X47LF	D	2	2	3	1	1	3	2	1	2	3
	C	2	2	3	1	1	3	2	1	2	3
	B	2	2	3	1	1	3	2	1	2	3
	A	2	2	3	1	1	3	2	1	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X48 AND 70298-X48LF	D	2	2	3	2	2	2	3	2	2	3
	C	2	2	3	2	2	2	3	2	2	3
	B	2	2	3	2	2	2	3	2	2	3
	A	2	2	3	2	2	2	3	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X49 AND 70298-X49LF	D	2	2	2	1	1	1	1	2	2	2
	C	2	2	2	1	1	1	1	2	2	2
	B	2	2	2	1	1	1	1	2	2	2
	A	2	2	2	1	1	1	1	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X50 AND 70298-X50LF	D	2	2	3	2	2	2	2	1	1	1
	C	2	2	3	2	2	2	2	1	1	1
	B	2	2	3	2	2	2	2	1	1	1
	A	2	2	3	2	2	2	2	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X51 AND 70298-X51LF	D	1	1	2	2	2	2	2	1	1	3
	C	1	1	2	2	2	2	2	1	1	3
	B	1	1	2	2	2	2	2	1	1	3
	A	1	1	2	2	2	2	2	1	1	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X52 AND 70298-X52LF	D	2	2	3	2	2	2	2	1	1	2
	C	2	2	3	2	2	2	2	1	1	2
	B	2	2	3	2	2	2	2	1	1	2
	A	2	2	3	2	2	2	2	1	1	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X53 AND 70298-X53LF	D	2	2	2	2	2	2	2	2	3	2
	C	2	2	2	2	2	2	2	2	3	2
	B	2	2	2	2	2	2	2	2	3	2
	A	2	2	2	2	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X54 AND 70298-X54LF	D	2	2	3	2	3	2	3	2	1	1
	C	2	2	3	2	3	2	3	2	1	1
	B	2	2	3	2	3	2	3	2	1	1
	A	2	2	3	2	3	2	3	2	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X55 AND 70298-X55LF	D	6	6	6	6	6	6	6	6	6	7
	C	6	6	6	6	6	6	6	6	6	7
	B	6	6	6	6	6	6	6	6	6	7
	A	6	6	6	6	6	6	6	6	6	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X56 AND 70298-X56LF	D	6	7	6	6	6	6	6	6	6	7
	C	6	7	6	6	6	6	6	6	6	7
	B	6	7	6	6	6	6	6	6	6	7
	A	6	7	6	6	6	6	6	6	6	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X57 AND 70298-X57LF	D	3	2	2	3	3	3	3	3	3	3
	C	3	2	2	3	3	3	3	3	3	3
	B	3	2	2	3	3	3	3	3	3	3
	A	3	2	2	3	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X58 AND 70298-X58LF	D	3	3	3	3	3	3	3	2	2	3
	C	3	3	3	3	3	3	3	2	2	3
	B	3	3	3	3	3	3	3	2	2	3
	A	3	3	3	3	3	3	3	2	2	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X59 AND 70298-X59LF	D	3	3	2	2	2	2	2	2	4	4
	C	3	3	2	2	2	2	2	2	4	4
	B	3	3	2	2	2	2	2	2	4	4
	A	3	3	2	2	2	2	2	2	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X60 AND 70298-X60LF	D	4	4	4	4	4	4	4	4	4	3
	C	4	4	4	4	4	4	4	4	4	3
	B	4	4	4	4	4	4	4	4	4	3
	A	4	4	4	4	4	4	4	4	4	3

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI			
lfr	ecn no.	dr	date	linear	0.X ±0.3	projection	COPY	www.fciconnect.com			
CD					0.XX ±0.13				title	METRAL SIGNAL HEADER	
					.XXX ±0.051					2 MOD, 4 ROW PRESS-FIT	
				angles	0° ±2°		MM	product family	METRAL		
				dr	T.BRUNGARD 01/27/00				size	dwg no	code
				engr	M.STRAWSE 01/27/00						
				chr	M.STRAWSE 01/27/00						
				appd	M.STRAWSE 02/29/00						
sheet index		revision sheet				scale		1:1	A		
								cage code			
								22526			



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X61 AND 70298-X61LF	D	8	3	4	3	3	4	3	3	3	3
	C	8	3	4	3	3	4	3	3	3	3
	B	8	3	4	3	3	4	3	3	3	3
	A	8	3	4	3	3	4	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X62 AND 70298-X62LF	D	1	1	1	1	1	1	1	1	1	1
	C	1	1	1	1	1	1	1	1	1	1
	B	1	1	1	1	1	1	1	1	1	1
	A	1	1	1	1	1	1	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X63 AND 70298-X63LF	D	1	1	1	1	1	1	1	1	3	2
	C	1	1	1	1	1	1	1	1	3	2
	B	1	1	1	1	1	1	1	1	3	2
	A	1	1	1	1	1	1	1	1	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X64 AND 70298-X64LF	D	20	7	8	8	7	7	6	6	6	6
	C	20	7	8	8	7	7	6	6	6	6
	B	20	7	8	8	7	7	6	6	6	6
	A	20	7	8	8	7	7	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X65 AND 70298-X65LF	D	20	8	7	6	6	6	6	6	6	6
	C	20	8	7	6	6	6	6	6	6	6
	B	20	8	7	6	6	6	6	6	6	6
	A	20	8	7	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X66 AND 70298-X66LF	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	1	1	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X67 AND 70298-X67LF	D	3	3	3	3	3	3	4	4	4	4
	C	3	3	3	3	3	3	4	4	4	4
	B	3	3	3	3	3	3	4	4	4	4
	A	3	3	3	3	3	3	4	4	4	4

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X68 AND 70298-X68LF	D	4	4	4	4	4	4	3	3	3	3
	C	4	4	4	4	4	4	3	3	3	3
	B	4	4	4	4	4	4	3	3	3	3
	A	4	4	4	4	4	4	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X69 AND 70298-X69LF	D	3	2	2	2	2	2	2	3	3	2
	C	2	3	2	2	2	2	2	1	3	2
	B	2	3	2	2	2	2	2	2	3	2
	A	3	2	2	2	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X70 AND 70298-X70LF	D	3	2	2	1	2	2	2	2	3	2
	C	3	2	2	2	2	2	2	2	3	2
	B	3	2	2	2	2	2	2	2	3	2
	A	3	2	2	2	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X71 AND 70298-X71LF	D	2	2	2	2	1	1	1	1	2	2
	C	2	2	2	2	1	1	1	1	2	2
	B	2	2	2	2	1	1	1	1	2	2
	A	2	2	2	2	1	1	1	1	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X72 AND 70298-X72LF	D	3	2	1	2	2	2	2	2	3	2
	C	3	2	2	2	2	2	2	2	3	2
	B	3	2	2	2	2	2	2	2	3	2
	A	3	2	2	2	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X73 AND 70298-X73LF	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	1	1	1	1	2	2
	B	2	2	2	2	1	1	1	1	2	2
	A	2	2	2	2	1	1	1	1	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X74 AND 70298-X74LF	D	3	-	-	2	-	1	2	2	2	2
	C	3	-	-	2	-	2	2	2	2	2
	B	3	-	-	2	-	2	2	2	2	2
	A	3	-	-	2	-	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X75 AND 70298-X75LF	D	3	-	-	2	-	2	2	2	2	2
	C	3	-	-	2	-	2	2	2	2	2
	B	3	-	-	2	-	2	2	2	2	2
	A	3	-	-	2	-	2	2	2	2	2

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI	
lfr	ecn no.	dr	date	linear	0.X ±0.3			COPY		www.fciconnect.com	
CD					0.XX ±0.13			projection		title	
					.XXX ±.051					METRAL SIGNAL HEADER	
					0° ±2°					2 MOD, 4 ROW PRESS-FIT	
				angles	dr	T.BRUNGARD	01/27/00	MM		product family	
					engr	M.STRAWSE	01/27/00	1:1		METRAL	
					chr	M.STRAWSE	01/27/00			code	
					appd	M.STRAWSE	02/29/00			213	
sheet index		revision sheet								sheet	
										8	



METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X76 AND 70298-X76LF	D	2	2	2	2	2	2	2	2	2	-
	C	2	2	2	2	2	2	2	2	2	-
	B	2	2	2	2	2	2	2	2	2	-
	A	1	2	2	2	2	2	2	2	2	-

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X77 AND 70298-X77LF	D	7	-	-	6	-	5	6	6	6	6
	C	7	-	-	6	-	6	6	6	6	6
	B	7	-	-	6	-	6	6	6	6	6
	A	7	-	-	6	-	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X78 AND 70298-X78LF	D	6	6	6	6	6	6	6	6	6	6
	C	6	6	6	6	6	6	6	6	6	6
	B	6	6	6	6	6	6	6	6	6	6
	A	5	6	6	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X79 AND 70298-X79LF	D	3	-	-	2	6	6	6	6	6	6
	C	3	-	-	2	6	6	6	6	6	6
	B	3	-	-	2	6	6	6	6	6	6
	A	3	-	-	2	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X80 AND 70298-X80LF	D	6	6	6	6	6	6	6	6	6	-
	C	6	6	6	6	6	6	6	6	6	-
	B	6	6	6	6	6	6	6	6	6	-
	A	5	6	6	6	6	6	6	6	6	-

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X81 AND 70298-X81LF	D	8	7	7	7	7	7	7	7	7	8
	C	8	7	7	7	7	7	7	7	7	8
	B	8	7	7	7	7	7	7	7	7	8
	A	8	7	7	7	7	7	7	7	7	8

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X82 AND 70298-X82LF	D	2	2	3	3	3	2	2	2	4	3
	C	2	2	3	3	3	2	2	2	4	3
	B	2	2	3	3	3	2	2	2	4	3
	A	2	2	3	3	3	2	2	2	4	3

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X83 AND 70298-X83LF	D	2	2	3	2	2	2	2	2	4	3
	C	2	2	2	2	2	2	2	2	4	3
	B	2	2	2	2	2	2	2	2	4	3
	A	2	2	2	2	2	2	2	2	4	3

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X84 AND 70298-X84LF	D	2	2	2	2	2	2	3	3	3	2
	C	2	2	2	2	2	2	3	3	3	2
	B	2	2	2	2	2	2	3	3	3	2
	A	2	2	2	2	2	2	3	3	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X85 AND 70298-X85LF	D	3	2	2	2	3	3	2	4	3	3
	C	3	2	2	2	3	3	2	4	3	3
	B	3	2	2	2	3	3	2	4	3	3
	A	3	2	2	2	3	3	2	4	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X86 AND 70298-X86LF	D	3	3	2	2	2	2	2	3	3	4
	C	3	3	2	2	2	2	2	3	3	4
	B	3	3	2	2	2	2	2	3	3	4
	A	3	3	2	2	2	2	2	3	3	4

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X87 AND 70298-X87LF	D	2	2	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X88 AND 70298-X88LF	D	20	7	7	7	7	7	20	7	7	6
	C	20	7	7	7	7	7	20	7	7	6
	B	20	7	7	7	7	7	20	7	7	6
	A	20	7	7	7	7	7	20	7	7	6

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X89 AND 70298-X89LF	D	4	4	4	4	4	4	2	2	2	2
	C	4	4	4	4	4	4	2	2	2	2
	B	4	4	4	4	4	4	2	2	2	2
	A	19	19	19	19	19	19	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1				MOD. 2					
		1	2	3	4	5	6	7	8	9	10
70298-X90 AND 70298-X90LF	D	2	2	2	2	2	2	3	3	3	3
	C	2	2	2	2	2	2	3	3	3	3
	B	2	2	2	2	2	2	3	3	3	2
	A	2	2	2	2	2	2	3	3	3	3

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI		
lfr	ecn no.	dr	date	linear	0.X ±0.3			COPY		www.fciconnect.com		
CD					0.XX ±0.13			projection		title		
					.XXX ±.051					METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT		
				angles	0° ±2°					product family		
				dr	T.BRUNGARD		01/27/00		MM		METRAL	
				engr	M.STRAWER		01/27/00		scale		code	
				chr	M.STRAWER		01/27/00		1:1		213	
				appd	M.STRAWER		02/29/00		A		sheet	
sheet index		revision sheet								9		



METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X91 AND 70298-X91LF	D	2	2	2	2	2	2	4	4	4	4	4	4
	C	2	2	2	2	2	2	4	4	4	4	4	4
	B	2	2	2	2	2	2	4	4	4	4	4	4
	A	2	2	2	2	2	2	19	19	19	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X92 AND 70298-X92LF	D	4	4	4	4	4	4	3	3	3	3	3	3
	C	4	4	4	4	4	4	3	3	3	3	3	3
	B	4	4	4	4	4	4	3	3	3	3	2	2
	A	19	19	19	19	19	19	3	3	3	3	3	3

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X93 AND 70298-X93LF	D	-	3	3	-	3	3	3	-	-	3	3	-
	C	3	-	3	-	3	3	3	-	3	-	3	-
	B	3	3	-	3	3	3	3	-	3	3	-	-
	A	-	3	3	-	3	3	3	-	-	3	3	-

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X94 AND 70298-X94LF	D	2	2	2	1	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X95 AND 70298-X95LF	D	1	1	1	1	1	1	3	3	3	3	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	19
	B	1	1	1	1	1	1	1	1	1	1	1	19
	A	1	1	1	1	1	1	1	1	1	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X96 AND 70298-X96LF	D	5	5	5	5	5	5	5	20	5	5	20	
	C	5	5	5	5	5	5	5	20	5	5	20	
	B	5	5	5	5	5	5	5	20	5	5	20	
	A	5	5	5	5	5	5	5	20	5	5	20	

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X97 AND 70298-X97LF	D	1	1	19	1	1	19	5	20	5	5	5	5
	C	1	1	19	1	1	19	5	20	5	5	5	5
	B	1	1	19	1	1	19	5	20	5	5	5	5
	A	1	1	19	1	1	19	5	20	5	5	5	5

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X98 AND 70298-X98LF	D	1	1	19	1	1	19	1	1	19	1	1	1
	C	1	1	19	1	1	19	1	1	19	1	1	1
	B	1	1	19	1	1	19	1	1	19	1	1	1
	A	1	1	19	1	1	19	1	1	19	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X99 AND 70298-X99LF	D	1	1	1	1	3	3	3	3	3	3	1	1
	C	1	1	1	1	1	1	1	1	1	1	1	19
	B	1	1	1	1	1	1	1	1	1	1	1	19
	A	1	1	1	1	1	1	1	1	1	19	19	19

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X100 AND 70298-X100LF	D	1	5	1	1	1	1	1	1	20	5	5	20
	C	1	5	1	1	1	1	1	1	20	5	5	20
	B	5	5	1	1	1	1	1	1	20	5	5	20
	A	5	5	1	1	1	1	1	1	20	5	5	20

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X101 AND 70298-X101LF	D	1	1	19	1	1	19	19	19	19	1	1	1
	C	1	1	19	1	1	19	19	19	19	1	1	1
	B	1	1	19	1	1	19	1	1	19	1	1	1
	A	1	1	19	1	1	19	1	1	1	19	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X102 AND 70298-X102LF	D	2	2	2	2	2	2	2	1	2	2	2	19
	C	2	1	2	1	2	2	2	1	2	2	2	19
	B	2	2	2	2	2	2	2	2	2	2	2	19
	A	1	2	2	1	1	1	2	2	2	2	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X103 AND 70298-X103LF	D	6	6	6	6	20	6	6	6	6	6	6	6
	C	6	6	6	5	20	6	6	6	6	6	6	6
	B	6	6	6	6	20	6	6	6	6	6	6	6
	A	6	6	6	6	20	6	6	6	6	6	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X104 AND 70298-X104LF	D	2	2	2	2	2	19	2	3	2	1	2	19
	C	2	2	2	2	2	19	2	3	2	1	2	19
	B	2	2	2	2	2	19	2	3	2	1	2	19
	A	1	19	2	1	2	19	2	3	2	1	2	19

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					
		1	2	3	4	5	6	7	8	9	10	11	12
70298-X105 AND 70298-X105LF	D	6	6	6	6	6	20	6	7	6	5	6	20
	C	6	6	6	6	6	20	6	7	6	5	6	20
	B	6	6	6	6	6	20	6	7	6	5	6	20
	A	5	20	6	5	6	20	6	7	6	5	6	20

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCJ www.fcjconnect.com			
lfr	ecn no.	dr	date	linear	0.X ±0.3				projection	COPY			
CD					0.XX ±0.13					title			
					.XXX ±.051					METRAL SIGNAL HEADER 2 MOD, 4 ROW PRESS-FIT			
				angles	0° ±2°				MM scale 1:1	product family			
				dr	T.BRUNGARD 01/27/00					METRAL			
				enrg	M.STRAWER 01/27/00					code			
				chr	M.STRAWER 01/27/00				size				
				appd	M.STRAWER 02/29/00				dwg no				
sheet index		revision sheet										213	
												sheet 10	



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X106 AND 70298-X106LF	D	3	2	2	2	1	1	3	1	1	2
	C	3	2	2	2	1	1	3	1	1	2
	B	3	2	2	2	1	1	3	1	1	2
	A	3	2	2	2	1	1	3	1	1	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X107 AND 70298-X107LF	D	7	6	5	5	5	5	5	5	5	7
	C	7	6	5	5	5	5	5	5	5	7
	B	7	6	5	5	5	5	5	5	5	7
	A	7	6	5	5	5	5	5	5	5	7

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X108 AND 70298-X108LF	D	3	2	3	2	2	2	2	1	1	1
	C	3	2	3	2	2	2	2	1	1	1
	B	3	2	3	2	2	2	2	1	1	1
	A	3	2	3	2	2	2	2	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X109 AND 70298-X109LF	D	1	2	2	1	1	3	2	2	2	2
	C	1	2	2	1	1	3	2	2	2	2
	B	1	2	2	1	1	3	2	2	2	2
	A	1	2	2	1	1	3	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X110 AND 70298-X110LF	D	1	1	1	1	1	2	2	1	1	2
	C	1	1	1	1	1	2	2	1	1	2
	B	1	1	1	1	1	2	2	1	1	2
	A	1	1	1	1	1	2	2	1	1	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X111 AND 70298-X111LF	D	3	3	2	2	2	2	2	2	2	2
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	3	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X112 AND 70298-X112LF	D	3	2	2	2	1	1	1	2	1	1
	C	3	2	2	2	2	2	1	1	1	1
	B	3	2	2	2	1	2	1	1	1	1
	A	3	2	2	2	1	2	1	1	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X113 AND 70298-X113LF	D	2	2	1	2	2	1	1	2	1	1
	C	2	2	1	2	2	1	1	2	1	1
	B	2	2	1	2	2	1	1	2	1	1
	A	2	2	1	2	2	1	1	2	1	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X114 AND 70298-X114LF	D	2	2	2	3	1	1	2	2	2	2
	C	2	2	2	3	2	2	2	2	2	2
	B	2	2	2	3	2	2	2	2	2	2
	A	1	2	2	3	2	2	2	2	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X115 AND 70298-X115LF	D	2	2	2	2	19	19	2	3	2	2
	C	2	2	2	2	19	19	2	3	2	2
	B	2	2	2	2	19	19	2	3	2	2
	A	2	2	2	2	19	19	2	3	2	2

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X116 AND 70298-X116LF	D	2	2	2	2	19	19	2	3	2	1
	C	2	2	2	2	19	19	2	3	2	1
	B	2	2	2	2	19	19	2	3	2	1
	A	2	2	2	2	19	19	2	3	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X117 AND 70298-X117LF	D	6	6	6	6	20	20	6	7	6	6
	C	6	6	6	6	20	20	6	7	6	6
	B	6	6	6	6	20	20	6	7	6	6
	A	6	6	6	6	20	20	6	7	6	6

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X118 AND 70298-X118LF	D	2	2	2	2	2	2	2	2	2	1
	C	2	2	2	2	2	2	2	2	2	2
	B	2	2	2	2	2	2	2	2	2	2
	A	2	2	2	2	2	2	2	2	2	1

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2				
		1	2	3	4	5	6	7	8	9	10
70298-X119 AND 70298-X119LF	D	3	2	2	2	2	2	2	2	2	2
	C	3	2	2	2	2	2	2	2	2	2
	B	3	2	2	2	2	2	2	2	2	2
	A	3	2	2	2	2	2	2	2	2	1

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCJ	
lfr	ecn no.	dr	date	linear	0.X ±0.3	COPY		www.fcjconnect.com	
CD				angles	0.XX ±0.13	projection		title	
					.XXX ±.051			METRAL SIGNAL HEADER	
					0° ±2°			2 MOD, 4 ROW PRESS-FIT	
				dr	T.BRUNGARD 01/27/00	product family		METRAL	
				enrg	M.STRAWSE 01/27/00	size		dwg no	
				chr	M.STRAWSE 01/27/00	A		70298	
				appd	M.STRAWSE 02/29/00	sheet		213	
sheet index		revision sheet				cage code		22526	