





FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection INCH/MM	product family SLIM LINE
ltr	ecn no	dr	date	tolerances unless otherwise specified		scale 4:1	title
E	V61462	MDF	10/14/96	angles	linear		PRESS FIT HEADER ASS'Y SLIM LINE 4 WALL
F	V61785	SAR	12/13/96				
G	V61745	MDF	1/23/97	0°±2°			
H	V20526	RGD	3/18/02	dr	M. CLUSER	8/27/87	
J	M05-0099	MHT	5/24/05	enrg	B. TROSTLE	8/27/87	
K	M07-0116	AGS	2/24/07	chr	R. DOUTRICH	10/6/88	
L	M07-0489	MHT	11/13/07	appd	R. DOUTRICH	10/6/88	
sheet index	revision	L	L	L	L	L	
	sheet	1	2	3	4	5	



dwg no 68712 sheet 1 of 5 size A3

type Product Customer Drawing

1

2 3

4

5




6

PRODUCT NUMBER

SEE TABLE

NOTES:

- ① MOLDING MATERIAL: 30% GLASS FILLED POLYESTER
FLAME RETARDENT PER UL94V-O. COLOR-BLUE.
- ② TERMINAL MATERIAL: PHOSPHOR BRONZE.
- ③ REFER TO TA 556 FOR APPLICATION, TOOLING
AND INSTRUCTIONS.
4. UNLESS OTHERWISE SPECIFIED, 1° MAX DRAFT
PERMISSIBLE ON ALL SURFACES.
5. LOGO LOCATION OPTIONAL.
- ⑥ TWO NON-CRITICAL SIDES OF PIN TIP NOT
PLATED TYP BOTH ENDS.
7. 3 LBS / .36 KG PIN RETENTION IN BOTH
DIRECTIONS.
8. RECOMMENDED PLATED-THRU-HOLE DIMENSIONS ARE:
DRILLED HOLE: .0453/1.151±.0010/.025 DIA
COPPER PLATING THICKNESS: .001/.025 TO .003/.076
SOLDER PLATING THICKNESS: .0003/.076 TO .0007/.0178
OVERALL HOLE SIZE: .040/1.016±.003/.076 DIA
- ⑨ ON HEADERS 2 X 20 AND LARGER THE .260/6.6 DIM
HAS A MINIMUM SIZE OF .240/6.1.
- ⑩ PIN PLATING-DUPLEX- 30u"/.076u Au OVER 50u"/1.27uNi
ON CONTACT AREA OF PIN AND 40u"/1.02u-80u"/2.03u
TIN/LEAD ON PRESS FIT AREA OF PIN.
LEAD FREE: PIN PLATING-DUPLEX- 30u"/.076u Au OVER 50u"/1.27uNi
ON CONTACT AREA OF PIN AND 40u"/1.02u-80u"/2.03u
PURE TIN ON PRESS FIT AREA OF PIN.
- ⑪ PART NUMBER WITH "LF" SUFFIX AT THE END ARE LEAD FREE.
12. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑬ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.
14. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING
SOLDER PROCESS.

2 X 5
STYLE A2 X 7
STYLE C2 X 5
STYLE B2 X 8 & LARGER
STYLE D

FCIconnect.com

Copyright FCI

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection  INCH/MM scale 4:1 		product family SLIM LINE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified						title				
L					angles	linear	XXX±.01/XX±.3				PRESS FIT HEADER ASS'Y				
							XXX±.005/XX±0.13				SLIM LINE 4 WALL				
					0°±2'		XXX±.0020/XXX±.051			dwg no					
					dr	M. CLUSER	8/27/87				sheet2 of 5		size		
					enr	B. TROSTLE	8/27/87				68712		A3		
					chr	R. DOUTRICH	10/6/88								
					app	R. DOUTRICH	10/6/88								
sheet index		revision sheet													

form: A3

1

2

3

4

5

6



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING NOTE 13	STYLE
68712-001LF	2 X 5	.78/19.81	.72/18.28	.400/10.16	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	A
-002LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-003LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-004LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-005LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-006LF	2 X 5	.78/19.81	.72/18.28	.400/10.16	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	A
-007LF	2 X 7	.98/24.89	.92/23.37	.600/15.24	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	C
-008LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-009LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-010LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-011LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-012LF	2 X 7	.98/24.89	.92/23.37	.600/15.24	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	C
-013LF	2 X 8	1.08/27.43	1.02/25.91	.700/17.78	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-014LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-015LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-016LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-017LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-018LF	2 X 8	1.08/27.43	1.02/25.91	.700/17.78	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-019LF	2 X 10	1.28/35.51	1.22/30.99	.900/22.86	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-020LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-021LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-022LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-023LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
68712-024LF	2 X 10	1.28/35.51	1.22/30.99	.900/22.86	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D

mat'l. code				surface ☒ ISO 1302		tolerance ☒ ISO 406 ☒ ISO 1101		projection 		product family SLIM LINE			
ltr	ecn no	dr	date	tolerances unless otherwise specified						title			
L				angles	linear	.XX±.01/XX±0.3		INCH/MM	PRESS FIT HEADER ASS'Y SLIM LINE 4 WALL				
				0°±2'		.XXX±.005/XX±0.13							
						.XXXX±.0020/XXX±0.051		scale 4:1	dwg no sheet3 of 5 size 68712 A3				
		dr	M. CLUSER	8/27/87									
		enr	B. TROSTLE	8/27/87									
		chr	R. DOUTRICH	10/6/88									
		app	R. DOUTRICH	10/6/88					type Product Customer Drawing				
sheet index		revision sheet											

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	NO OF POS	DIM R	DIM S	DIM T	DIM E	TERMINAL PLATING NOTE 13	STYLE
68712-049LF	2 X 20	2.28/57.91	2.22/56.39	1.900/48.26	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-050LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-051LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-052LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-053LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-054LF	2 X 20	2.28/57.91	2.22/56.39	1.900/48.26	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-055LF	2 X 22	2.48/62.99	2.42/61.47	2.100/53.34	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-056LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-057LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-058LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-059LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-060LF	2 X 22	2.48/62.99	2.42/61.47	2.100/53.34	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-061LF	2 X 25	2.78/70.61	2.72/69.09	2.400/60.96	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-062LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-063LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-064LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-065LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-066LF	2 X 25	2.78/70.61	2.72/69.09	2.400/60.96	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-067LF	2 X 30	3.28/83.31	3.22/81.79	2.900/73.66	.160/4.06	30u"/.76u Au OVER 50u"/1.27 Ni	D
-068LF					.160/4.06	30u"/.76u GXT OVER 50u"/1.27u Ni	
-069LF					.610/15.49	30u"/.76u Au OVER 50u"/1.27 Ni	
-070LF					.610/15.49	30u"/.76u GXT OVER 50u"/1.27u Ni	
-071LF					.733/18.62	30u"/.76u Au OVER 50u"/1.27 Ni	
-072LF	2 X 30	3.28/83.31	3.22/81.79	2.900/73.66	.733/18.62	30u"/.76u GXT OVER 50u"/1.27u Ni	
-073LF	2 X 17	1.98/50.29	1.92/48.77	1.600/40.64	.160/4.06	50u"/1.27u Au OVER 50u"/1.27u Ni	D
-074LF	2 X 5	.78/19.81	.72/18.29	.400/10.16	.110/2.79	30u"/.76u GXT OVER 50u"/1.27u Ni	A
-075LF	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.110/2.79	30u"/.76u GXT OVER 50u"/1.27u Ni	D
-076LF	2 X 12	1.48/37.59	1.42/36.07	1.100/27.94	.110/2.79	30u"/.76u GXT OVER 50u"/1.27u Ni	D
68712-201LF	2 X 5	.78/19.81	.72/18.29	.400/10.16	.160/4.06	SEE NOTE 10	A
68712-201	2 X 5	.78/19.81	.72/18.29	.400/10.16	.160/4.06	SEE NOTE 10	A
68712-219LF	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.160/4.06	SEE NOTE 10	D
68712-219	2 X 10	1.28/32.51	1.22/30.99	.900/22.86	.160/4.06	SEE NOTE 10	D

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family SLIM LINE
ltr	ecn no	dr	date	tolerances unless otherwise specified		 INCH/MM scale 4:1	title
L				angles	linear		PRESS FIT HEADER ASS'Y
				0°±2'			SLIM LINE 4 WALL
				dr	M. CLUSER	8/27/87	dwg no
				enr	B. TROSTLE	8/27/87	sheet5 of 5 size
				chr	R. DOUTRICH	10/6/88	68712 A3
				appd	R. DOUTRICH	10/6/88	type Product Customer Drawing
sheet index	revision sheet						

form: A3