




PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family LATCH-N-LOK			
ltr ecn nodr date				tolerances unless otherwise specified						title			
M	M07-0521	AGS	12/10/07	angles	linear	.XXX±.01/.XXX±.03		INCH/MM 	2X4 LNL LOW PROFILE HEADER ASSEMBLY				
N	ELX-N-004176	KW	06/22/11			.XXX±.005/.XXX±.013							
P	ELX-N-008473	ZK	11/28/11			.XXX±.0020/.XXX±.0051							
				0'±2"				scale 2:1					
				dr	M. CLOUSER	12/22/89			dwg no		sheet 1 of 2	size	
J	M05-0052	MHT	3/16/05	engr	D. HORCHLER	12/22/89			69958		A3		
K	M06-0285	AGS	7/28/06	chr	D. HORCHLER	12/22/89							
L	M06-0365	AGS	9/20/06	app	D. HORCHLER	12/22/89			type Product Customer Drawing				
sheet revision				P	P								
index sheet				1	2								

69958-XXXXLF


LEAD FREE OPTION ⑥⑧

HIGH TEMPERATURE ⑦

	COLOR ④	
1	70343-LT GRAY	OBS
2	80166 OFF WHITE	
3	70634-DK GRAY	OBS
4	701 BLACK	
5	70511-SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING ③
0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni

	PIN LENGTH
	DIM L
0	.200/5.08
1	.130/3.30



RECOMMENDED PCB LAYOUT

NOTES:

- HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC, UL-94V-0 RATED
- GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u TIN.
- SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING OPTIONALLY: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT AREA OR TAIL, OPTIONALLY (78---295u") TIN ON TAIL.
- NUMBERS SHOWN ARE FOR G.E. LEXAN AND ARE FOR REFERENCE ONLY.
- THIS ASSEMBLY UL APPROVED PER FILE E66906 VOL. 1, SEC. 84 AND CSA APPROVED PER MASTER FILE LR46923
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- FOR 69958-XXXXLF THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PRODUCT SPEC: GS-12-003

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family LATCH-N-LOK	
ltr ecn nodr date		tolerances unless otherwise specified		title		dwg no		sheet 2 of 2 size	
P		angles	line	.XX±.01/.3 XXX±.005/.13 XXX±.0020/.051		scale 1:1		69958 A3	
		dr	M. CLOUSER	12/22/89		FCI			
		enr	D. HORCHLER	12/22/89					
		chr	D. HORCHLER	12/22/89					
		app	D. HORCHLER	12/22/89					
sheet index		revision sheet							