





PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70228-X01/X01LF	1.6	2.90
70228-X11/X11LF	2.4	3.53



PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:




- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 6 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- 8 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.





RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltn	ecn	nodr	date	linear	projection	title	www.fciconnection
K	DG04-004	CLU	04/22/01			RA FEMALE SIGNAL	
L	DG06-0477	CenH	11/17/06			STB 24 mm VERSION	
M	DG07-0168	CenH	05/10/07	angles			
N	DG09-0068	CenH	06/06/09	dir	Avan Zanten	900918	
				engr	H. Bouwknegt	940308	
H	V00578	LLA	000316	chr	A van Zanten	900918	
J	V00847	LLA	000530	app	H van Voensel	900918	
sheet	revision	N	N				
index	sheet	1	2	3			

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70228-X02/X02LF	1.6	2.90
70228-X12/X12LF	2.4	3.53




PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL

PC BOARD THICKNESS SEE TABLE ± 0.20 

PRODUCT AFTER HOT RIVETTING.

NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDERTAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 6 SET BACK FOR PRESS BLOCK.
- 7 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO
0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE
TAIL LENGTH BEFORE APPLICATION TO A BOARD
- 8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008 .
- 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION.
- 10 DIAMOND LOCATION PEG ARE ONLY EXISTED ON
THE BOTH SIDES OF PRODUCT.





RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

Mat'l code				tolerances unless otherwise specified				CUSTOMER COPY				www.Fcconnect.com		
l	t	r	e	c	n	n	d	a	t	e	linear		project title	
N											angles		RA FEMALE SIGNAL STB 24 mm VERSION	
											dr D de Bil 970529		product family METRAL(tn)	
											Engr P. Schaik 970529		size dwg no	
											chr P. Schaik 970529		scale	
											app H. Cooljans 970529		A2 70228	
sheet index		revision sheet										sheet 2 of -		




All rights strictly reserved. Reproduction or issue in any form without written authority from the proprietor.
Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite du propriétaire.
FCI S.A. - 13000 MARSEILLE Cedex 09 - FRANCE
© FCI S.A.


PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM "A"
70228-X03/X03LF	1.6	2.90
70228-X13/X13LF	2.4	3.53



PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 6 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- 8 DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

nat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
litr	ecnr	nodr	date	linear	projection	title	www.fciconnection
N					mm	RA FEMALE SIGNAL STB 24 mm VERSION	
				angles		product family	METRAL (tm)
				dir	Heaven Cen	11/17/06	code
				enr	Collins Lu	11/17/06	213
				chr	Beer Fu	11/17/06	sheet
				appd	Joseph Hsla	11/17/06	3 of -
sheet	revision			scale	5:1	A2	70228
index	sheet						