



PRODUCT NO




SEE TABLE




.345 [8.76] REF
⊕ ∅.006/0.15 M X



SECTION A-A



w/WINDOW OPTION
SEE TABLE



DRAWN WITHOUT WINDOW OPTION

spec ref				dr		Yong Huang	2010/10/25	projection		INCH / MM		size		A3	scale		1.000				
tolerance std				eng		Zheng-Kun Hu	2013/08/27					ecn no		ELX-N-13688-1							
ISO406 ISO1101				chr		-	-					rel level		Released							
ISO1302				appr		Rick Bian	2013/08/27	product family													
surface		linear		0.X		±0.3				title		QUICK II HDR D/R		dwg no		72454		rev		AK	
				0.XX		±0.13															
				0.XXX		±0.05															
		ISO 1302		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw				sheet 1 of 4			



Copyright FCI.

A

B

C

D

A

B

C

D


PRODUCT NO SEE TABLE	PLATING CODE	CONTACT AREA PLATING	SOLDER TAIL PLATING
	AA	30u"/.76u GXT OVER 50u"/1.27u Ni	100u"/2.54u Sn OVER 50u"/1.27u Ni
	4	100u"/2.54u Sn OVER 50u"/1.27u Ni	100u"/2.54u Sn OVER 50u"/1.27u Ni

LEAD FREE PLATING	AA	30u"/.76u GXT OVER 50u"/1.27u Ni	100u"/2.54u Sn OVER 50u"/1.27u Ni
	4	100u"/2.54u Sn OVER 50u"/1.27u Ni	100u"/2.54u Sn OVER 50u"/1.27u Ni


NOTE 11

NOTES:


1. BODY MATERIAL: PA46, GLASS FIBER REINFORCED, FLAME RETARDENT PER UL-94V-0.
COLOR: BLACK
OR
MINERAL FILLED LCP, FLAME RETARDENT PER UL-94V-0
COLOR: BLACK
2. PIN MATERIAL: PHOS-BRONZE.
3. PINS DELETED FROM SPECIFIED LOCATIONS FOR POLARIZATION. SEE TABLE FOR LOCATIONS.
4. PACKAGING OPTIONS: CHECK SPECIFIC PART NUMBERS FOR AVAILABILITY.
PART NUMBERS WITHOUT A SUFFIX ARE PACKAGED
PART NUMBERS FOLLOWED BY A "V" SUFFIX ARE PACKAGED
TAPE-ON-REEL INSTALLED PER BUS-14-200 SECTION 2. VACUUM CAP TO BE CENTRALLY LOCATED REGARDLESS OF NUMBER OF POSITIONS.
PART NUMBERS FOLLOWED BY A "B" SUFFIX ARE PACKAGED IN TRAYS WITH A PICK UP CAP INSTALLED PER BUS-14-445 & SEE GS-14-920 FOR LEAD FREE PACKAGED SPEC.
5. MEASURED WITH PART IN RESTRAINED CONDITION.
6. TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS (SIMPLEX PLATING ONLY).
7. 2 LBS/0.9KG MIN PIN RETENTION IN EITHER DIRECTION.
8. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
9. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
10. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10-20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
11. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."
12. PRODUCT SPEC: BUS-12-082




RECOMMENDED PAD LAYOUT
SCALE 4/1



5 POSITION
2 X 5
STYLE A




7 POSITION
2 X 7
STYLE C




2 x 8 AND LARGER, STYLE D


spec ref				dr		Yong Huang	2010/10/25	projection	INCH / MM	size		A3	scale		1.000
tolerance std				eng		Zheng-Kun Hu	2013/08/27			ecn no		ELX-N-13688-1			
ISO406 ISO1101				chr		-	-			rel level		Released			
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr		Rick Bian	2013/08/27			product family					
surface ISO 1302		linear	0.X	±0.3	FCi	title QUICK 11 HDR D/R SLIMLINE SMT ASSEMBLY				dwg no 72454		rev AK			
			0.XX	±0.13											
			0.XXX	±0.05											
		angular	0°	±2°	www.fci.com	cat. no.		Product - Customer Drw				sheet 2 of 4			

PRODUCT NO
SEE TABLE



UN-REELING DIRECTION OF FEED →



spec ref				dr		Yong Huang	2010/10/25	projection 	INCH / MM 	size	A3	scale	1.000	
tolerance std				eng		Zheng-Kun Hu	2013/08/27			ecn no				ELX-N-13688-1
TOLERANCES UNLESS OTHERWISE SPECIFIED				chr		-	-			rel level				Released
				appr		Rick Bian	2013/08/27			product family				
surface 		linear	0.X ±0.3	FCI		title QUICK II HDR D/R SLIMLINE SMT ASSEMBLY				dwg no 72454		rev AK		
ISO 1302		angular	0° ±2°	www.fci.com										
cat. no.						Product - Customer Drw						sheet 3 of 4		

A

B

C

D

PRODUCT NUMBER	NO. OF POSITIONS	DIM B	DIM C	STYLE	POLARIZED POSITION	WINDOW OPTION	PLATING CODE	PACKAGING	TAPE WIDTH DIM M	POCKET DEPTH	DIM N	LEAD FREE OPTION
72454-008	2 X 4	.610/15.50	.690/15.33	A	-	N	AA	TRAY	--	--	--	NOTE 8,9 ↑
72454-010	2 X 5	.710/18.03	.790/20.07	A	-	N	AA	TRAY	--	--	--	
72454-010V	2 X 5	.710/18.03	.790/20.07	A	-	N	AA	TAPE ON REEL	1.260/32.00	.515/13.08	.790/20.07	
72454-014	2 X 7	.910/23.11	.99/25.2	C	-	N	AA	TRAY	--	--	--	
72454-014V	2 X 7	.910/23.11	.99/25.2	C	-	N	AA	TAPE ON REEL	1.732/44.00	.515/13.08	1.090/27.69	
72454-016	2 X 8	1.010/25.65	1.090/27.69	D	-	N	AA	TRAY	--	--	--	
72454-016V	2 X 8	1.010/25.65	1.090/27.69	D	-	N	AA	TAPE ON REEL	1.732/44.00	.515/13.08	1.090/27.69	
72454-020	2 X 10	1.210/30.73	1.290/32.77	D	-	N	AA	TRAY	--	--	--	
72454-020V	2 X 10	1.210/30.73	1.290/32.77	D	-	N	AA	TAPE-ON-REEL	2.205/56.00	.505/12.83	1.290/32.77	
72454-021	2 X 11	1.310/33.27	1.390/35.31	D	12	N	AA	TRAY	--	--	--	
72454-022	2 X 11	1.310/33.27	1.390/35.31	D	-	N	AA	TRAY	--	--	--	
72454-024	2 X 12	1.410/35.81	1.490/37.9	D	-	N	AA	--	--	--	--	
72454-024V	2 X 12	1.410/35.81	1.490/37.9	D	-	N	AA	TAPE-ON-REEL	2.205/56.00	.515/13.08	1.490/37.85	
72454-026	2 X 13	1.510/38.35	1.590/40.39	D	-	N	AA	TRAY	--	--	--	
72454-026V	2 X 13	1.510/38.35	1.590/40.39	D	-	N	AA	TAPE-ON-REEL	2.205/56.00	0.787/20.00	1.614/41.00	
72454-030	2 X 15	1.710/43.43	1.790/45.47	D	-	N	AA	TRAY	--	--	--	
72454-030V	2 X 15	1.710/43.43	1.790/45.47	D	-	N	AA	TAPE-ON-REEL	2.834/72.00	0.787/20.00	1.771/45.00	
72454-034	2 X 17	1.910/48.51	1.990/50.60	D	-	N	AA	TRAY	--	--	--	NOTE 8,9 ↓
72454-040	2 X 20	2.210/56.13	2.290/58.17	D	-	N	4	TRAY	--	--	--	
72454-040V	2 X 20	2.210/56.13	2.290/58.17	D	-	N	4	TAPE-ON-REEL	3.465/88.00	0.787/20.00	2.290/58.25	
72454-041	2 X 20	2.210/56.13	2.290/58.17	D	-	N	AA	TRAY	--	--	--	
72454-041V	2 X 20	2.210/56.13	2.290/58.17	D	-	N	AA	TAPE-ON-REEL	3.465/88.00	0.787/20.00	2.290/58.25	
72454-044	2 X 22	2.410/61.21	2.490/63.25	D	-	N	AA	TRAY	--	--	--	
72454-050	2 X 25	2.710/68.83	2.790/70.87	D	-	N	AA	TRAY	--	--	--	
72454-051	2 X 10	1.210/30.73	1.290/32.77	D	-	Y	AA	TRAY	--	--	--	
72454-051V	2 X 10	1.210/30.73	1.290/32.77	D	-	Y	AA	TAPE-ON-REEL	2.205/56.00	.505/12.83	1.290/32.77	
72454-052	2 X 20	2.210/56.13	2.290/58.17	D	20	N	AA	TRAY	--	--	--	
72454-053V	2 X 5	0.710/18.03	0.790/20.07	A	9	N	AA	TAPE ON REEL	1.260/32.00	.515/13.08	.790/20.07	

A

B

C

D

spec ref				dr	Yong Huang		2010/10/25		projection		INCH/MM		size	A3		scale	1.000				
tolerance std				eng	Zheng-Kun Hu		2013/08/27						ecn no		ELX-N-13688-1						
ISO406 ISO1101				chr	-		-						rel level				Released				
surface				linear		0.X		±0.3				QUICK II HDR D/R SLIMLINE SMT ASSEMBLY		dwg no		72454		rev		AK	
				0.XX		±0.13															
				0.XXX		±0.05															
ISO 1302				angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw				sheet 4 of 4			