



AC

B



CONFIDENTIAL



www.fciconnect.com

title	SCA2 PLUG CONNECTOR STRADDLE MOUNT
-------	---------------------------------------

product family		SCA-2	code
size	dwg no		—

A	72547	sheet 1 of 3
---	-------	-----------------

[illegible]

	cage code	22526
--	-----------	-------

STATUS: **Released**

Printed: Feb 01, 2007


mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com			
litr	ecn no	dr	date	linear	.X ±.3				projection 	title SCA2 PLUG CONNECTOR STRADDLE MOUNT			
G	S10131	GLL	11/12/01		.XX ±.13								
H	S03-0049	GLL	4/3/03		.XXX ±.051								
J	S04-0029	GLL	3/2/04	angles	0° ±2°				 MM scale 1:1	product family SCA-2		code -	
K	S04-0058	GLL	3/30/04	dr	TANGWEI	9/25/98		size		dwg no	72547		sheet 1 of 3
L	S04-0246	GLL	11/18/04	engr	GL LOO	9/25/98							
M	S05-0051	GLL	2/23/05	chr	GL LOO	9/25/98							
				appd	JOEY NG	9/25/98							
sheet index	revision sheet	M 1	M 2	M 3									

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.


FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.
SEE TABLE



RECOMMENDED PC BOARD
MOUNTING DIMENSIONS



SECTION X-X

CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		A FCI www.fciconnect.com								
ltr	ecn no	dr	date	linear	.X ±.3			projection 	title SCA2 PLUG CONNECTOR STRADDLE MOUNT									
M					.XX ±.13													
					.XXX ±.051													
				angles	0° ±2°			MM scale 1:1	product family SCA-2				code					
				dr	TANGWEI	9/25/98	size		dwg no		-							
				enrg	GL L00	9/25/98	A		72547		sheet 2 of 3							
				chr	GL L00	9/25/98												
				appd	JOEY NG	9/25/98												
sheet index	revision sheet		1															

cage code
22526

ACAD

PDM: Rev:M

STATUS: Released

Printed: Feb 01, 2007

PRODUCT NO.	NO. OF POS.	RECOMMENDED PCB THICKNESS	DIM. A	DIM. B	DIM. C	DIM. D	PLATING SPEC	PRODUCT NO.	PLATING SPEC	PRODUCT NO.	PLATING SPEC
72547-001	20	1.19	.970	1.32	0.88	4.00	NOTE 2	72547-001LF	NOTE 16	72547-201LF	NOTE 12
72547-001S											
72547-002								72547-002LF		72547-202LF	
72547-002S											
72547-003	20	1.57	1.520	1.83	1.44	5.00	NOTE 10	72547-003LF		72547-203LF	
72547-003S											
72547-103S											
72547-004											
72547-004S	20	1.57	1.520	1.83	1.44	4.00	NOTE 10	---		72547-204LF	

NOTES:

- HOUSING : LCP, UL94V-0 RATED, COLOR: BLACK
CONTACTS: PHOSPHOR BRONZE
ESD CONTACT: PHOSPHOR BRONZE
- PLATING: CONTACT: 0,76µm (30µ") MIN GXT IN CONTACT AREA, 2,54µm (100µ") MIN TIN-LEAD ON P.C. BOARD LEG, 1,27µm (50µ") MIN. NICKEL UNDERPLATE OVER ENTIRE TERMINAL
ESD CONTACT: 2,54 µm (100µ") MIN TIN-LEAD PLATING WITH 1,27µm (50µ") MIN. NICKEL UNDERPLATE
- MEASURED AT THE FLOOR OF THE CAVITY MEASURED 6mm FROM DATUM $\boxed{-Z-}$.
- APPLIES TO ALL SURFACES OF CONTACT TAILS
- MAXIMUM BOARD THICKNESS THAT CONNECTOR CAN ACCOMODATE IS DEFINED BY "B" DIM.
- THESE DIMENSIONS RESULT IN THE CONTACT RESTING IN CENTER OF PAD WIDTH. THESE DIMENSIONS ARE SUBJECT TO CHANGE DEPENDING ON CUSTOMERS MANUFACTURING PREFERENCES IN PROCESS, SOLDER PLACEMENT AND REFLOW.
- DATE CODE IN THIS AREA.
- MEASUREMENT MADE AT THE CENTER OF PART MAY BE AS LOW AS 6.55. DESIGN TO BE MADE TO ACHIEVE THE NOMINAL DIMENSION ACROSS THE ENTIRE PART.
- DISTANCE MEASURED ACROSS CONTACT MATING SURFACES ALONG EFFECTIVE MATING AREA AND CONTACT MUST BE ABOVE PLASTIC ALONG EFFECTIVE MATING AREA.
- PLATING: CONTACT: 0,76µm (30µ") MIN GOLD IN CONTACT AREA, 2,54µm (100µ") MIN TIN-LEAD ON P.C. BOARD LEG, 1,27µm (50µ") MIN. NICKEL UNDERPLATE OVER ENTIRE TERMINAL
ESD CONTACT: 2,54 µm (100µ") MIN TIN-LEAD PLATING WITH 1,27µm (50µ") MIN. NICKEL UNDERPLATE
- PART NUMBERS ENDING IN -0xx or -0xxS or -1xxS ARE MANUFACTURED WITH BRIGHT FINISH TIN-LEAD PLATING IN P.C. BOARD LEG AREA.
- PLATING: CONTACT: 0,76µm (30µ") MIN GOLD IN CONTACT AREA, 2,54µm (100µ") - 5,08µm (200µ") TIN ON P.C. BOARD LEG, 1,27µm (50µ") MIN. NICKEL UNDERPLATE OVER ENTIRE TERMINAL
ESD CONTACT: 2,54 µm (100µ") -5,08µm (200µ") TIN PLATING WITH 1,27µm (50µ") NICKEL UNDERPLATE
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- PART NUMBERS ENDING IN "LF" MEANS FOR NOTE 14 LEAD FREE IDENTIFICATION. P/N XXXXX-2XXLF IS EQUIVALENT TO PREVIOUS P/N XXXXX-2XX.
- PLATING: CONTACT: 0,76µm (30µ") MIN GXT IN CONTACT AREA, 2,54µm (100µ") - 5,08µm (200µ") TIN ON P.C. BOARD LEG, 1,27µm (50µ") MIN. NICKEL UNDERPLATE OVER ENTIRE TERMINAL
ESD CONTACT: 2,54 µm (100µ") -5,08µm (200µ") TIN PLATING WITH 1,27µm (50µ") NICKEL UNDERPLATE

CONFIDENTIAL

mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		A FCI www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ±.3			projection 	title SCA2 PLUG CONNECTOR STRADDLE MOUNT			
M					.XX ±.13							
					.XXX ±.051							
				angles	0° ±2°				product family SCA-2 size dwg no A 72547			
				dr	TANGWEI	9/25/98						
				enrg	GL LOO	9/25/98						
				chr	GL LOO	9/25/98	scale 1:1					
				appd	JOEY NG	9/25/98						
sheet index		revision sheet										
		1										