





Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
SEE TABLE



mat'l. code SEE NOTE 1				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.3	projection	title		
B	V04-0580	VS	6/8/04		.XXX ±.005/.XX±.13		SERPENT(SMALL)		
				angles	.XXXX ±.0020/.XXX±.051	 INCH/MM	product family		code
				dr	0° ± 2'		SERPENT		213
				engr	V.SEASTIAN 6/8/04	scale	size		sheet
				chr	H.SUNDY 6/8/04		dwg no		1 of 2
				appd	H.SUNDY 6/8/04		A 76679		
sheet index	revision sheet	B 1	B 2				cage code		
							22526		

ACAD

PDM: Rev:B

STATUS:Released

Printed: Feb 17, 2006

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER	UNREELING DIRECTION	PLATING	WIRE RANGE	CRIMP HEIGHT	INSULATION RANGE	NOTES
76679-001	CW	50u"/1.27u MIN Ni UNDERPLATE,OVERPLATE WITH 30u"/.76uM GOLD IN CONTACT AREA. A GOLD FLASH ON REMAINDER. CARRIER STRIP IS DEVOID OF GOLD.	28 TO 32 AWG	$.029 \pm .001$ $.737 \pm .025$	$.026$ TO $.075$ $.66$ TO 1.91	
-004	CCW					
-005	LOOSE PIECE					NOTE 3
-006	CW	50u"/1.27uM MIN Ni UNDERPLATE,OVERPLATE WITH 30u"/.76uM GOLD IN CONTACT AREA. 50u"/1.27uM MIN TIN-LEAD IN AREA "A".				
-007	CCW					
76679-008	LOOSE PIECE					

NOTES:

1. TERMINAL MATERIAL: .012/.30 ± .0005/.013 THICK PHOSPHOR BRONZE.
2. TERMINAL PLATING: SEE TABLE, PAGE 2
3. .010/.25 MAX APPLIES TO 75971-005 ONLY.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com	
ltr	ecn no	dr	date	linear	.xx ±.01/.x±.3		projection	title	
B					.xxx ±.005/.xx±.13				SERPENT(SMALL)
				angles	.xxxx ±.0020/.xxx±.051		INCH/MM		product family SERPENT
				dr	0° ±2°			scale	code
				enr	V.SEASTIAN	6/8/04	15:1		213
				chr	H.SUNDY	6/8/04		A	sheet
				appd	H.SUNDY	6/8/04	76679		2 of 2
sheet index	revision sheet								

cage code
22526

ACAD