

PRODUCT NUMBER	DIM "J"	DIM "K"
76314-XXX(LF)	SEE NEXT SHEET	

WHEN NEEDED, SUFFIX LETTER "LF" INDICATES THE PRODUCT IS RoHS COMPATIBLE, SEE NOTE 5

WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.

NOTES:

- MATERIAL HOUSING: THERMOPLASTIC POLYESTER 30 % GLASS FILLED, COLOUR BLUE, FLAME RETARDANT PER UL 94-V0
- MATERIAL BOX: BRASS ASTM B36 C26000-H02
- MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194 C 17200-TF 00
- PLATING: SEE NEXT SHEET
- RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.


c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-22-008

76314-1XXLF &-2XXLF ARE SIMILAR TO 76314-(1*2)XX, THE SUFFIX 'LF' IS ADDED FOR LEAD FREE IDENTIFICATION.

EXCEPT FOR 76314-9XX; 2µm MIN MATTE TIN OVER 1.27µm Ni IS SUPPLIED INSTEAD OF SnPb.



mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family BERGCON			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title V. C. C. DOUBLE ROW .100x.100			
C	F40751	PNZ	94.10.12	angles	linear					
D	F60062	OMA	96.01.29	±2'		scale 5:1	dwg no 76314			
E	V60456	OMA	96.03.11							
F	F05-0235	DLE	05.08.25	dr	O. MATHEVON	96.01.29	sheet 1 of 2			
G	F06-0216	DLE	06.07.11	engr	AESCHBACHER	96.01.29				
				chr	O. MATHEVON	96.01.29	size A3			
				appd	M. AE	96.01.29				
sheet index	revision sheet	G	G				type CUSTOMER Drawing			
		1	2							

