



PRODUCT NUMBER

77312-YXXLF

RoHS COMPATIBLE
SEE NOTE 7

PIN STYLE

PLATING SEE SHEET 2



NOTES:

1. HOUSING MAT'L : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
3. PRODUCT PACKAGED IN POLY BAGS.
4. 9N MIN RETENTION IN EITHER DIRECTION
5. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
6. UNDERPLATING : 1.27µm Ni MIN
7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.



b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.


c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004



BOTTOM VIEW



mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BSTIK
ltr	ecr no	dr	date	tolerances unless otherwise specified		mm	title
AR	F-24825	AMA	16.08.26	angles	linear		HEADER SR,STR, POL,DUPLEX,2.54mm
AS	F-25332	DDE	16.11.15			scale 5:1	dwg no
AT	F-25396	LMU	16.11.21	dr	COMPAGNON J	95.10.27	sheet 1 of 5
AM	B-20230	LMU	15.02.09	enr	JMC	95.10.27	size
AN	B-21118	LMU	15.06.10	chr			77312
AP	F-24327	AMA	16.06.17	appd	JMC	95.10.27	A3
sheet	revision	AT	T	N	Y	G	type
index	sheet	1	2	3	4	5	CUSTOMER Drawing



PIN STYLE	PRODUCT DEFINITION			
	NB OF POS	MATING SIDE	SOLDER SIDE	("OAL") REF
01	1x5	5.84	3.42	11.8
02	1x8	5.84	3.42	11.8
03	1x3	5.84	3.42	11.8
04	1x8	5.72	2.54	10.8
05	1x16	5.72	2.54	10.8
06	1x12	5.72	2.54	10.8
07	1x28	5.84	3.42	11.8
15	1x19	5.84	3.42	11.8
16	1x18	5.84	3.42	11.8
17	1x7	5.84	3.42	11.8
18	1x7	5.84	3.42	11.8
19	1x9	5.84	3.42	11.8
20	1x9	5.84	3.42	11.8
21	1x32	5.84	3.42	11.8
22	1x32	5.84	3.42	11.8

BOTTOM VIEW OF HEADER SHOWING MISSING PIN POSITIONS							
1	5	10	15	20	25	30	35

77312-GXXLF	0.76μm FULL GXT	
77312-SXXLF	0.38μm FULL GXT	
77312-8XXLF	0.38μm Au/GXT	2.0-7.5μm Sn MATTE
77312-5XXLF	0.25μm Au/GXT	2.0-7.5μm Sn MATTE
77312-4XXLF	2.0-7.5μm FULL MATTE TIN	
77312-2XXLF	1.27μm Au	2.0-7.5μm Sn MATTE
77312-1XXLF	0.76μm Au/GXT	2.0-7.5μm Sn MATTE
77312-1XXSLF	0.76μm Au/GXT	GOLD FLASH
PLATING CODE	CONTACT AREA	REMAINDER
	PLATING THICKNESS OVER 1.27μm Ni	

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family BSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
S	B-18917	LMU	14.09.26	angles	linear		HEADER,SR,STR, POL,DUPLEX,2.54mm
T	B-21118	LMU	15.06.10			scale 1:1	
M	F10707	LMU	01.11.28	dr	COMPAGNON J		dwg no
N	F06-0196	LMU	06.06.20	enrg	JMC		sheet 2 of -
P	F08-0148	RTR	08.03.31	chr			size
R	B-17773	LMU	14.05.26	appd	JMC		77312 A3
sheet index	revision sheet						type CUSTOMER Drawing



FCIconnect.com

Copyright FCI

form: A3

PIN STYLE	PRODUCT DEFINITION			
	NB OF POS	MATING SIDE	SOLDER SIDE	("OAL") REF
23	1x 13	5.84	3.42	11.8
24	1x 14	5.84	3.42	11.8
25	1x 4	5.84	3.42	11.8
26	1x 10	5.84	3.42	11.8
27	1x 10	5.84	3.42	11.8
28	1x 6	5.72	2.54	10.8
29	1x 7	5.84	3.42	11.8
30	1x 19	5.84	3.42	11.8
31	1x 25	5.84	3.42	11.8
32	1x 15	5.84	3.42	11.8
33	1x 8	5.84	3.42	11.8
34	1x 10	5.84	3.42	11.8
35	1x 6	5.84	3.42	11.8
36	1x 11	5.84	3.42	11.8
37	1x 29	5.84	3.42	11.8
38	1x 25	5.84	3.42	11.8
39	1x 5	5.72	2.54	10.8
40	1x 11	5.72	3.05	11.3
41	1x 11	5.72	3.05	11.3
42	1x 8	7.75	3.06	13.35
43	1x 7	5.84	3.42	11.8
44	1x 7	5.72	2.54	10.8
45	1x 20	5.72	7.64	15.9
46	1x 11	5.72	3.05	11.3
48	1x 4	5.72	3.05	11.3
49	1x 16	5.72	7.64	15.9
50	1x 3	5.72	3.05	11.3

BOTTOM VIEW OF HEADER SHOWING MISSING PIN POSITIONS							
123							
1	5	10	15	20	25	30	

1					2 3					4					5					6														
PIN STYLE	PRODUCT DEFINITION				BOTTOM VIEW OF HEADER SHOWING MISSING PIN POSITIONS										1 2 3																			
	NB OF POS	MATING SIDE	SOLDER SIDE	("OAL") REF	1	5	10	15	20	25	30	35																						
51	1x5	5.72	3.05	11.3																														
52	1x13	5.72	3.05	11.3																														
53	1x35	5.72	3.05	11.3																														
54	1x11	5.72	3.05	11.3																														
55	1x23	12.83	3.03	18.4																														
56	1x23	17.5	3.46	23.5																														
57	1x5	5.84	3.42	11.8																														
58	1x7	5.72	3.05	11.3																														
59	1x5	5.72	3.05	11.3																														
60	1x6	5.72	3.05	11.3																														
61	1x8	5.72	3.05	11.3																														
62	1x4	5.72	3.05	11.3																														
63	1x4	15.57	2.84	20.95																														
65	1x4	5.72	2.54	10.8																														
66	1x8	5.72	2.54	10.8																														
67	1x4	5.72	3.05	11.3																														
68	1x4	5.72	3.05	11.3																														
69	1x6	5.72	3.05	11.3																														
70	1x3	5.72	2.54	10.8																														
71	1x5	5.84	2.42	10.8																														
72	1x13	5.72	2.54	10.8																														
73	1x8	5.84	2.41	10.8																														
74	1x16	5.84	2.41	10.8																														
75	1x08	5.84	2.41	10.8																														
76	1x05	2.50	1.80	6.84																														
77	1x05	2.50	1.80	6.84																														
78	1x03	8.13	2.33	13.00																														
79	1x35	5.84	3.42	11.80																														
80	1x07	2.50	1.80	6.84																														
81	1x03	24.90	3.00	30.40																														
82	1x05	20.65	11.00	34.15																														
83	1x12	5.84	3.42	11.80																														
84	1x05	8.00	2.90	13.40																														
85	1x07	8.00	2.90	13.40																														
					mat'l. code					surface ☒ ISO 1302 ☐ ISO 406 ☐ ISO 1101		tolerance ☐ ISO 1101		projection		product family BSTIK																		
					ttr ecn no dr date					tolerances unless otherwise specified				mm		title																		
					S F10355 LMU 01.06.25					angles		linear				HEADER,SR,STR, POL,DUPLEX,2.54mm																		
					T F10707 LMU 01.11.28									scale N/A		dwg no sheet 4 of size																		
					U F06-0196 LMU 06.06.20											77312 A3																		
					V F11-0034 LMU 11.03.03 dr					COMPAGNON J		95.10.11				type CUSTOMER Drawing																		
					W F11-0045 LMU 11.04.06 engr					JMC		95.10.27																						
					X F11-0329 LMU 11.11.17 chr																													
					Y B-16703 LMU 14.01.09 appd					JMC		95.10.27																						
					sheet index		revision sheet																											
form: A3					1					2					3					4					5					6				

