




PRODUCT N°: SEE SHEET 213-2 OF 2



R TO FULL RADIUS ALLOWED TYP

NOTES:

1. MATERIAL HOUSING: THERMOPLASTIC POLYESTER, 30% GLASFILLED, COLOUR BLUE, FLAME RETARDANT PER UL 94-V0.
2. MATERIAL BOX: BRASS ASTM B36 C26000-H02
3. MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194 C17200-TF 00
4. PLATING: SEE SHEET 213-2 OF 2



PDMD Me RB: B STABUSING Re Released Printed on 18p22032005

THIS PRINT IS THE PROPERTY OF AND EMPLOYS PROPRIETARY DESIGNS OF THE BERG ELECTRONICS DIVISION OF DUPONT DE NEMOURS NEDERLAND BV. NO PART OF THE DESIGN SHOWN IN THIS PRINT MAY BE USED IN ANY WAY WITHOUT THE WRITTEN CONSENT OF BERG ELECTRONICS DIVISION, A HERTINGENBOCH, HOLLAND.

76 325
SHEET 213 - 1 OF 2

CUSTOMER COPY FOR REFERENCE ONLY			
BERG ELECTRONICS DIVISION DUPONT DE NEMOURS NEDERLAND BV			
SEE NOTES	SEE NOTE 4	B ECP BEU 5095	76 325
PART NO	MATERIAL	A ECP BEU 4659	H B
R. SCHELLEKENS OCT 1974		RELEASED 0670	SHEET 213 - 1 OF 2
M. Lo		VERTICAL CARD CONNECTOR	
5.1		double row 100x100	

PRODUCT	NO	NO OF POS	DIM. ('J')	DIM. ('K')
76325	X02	2 x 02	2.54 100	5.08 200
	X03	2 x 03	5.08 200	7.62 300
	X04	2 x 04	7.62 300	10.16 400
	X05	2 x 05	10.16 400	12.70 500
	X06	2 x 06	12.70 500	15.24 600
	X07	2 x 07	15.24 600	17.78 700
	X08	2 x 08	17.78 700	20.32 800
	X09	2 x 09	20.32 800	22.86 900
76325	X10	2 x 10	22.86 900	25.40 1,000
	X11	2 x 11	25.40 1,000	27.94 1,100
	X12	2 x 12	27.94 1,100	30.48 1,200
	X13	2 x 13	30.48 1,200	33.02 1,300
	X14	2 x 14	33.02 1,300	35.56 1,400
	X15	2 x 15	35.56 1,400	38.10 1,500
	X16	2 x 16	38.10 1,500	40.64 1,600
	X17	2 x 17	40.64 1,600	43.18 1,700
	X18	2 x 18	43.18 1,700	45.72 1,800
	X19	2 x 19	45.72 1,800	48.26 1,900
76325	X20	2 x 20	48.26 1,900	50.80 2,000
	X21	2 x 21	50.80 2,000	53.34 2,100
	X22	2 x 22	53.34 2,100	55.88 2,200
	X23	2 x 23	55.88 2,200	58.42 2,300
	X24	2 x 24	58.42 2,300	60.96 2,400
	X25	2 x 25	60.96 2,400	63.50 2,500
	X26	2 x 26	63.50 2,500	66.04 2,600
	X27	2 x 27	66.04 2,600	68.58 2,700
	X28	2 x 28	68.58 2,700	71.12 2,800
	X29	2 x 29	71.12 2,800	73.66 2,900
76325	X30	2 x 30	73.66 2,900	76.20 3,000

PRODUCT NO	NO OF POS	DM. ('J')	DM. ('K')
76325 - X31	2 x 31	78.28 3.000	78.75 3.100
- X32	2 x 32	78.75 3.100	81.28 3.200
- X33	2 x 33	81.28 3.200	83.82 3.300
- X34	2 x 34	83.82 3.300	86.36 3.400
- X35	2 x 35	86.36 3.400	88.90 3.500
- X36	2 x 36	88.90 3.500	91.44 3.600
- X37	2 x 37	91.44 3.600	93.98 3.700
- X38	2 x 38	93.98 3.700	96.52 3.800
- X39	2 x 39	96.52 3.800	99.06 3.900
76325 - X40	2 x 40	99.06 3.900	101.60 4.000
- X41	2 x 41	101.60 4.000	104.14 4.100
- X42	2 x 42	104.14 4.100	106.68 4.200
- X43	2 x 43	106.68 4.200	109.22 4.300
- X44	2 x 44	109.22 4.300	111.76 4.400
- X45	2 x 45	111.76 4.400	114.30 4.500
- X46	2 x 46	114.30 4.500	116.84 4.600
- X47	2 x 47	116.84 4.600	119.38 4.700
- X48	2 x 48	119.38 4.700	121.92 4.800
- X49	2 x 49	121.92 4.800	124.46 4.900
76325 X50	2 x 50	124.46 4.900	127.00 5.000

4	$1.9 \mu\text{m}$ $75 \mu\text{inch}$ Au	$1.3 \mu\text{m}$ $50 \mu\text{inch}$ Ni MINIMUM
3	$1.3 \mu\text{m}$ $50 \mu\text{inch}$ Au	$1.3 \mu\text{m}$ $50 \mu\text{inch}$ Ni MINIMUM
2	$1.0 \mu\text{m}$ $40 \mu\text{inch}$ Au	$1.3 \mu\text{m}$ $50 \mu\text{inch}$ Ni MINIMUM
X	PLATING THICKNESS	THICKNESS

CUSTOMER COPY FOR REFERENCE ONLY			
NO POSTAGE-NECESSARY IF MAILED IN THE UNITED STATES			
MATERIAL SEE TABLE		CO COSTERVELD 830303	DATE APR 12 1968 <i>R. Hansen</i>
MEAT TREAT		CNR M. LARSEN	DATE APR 12 REL EASED
			
FEDERAL BUREAU OF INVESTIGATION U. S. DEPARTMENT OF JUSTICE			
PHASE SEE TABLE		NEW YORK 100-100000-100000	
LAYOUT		POSTAL C	DATE APR 12 1968

PDMD Rev: B STATUS: Not Released Printed: Sep 2003 2005

76325

5

4

3




2

1

PRODUCT N° 76325-XXX

THIRD ANGLE
PROJECTION

This print is the property of and embodies proprietary designs of the BERG ELECTRONICS DIVISION of DU PONT DE NEMOURS (NEDERLAND) B.V. No part of the design shown on this print may be used in any way without the written consent of BERG ELECTRONICS DIVISION, s-Hertogenbosch, Holland.

DIMENSIONS $\frac{\text{mm}}{\text{INCHES}}$
DO NOT SCALERECOMMENDED
PIN PATTERNRECOMMENDED
HOLE PATTERN

NOTES :

1. THICKNESS P.C. BOARD INCLUDING METAL FOIL 1.60 ± 0.20 (.063 ± .008)
2. TERMINALS CAN ONLY BE USED FOR P.C. BOARD APPLICATION WITH NON-PLATED THROUGH HOLES.
3. PRODUCT TO MATE WITH 0.635 ± 0.025 (.025 ± .001) SQUARE PIN OR ROUND PIN.

CUSTOMER COPY FOR REFERENCE ONLY

BERG ELECTRONICS DIVISION
 DU PONT DE NEMOURS (NEDERLAND) B.V.
 s-hertogenbosch holland

PART NO. MATERIAL PLATING

 DR. R. SCHELLEKENS DATE: OCT 30 APP: 21 NOV 30
 CHK: M. 40 DATE: NOV 80 REL: DATE:

RELEASED 0670

SCALE
10:1TITLE
VERTICAL CARD CONNECTOR
double row. 100x.100
 LOC SIZE NO 76325 REV
 H B SHEET 215 1. OF 1.