



6

Technical drawing of a 10-hole punch plate. The drawing shows a rectangular plate with 10 circular holes arranged in a single row. The center-to-center distance between adjacent holes is labeled as $(N-1) \times 2.54$. The total length of the plate is labeled as $N \times 2.54 \text{ MAX}$. A note "NOTE 5" is present. The plate has a thickness of 1.2. The holes are shown with dashed lines indicating they pass through the plate. The drawing is a top view.



d - LEGAL STATEMENT: SEE GS-47-0004

6



FCIconnect.com

Copyright FCI

PRODUCT SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	DIM "C"
01		5.72	2.57	1.5
02		5.72	5.11	1.5
03		5.72	7.65	1.5
07		5.72	5.11	3.9
13		5.72	3.45	1.5
18		5.84	3.05	1.5
22		11.71	3.2	1.5
24		6.75	2.85	1.5
25		8.07	3.05	1.5
26		8.2	12.6	1.5
27		5	3.9	1.5
28		3.1	3.1	1.5
29		9.7	2.90	1.5
30		8.30	4.40	1.5
31		11.70	2.80	1.5
32		8.90	3.05	1.5
33		10.20	3.05	1.5
34		10.00	3.25	1.5
35		5.72	12.73	1.5
36		N/A		
37		N/A		
38		8.51	5.51	1.5
39		9.80	9.30	1.5
40		8.13	2.54	3.90
41		14.20	3.05	1.5
42		9.00	7.20	1.5
43		8.08	2.79	1.5
44		15.70	2.79	1.5
45		8.20	2.35	1.5
46		3.10	9.90	1.5
47		2.30	2.30	1.5
48		3.50	3.05	1.5

PLATING

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
4 = 3µm-5µm TIN FULL PLATED REFLOW
5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
G = 0.76µm FULL GXT
S = 0.38µm FULL GXT
- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family BERGSTIK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title UNSHR.HEADER RA SR TMT			
AP	F-23462	LMU	16.03.07	angles	linear					
AR	F-23551	LMU	16.03.21							
AS	F-24328	AMA	16.06.17			scale 5:1	dwg no 77315 sheet 2 of 2 size A3			
AT	F-25336	DDE	16.11.15	dr	D.LE	01.01.24				
AU	F-25361	DDE	16.11.16	enr	JM.C	01.01.24				
				chr	JM.C	01.01.24	type CUSTOMER Drawing			
AN	F-23373	AMA	16.02.26	appd	JF.N	01.01.24				
sheet	revision									
index	sheet									