




PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family LATCH-N-LOK				
ltr ecn nodr date				tolerances unless otherwise specified						title				
H	ELX-N-008453	ZK	11/28/11	angles	linear	.XXX±.01/.XXX±0.3 .XXX±.005/.XXX±0.13 .XXX±.0020/.XXX±0.051		INCH/MM 		2X6 LNL VERTICAL PANEL HEADER ASSEMBLY				
C	V01703	TFG	7/21/00	0°±2°				scale 1:1		dwg no				
D	V10987	TFG	2/15/01	dr	M. CORMAN	6/25/90				sheet 1 of 2		size		
E	M05-0050	MHT	3/16/05	engr	D. HORCHLER	6/25/90				78098		A3		
F	M06-0282	AGS	7/28/06	chr	D. HORCHLER	6/25/90				type		Product	Customer	Drawing
G	M06-0365	AGS	9/20/06	appd	D. HORCHLER	6/25/90								
sheet		revision		H										
index		sheet		1	2									


78098-XXXXLF

LEAD FREE OPTION (6)(8)

	COLOR (4)	
1	70343 LT GRAY	OBS
2	80166 OFF WHITE	
3	70634 DK GRAY	OBS
4	701 BLACK	
5	70511 SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING (3)
0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni

	PIN LENGTH
	DIM L
0	.200/5.08
1	.130/3.30



RECOMMENDED P.C.B. LAYOUT

NOTES:

- HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC.
UL-94V-0 RATED.
- GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u" TIN
- SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING OPTION: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
- NUMBERS SHOWN ARE FOR G.E. LEXAN AND
ARE FOR REFERENCE ONLY.
- THIS ASSEMBLY U.L. APPROVED PER FILE E66906 VOL. 1, SEC. 84
AND CSA APPROVED PER MASTER FILE LR46923.
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PRODUCT SPEC: GS-12-003

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family LATCH-N-LOK	
ltr ecn nodr date		tolerances unless otherwise specified		angles linea		scale 1:1		title 2X6 LNL VERTICAL PANEL HEADER ASSEMBLY	
H				0°±2'		FCCI		dwg no 78098	
		dr M. CORMAN 6/25/90		engr D. HORCHLER 6/25/90				sheet 2 of 2 size A3	
		chr D. HORCHLER 6/25/90		app D. HORCHLER 6/25/90				type Product Customer Drawing	
sheet index		revision sheet							