





PRODUCT NUMBER
91613-YXX-XX

PART NUMBER DEFINITION

91613-YXX-XX
 — NB OF POSITIONS
 — VERSION
 — PLATING
 — BASE PART NUMBER



RECOMMENDED HOLE PATTERN



NOTES:

- 1 - PIN MATERIAL : COPPER ALLOY.
- 2 - MATERIAL BODY : POLAMID 30% GLASS-FILLED , FLAME RETARDANT PER UL-VO COLOR BLACK.
- 3 - DIM 1.27 $^{+0.03}_{-0.13}$ FOR MOULDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.02 TO 1.7 MAX APPLIES.
- 4 - PIN PUSH OUT FORCE : 12N MIN.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	ELECTRONICS www.fciconnect.com		
SEE P/N						projection	title		
ltr	ecn no	dr	date	linear			HEADER STR,DR DOUBLE BODY,DUPLEX		
C	F31015	JMC	93.12.23	angles			product family	BSTIK	code
D	F50645	JMC	95.08.29			size	dwg no	213	
E	F50821	JMC	95.11.07	dr	COMPAGNON J	93.12.23	product family BSTIK code size dwg no 213		
F	F60320	JMC	96.04.23	engr	JCO	95.08.29	scale 5:1 A3 91613 sheet 1 of 2		
sheet index				revision	F	E			
				sheet	1	2			

Tous droits réservés. Reproduction ou communication sans autorisation écrite de FCI Electronics S.A. est formellement interdite.

All rights reserved. Reproduction or communication without written authority from FCI Electronics S.A. is expressly prohibited.

PRODUCT NUMBER	PRODUCT DIMENSIONS			
	"A" ±0.15	"E" ±0.25	"B" ±0.25	("L") REF
91613-X01-XX	5.6	10	3	18.6
91613-X02-XX	10.6	11.8	3	26
91613-X03-XX	9.8	9.6	3	22.4
91613-X04-XX	6.77	5.1	2.6	14.47
91613-X06-XX	6.61	11.3	3.05	20.96
91613-X07-XX	10.5	17.5	3.12	31.12
91613-X08-XX	6	12.8	3.6	22.4
91613-X09-XX	11.5	13.5	2.8	28

91613-8XX	0.4µm Au	4µm SnPb
91613-1XX	0.76µm Au	4µm SnPb
PLATING CODE	CONTACT AREA	REMAINDER
	PLATING THICKNESS OVER 1.27µm Ni MIN	

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY	 ELECTRONICS www.fciconnect.com		
ltr	ecn no	dr	date	linear	projection 	title HEADER STR,DR DOUBLE BODY DUPLEX	
C	F31015	JMC	93.12.23				
D	F50645	JMC	95.08.30	angles	mm ←→	product family BSTIK	
E	F60320	JMC	96.04.23				
			dr	COMPAGNON J	95.08.29	code 213	
			engr	JMC	95.08.29		
			chr			size A3	
			appd	JMC	95.08.30		
sheet index	revision sheet					scale	91613 sheet 2 of -