


NOTES:

1. MATERIAL AND FINISH:
BODY - BRASS, GOLD PLATING
CONTACT - BERYLLIUM COPPER, GOLD PLATING
INSULATOR - PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE:50 OHM
B. FREQUENCY RANGE: 0-2 GHz
C. VSWR (RETURN LOSS): 1.2 MAX.
D. DIELECTRIC WITHSTANDING VOLTAGE:1000 VRMS. (FOR ONE MINUTE)
E. CONTACT RESISTANCE: 5 mOHM MAX. (CENTER CONTACT)
1 mOHM MAX. (OUTER CONTACT)
F. VOLTAGE RATING: 500 VOLTS
G. INSULATION RESISTANCE: 10000 MOHM (AT 500V FOR ONE MINUTE)
3. MECHANICAL:
A. DURABILITY:500 CYCLES MIN.
B. TEMPERATURE RANGE:-40°C TO +85°C
C. OPERATING HUMIDITY: 10% TO 80% REL HUMIDITY




THIRD ANGLE PROJ.



SCALE 5.000

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	ENGINEERING PROTOTYPE	7/1/98	--	PB/TA
B	DELETE PACKAGING INFORMATION AND BOM	2/11/99	--	CPM/PB
C	TRANSFERED TO ARFA	29-Dec-08	--	SH
D	ADDED NOTE 3.C.\RD-DM09062601M	09-Jul-09	47492	SH
E	CONTACT PIN'S ASSEMBLING DIMENSION WAS CHANGED \RD-DM11012701S4	31-Jan-11	48283	DH
F	2.29 WAS 1.52, 0.46 WAS 0.76, REMOVED STAKE \RD-DM15042301J1	29-Apr-15	50419	HH



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 120mm ± 0.3mm ANGLES ±1°	MATERIAL -	DRAWN JEKY.C	DATE 28-Apr-15	TITLE MCX RECEPTACLE SURFACE MOUNT	Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER P.BRENZEL	DATE 18-Jun-98			
		REFERENCE EAR 102-966929 1 615X-1429-100 GEN# ASSYF3-MCX	APPROVED H.HE	DATE 28-Apr-15	DRAWING NO. 919-118J-51P	
		FINISH	CAD FILE I:\MCX\919-118J-51P	SCALE: 10.0:1.0 B	REV F	ITEM NO. 919-118J-51P
						PART NO. 919-118J-51P