



1. MATERIALS AND FINISHES:
BODY - STAINLESS STEEL, PASSIVATED
CONTACT - BeCu, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 75 OHM
B. FREQUENCY RANGE: DC - 4 GHz
C. RETURN LOSS: -30 dB MIN AT 3 GHz
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +100° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, APH-NJ-HDBNCJ AND DATE CODE"

REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASED TO MFG.	10/6/10	48270	NMV



SCALE 2.000



ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL SEE NOTES	DRAWN NISCHIT MV	DATE 26-Jul-10	TITLE ADAPTOR, 75 OHM N JACK TO HD BNC JACK		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER NISCHIT MV	DATE 26-Jul-10			DRAWING NO. APH-NJ-HDBNCJ	
	REFERENCE EAR # 4100 AND	APPROVED K. CAPOZZI	DATE 9/22/10	SCALE: 5.0:1.0	SHEET 2 OF 2	ITEM NO. APH-NJ-HDBNCJ	
	CONFIGURATION LEVEL: In Work	CAD FILE Root Folder/HD-BNC/APH-NJ-HDBNCJ	DWG SIZE B		REV A	PART NO. APH-NJ-HDBNCJ	