





SHELLS	:	TIN/ZINC PLATED STEEL
INSULATOR MATERIAL	:	SELF EXTINGUISHING THERMOPLASTIC- TO UL CLASS 94 V0. THE HOUSING WILL WITHSTAND EXPOSURE TO 260-265°C IF WE USE PROTECTIVE ADHESIVE (Kapton or Teflon) OR PROTECTIVE METALLIC DEVICE
CONTACTS DIA ON ACTIVE AREA	:	Ø1 MM.
CONTACTS MATERIAL	:	COPPER ALLOY
CONTACT PLATING	:	GXT / GOLD OVER NICKEL
OPERATING TEMPERATURE	:	-55°C +125°C
OPERATING CURRENT	:	7.5 A PER CONTACT
CONTACT RESISTANCE	:	≤7.3 m Ω
INSULATION RESISTANCE	:	≥5000 M Ω
MAXIMUM VOLTAGE	:	1000 V.r.m.s
MECHANICAL ENDURANCE	:	500 MATINGS MIN.FOR CODE 65 200 MATINGS MIN.FOR CODE 64
DAMP HEAT	:	56 DAYS FOR CODE 65 21 DAYS FOR CODE 64

NOTE:—INSIDE DIMENSIONS OF MALE AND
OUTSIDE DIMENSIONS OF THE FEMALE CONNECTOR.

[illegible]