




| REVISIONS | | | |
|-----------|--------------|----------|--------|
| SYM ZONE | ECN, ERN NO. | DATE | APPRD. |
| A | PROPOSAL | 02/10/19 | |

THIS IS A CAD DRAWING. DO NOT MANUALLY REVISE.




LOCATE HOLES
 $\phi \pm 0.005 [0.127]$
 POSITION DIMENSIONS
 ARE BASIC

MATERIALS:
 PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0
 PHOSPHOR BRONZE
 PLATING: 50 μ [1.27 MICRONS]
 MIN. GOLD ON MATING SURFACES.
 50 μ [1.27 MICRONS]
 MIN. NICKEL UNDERPLATE
 100 μ [2.54 MICRONS]
 MIN. TIN/LEAD ON CONTACT TAILS.

RECOMMENDED P.C.B. LAYOUT
 (COMPONENT SIDE OF BOARD)
 (FRJA-408 SHOWN, FOOTPRINT FOR OTHER
 PART NUMBERS BASED ON
 # OF CONTACTS & RELATED POSITIONS)

PART NUMBER: FRJA-40X

- CONTACTS:**
- 2 = 2 CONTACTS LOADED IN POSITION 4 & 5.
 - 4 = 4 CONTACTS LOADED IN POSITION 3 TO 6.
 - 6 = 6 CONTACTS LOADED IN POSITION 2 TO 7.
 - 8 = 8 CONTACTS LOADED IN POSITION 1 TO 8.
 - C = 2 CONTACTS LOADED IN POSITION 3 & 6.



RECOMMENDED PANEL CUTOUT

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
 MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
 PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

| | | | |
|---|-------------|------------|--------------|
| DRAWN | L. CHAN | DATE | 02/10/19 |
| DESIGNED | | | |
| CHECKED | LESSAUEE | | 02/10/19 |
| L. E. APPROB. | | | |
| Q. A. APPROB. | | | |
| ENGR. REL. NO. | | | |
| REF. EAR 11205 | | | |
| DIMENSIONS ARE IN | 303E D. NOS | | |
| INCHES [mm] | 03554 | | |
| Amphenol Canada Corp. MODULAR JACK, B POSITIONS, WITHOUT FERRITE, WITHOUT SHIELD | | | |
| DWG | DRAWING NO. | P-FRJA-40X | REV. A |
| BDALE | WT. | SUFF. | SHEET 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[FRJA-488](#) [FRJA-438](#) [FRJA-418](#) [FRJA-468](#) [FRJA-408](#) [FRJA-666](#)