

B

A





TABLE 1

PART NO.	NO. OF POS.	DIMENSIONS	
		A ^{+0.2} _{-0.0}	B ^{±0.1}
WH2D-1/WH2D-1LF	2	7.5	2.5
WH3D-1/WH3D-1LF	3	10.0	5.0
WH4D-1/WH4D-1LF	4	12.5	7.5
WH5D-1/WH5D-1LF	5	15.0	10.0
WH6D-1/WH6D-1LF	6	17.5	12.5
WH7D-1/WH7D-1LF	7	20.0	15.0
WH8D-1/WH8D-1LF	8	22.5	17.5 ^{+0.15} _{-0.10}
WH9D-1/WH9D-1LF	9	25.0	20.0 ^{+0.15} _{-0.10}
WH10D-1/WH10D-1LF	10	27.5 ^{±0.3}	22.5 ^{+0.15} _{-0.10}
WH11D-1/WH11D-1LF	11	30.0 ^{±0.3}	25.0 ^{+0.15} _{-0.10}
WH12D-1/WH12D-1LF	12	32.5 ^{±0.3}	27.5 ^{+0.15} _{-0.10}
WH13D-1/WH13D-1LF	13	35.0 ^{±0.3}	27.5 ^{+0.15} _{-0.10}


SUFFIX "LF" SEE NOTE 5

1 | 2


1 | 2



SEE NOTE 3




SEE NOTE 3



NOTES:

1. MATERIAL : NYLON 66, UL94V-0 RATED.
2. ORDERING INFORMATION: SEE TABLE 1
3. FLASH : 0.2 MAX.
4. APPEARANCE : 0.3 MAX.
5. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS(WAVE SOLDER & SMT)



PCB LAYOUT RECOMMENDED

3 |

4

ACAD

3 |

4

A

PDM: Rev:B

STATUS Released

Printed: Jul 18, 2006