



	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

A	Male							A
---	-----------------	--	--	--	--	--	--	---



Product Specification

Material

Insulator : Glass-Filled Thermoplastic PBT, UL94V-0,Black

Contact : Copper alloy, plating gold flash selective gold

Shell : Steel, 1000µ" Tin Over 500µ" min Copper

Electrical

- Contact Resistance : 20 milliohms Max at 1 AMP DC.
- Insulation Resistance : 1000 megohms at 500 VDC
- Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
- Current Rating : 3 AMP
- Voltage Rating : 250 VAC/rms 60Hz
- Wire Spec : 26 AWG-28 AWG
- Operating Temperature:-20°C--+85°C

⑤ UL E No #E198287

Cover






Order Code: A-DXF xx LP111/Z

Contact style: F - Female S - Male

No. of Contacts 09 / 15 / 25 / 37

Standard: Quality class III



Strain Relief

Dimensions	Positions	A	B	C	E	F
	9	30.81	24.99	16.92	11.08	13.10
	15	39.20	33.30	25.25	19.39	20.70
	25	53.04	47.04	38.96	33.24	33.68
	37	69.40	63.50	55.42	49.86	50.30

F	Without Insulator Support							F
---	---------------------------	--	--	--	--	--	--	---

G	RoHS compliant Unit:mm							G
---	---	--	--	--	--	--	--	---

Scale	Free	⑤	Correct the UL-File number	03.04.2014	Winnie		Date	Name	Customer-No.
TOLERANCE		④	Update 17.58&17.28 into 17.40&17.10mm	07.03.2014	Winnie	Drawn	15.08.2012	Lucas	
X.	±0.38	③	Update the wire specification	28.06.2013	Winnie	Approved	03.04.2014	Winnie	ASSMANN WSW-No.
X.X	±0.25	②	Add the wire specification	06.03.2013	Winnie				A-DXF xx LP111/Z
X.XX	±0.13	①	Add the UL file No.	18.10.2012	Winnie				Drawing-No.
DIM	TOL	①							ASS 4891 CO
X.°	±3°								rev05
X.X°	±1.0°	①	Drawn	15.08.2012	Lucas				
Angle	TOL		Id.	Modification	Date	Name			Replace



H	1	2	3	4	5	6	7	H
---	---	---	---	---	---	---	---	---

