

**Isolierkörpermaterial**

Nylon, UL94V-0

**Kontaktmaterial**

Phosphorbronze

**Kontaktoberfläche**

Ni, Sn

**Kontaktwiderstand**

20mΩ max

**Isolationswiderstand**

500MΩ min

**Strombelastbarkeit**

1A

**Betriebstemperatur**

-25°C - +85°C

**Betriebsspannung**

100V AC

**Prüfspannung**

500V AC

**Verpackung**

Stangenverpackung

**Insulator material**

Nylon, UL94V-0

**Contact material**

Phosphor bronze

**Plating**

Ni, Sn

**Contact resistance**

20mΩ max

**Insulation resistance**

100MΩ min

**Current rating**

1A

**Operating temperature**

-25°C - +85°C

**Operating voltage**



100V AC

**Test voltage**




500V AC

**Packing**

Tube packing



A = 1.00 x  
No. of Spaces  
B = A + 4.0  
C = A + 2.3



**Bestellcode / Ordercode**

**Polzahlen**

04 - 32

**No. of contacts**

04 - 32

**Raster**

100 - 1.00mm

**Pitch**

100 -1.00mm

TVD - DIP, vertikal,  
Kontakte beidseitig

TVD - DIP, vertical,  
double sided contacts

**Verpackung**

T - Stange

**Packing**

T - Tube

**AFFC09** **xx** - **100** - **TVD** - **x**

Bitte „x“ durch die geeignete Option ersetzen  
Please replace „x“ with appropriate option