


	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

A	Male							A
---	-----------------	--	--	--	--	--	--	---



Product Specification

Material

Insulator : Glass-Filled Thermoplastic PBT, UL94V-0,Black

Contact : Copper alloy, plating gold flash selective gold

Shell : Steel, 1000µ" Tin Over 500µ" min Copper

Electrical

Contact Resistance : 20 milliohms Max at 1 AMP DC.

Insulation Resistance : 1000 megohms at 500 VDC

Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute

- ③ Current Rating : 3 AMP
- Voltage Rating : 250 VAC/rms 60Hz
- ③ Wire Spec : 26 AWG-28 AWG
- Operating Temperature:-20°C--+85°C
- ⑤ UL E No #E198287




Order Code:

A-DXF xx LP III/Z

Contact style:
F - Female
S - Male

No. of Contacts
09 / 15 / 25 / 37

Standard: Quality class III



Strain Relief

Without Insulator Support

Dimensions						
Positions	A	B	C	E	F	
9	30.81	24.99	16.92	11.08	13.10	
15	39.20	33.30	25.25	19.39	20.70	
25	53.04	47.04	38.96	33.24	33.68	
37	69.40	63.50	55.42	49.86	50.30	

F								F
---	--	--	--	--	--	--	--	---

G	RoHS compliant Unit:mm							G
---	---	--	--	--	--	--	--	---

Scale	Free	⑤	Correct the UL-File number	03.04.2014	Winnie	Customer-No.		
TOLERANCE		④	Update 17.58&17.28 into 17.40&17.10mm	07.03.2014	Winnie	Drawn	15.08.2012	Lucas
X.	±0.38	③	Update the wire specification	28.06.2013	Winnie	Approved	03.04.2014	Winnie
X.X	±0.25	②	Add the wire specification	06.03.2013	Winnie			
X.XX	±0.13	①	Add the UL file No.	18.10.2012	Winnie	ASSMANN WSW/ components		
DIM	TOL	①						
X.°	±3°							
X.X°	±1.0°	①	Drawn	15.08.2012	Lucas	Drawing-No. ASS 4891 CO rev05		
Angle	TOL	Id.	Modification	Date	Name			
						Replace		Sheet 1/2

H	1	2	3	4	5	6	7	H
---	---	---	---	---	---	---	---	---

