


## Inductive sensors special versions

## IFRM 08

## sample drawing



## general data

mounting type	shielded
special type	high temperature
nominal sensing distance $S_n$	2 mm
hysteresis	3 ... 20 % of $S_r$

## electrical data

switching frequency	< 5 kHz
voltage supply range +Vs	12 ... 30 VDC
current consumption max.	12 mA
voltage drop Vd	< 3 VDC
output current	< 100 mA
short circuit protection	yes
reverse polarity protection	yes

## mechanical data

type	cylindrical threaded
housing material	stainless steel
dimension	8 mm
housing length	30 mm
connection types	cable Teflon, 1 m

## ambient conditions

operating temperature	-25 ... +100 °C
protection class	IP 67

## order reference

IFRM 08N1707

IFRM 08P1707

## output circuit

NPN make function (NO)

PNP make function (NO)

## sample picture

