



ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	H-101C	T-1 (3mm) LED Holder 90° Mount, Single-Station
2	1	3SRC-S	T-1 (3mm) Shouldered LED

REV.	DESCRIPTION	DATE	APPROVED
A	Engineering Release	01/08/03	M. C.
B	LED Specification Upgrade	08/14/08	M. C.
C	Engineering Update w/o Changes	06/20/16	J. C.



LED P/N	Chip		Lens Appearance	Absolute Max. Ratings				Electro-Optical Data @ 20m A			Viewing Angle (Deg)
	Emitted Color	Peak Wavelength λp (nm)		Δλ (nm)	Pd (mW)	If (mA)	Peak If (mA)	Vf (V)		Iv (mcd)	
								TYP	MAX	TYP	
3SRC-S	SUPER RED	645	WATER CLEAR	-	70	20	150	1.7	2.4	60	30

ABSOLUTE MAXIMUM RATINGS (Ta=25° C)

REVERSE VOLTAGE
5V

REVERSE CURRENT
100uA

OPERATING TEMPERATURE RANGE
-25° C - 85° C

STORAGE TEMPERATURE
-30° C - 100° C

LEAD SOLDERING TEMPERATURE(1/16" FROM BODY)
260° C FOR 5 SECONDS

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u> .X ± .1 .XX ± .02 .XXX ± .010	<u>ANGULAR</u> X° ± 1° 	TITLE: T-1 (3MM) 90° SINGLE-LEVEL LED ASSEMBLY	
DESIGNED: D. Green	DATE: 01/08/03	PART NO: H101CSRC	REVISION: C
CHECKED: M. Chen	DATE: 01/08/03	CAGE CODE : 32559 SHEET # 1 OF 1	
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			