



DASH NO	MODEL NO	IMPD OHMS	A DIM
-1	BJ120	50	.055
-2	UBJ120	75	.025

INCH	MM
.005	0.13
.025	0.64
.030	0.76
.055	1.40
.120	3.05
.150	3.81
.317	8.05
.450	11.43
.550	13.97
.875	22.22

REVISIONS			1005-0455	SH 1	
REV	EO	DESCRIPTION	DWN	APPROVED	DATE
A	2462	MOD WAS JACK, PUSH ON	POB	<i>[Signature]</i>	9-20-74
B	4012	-2 WAS BASIC, ADDED -1	WJM	<i>[Signature]</i>	11-1-77
C	4161	8005-0180-1 WAS BASIC	TAH	<i>[Signature]</i>	4-10-78
D	7191	ADDED .055 DIA	JSA	<i>[Signature]</i>	9-18-86




RECOMMENDED  
PANEL CUTOUT  
SCALE: 2/1



SOLDER POT ACCEPTS  
A DIA WIRE

4. PANEL THK .120 MAX
3. FEMALE COAXIAL PUSH ON TYPE BULKHEAD JACK BOTH 50 & 75 OHM VERSIONS (BNC SIZE)
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES



QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ±.005 .XXXX ± ANGLES ±			<b>TROMPETER ELECTRONICS, INC.</b>		BJ120/UBJ120
DWN	JKR	9-6-73	MATERIAL	CODE IDENT	DRAWING NO.
CHK	<i>[Signature]</i>	10-5-73	—	<b>14949</b>	1005-0455
ENGR	<i>[Signature]</i>	10-9-73	DATE 10-9-73		REV
APPR	<i>[Signature]</i>	10/9/73	SCALE 4/1	DATE 10-9-73	D
NEXT ASSY			DATE 10-9-73		SHEET 1 OF 2