




- RoHS compliant* versions available (see How to Order “Termination” option)
- Low profile provides compatibility with DIPs
- Compatible with automatic insertion equipment
- Superior package integrity

- Now available with improved tolerance to $\pm 0.5\%$

4300R Series - Thick Film Molded SIPs

Resistance Range 10 ohms to 10 megohms
Maximum Operating Voltage 100 V
Temperature Coefficient of Resistance
50 Ω to 2.2 megohms..... ± 100 ppm/ $^{\circ}$ C
below 50 Ω ± 250 ppm/ $^{\circ}$ C
above 2.2 megohms..... ± 250 ppm/ $^{\circ}$ C
TCR Tracking..... 50 ppm/ $^{\circ}$ C
maximum; equal values
Resistor Tolerance..... See circuits
Operating Temperature
..... -55 $^{\circ}$ C to +125 $^{\circ}$ C
Power Rating Derate to zero
power from + 70 $^{\circ}$ C to + 125 $^{\circ}$ C
Insulation Resistance
..... 10,000 megohms minimum
Dielectric Withstanding Voltage
..... 200 VRMS
Lead Solderability..... Meet requirements
of MIL-STD-202 Method 208

TESTS PER MIL-STD-202.....	ΔR MAX.
Short Time Overload.....	±0.25 %
Load Life.....	±1.00 %
Moisture Resistance.....	±0.50 %
Resistance to Soldering Heat.....	±0.25 %
Terminal Strength.....	±0.25 %
Thermal Shock.....	±0.25 %

Flammability Conforms to UL94V-0
Lead Frame Material
.....Copper, solder coated
Body Material..... Novolac epoxy

43 06 R - 101 - 222

Model _____
(43 = Molded SIP)

Number of Pins _____

Physical Configuration _____
(R = Thick Film Low Profile)

Electrical Configuration _____

- 101 = Bussed
- 102 = Isolated
- 104 = Dual Terminator

Resistance Code _____

- First 2 digits are significant
- Third digit represents the number of zeros to follow.

Resistance Tolerance _____

- Blank = $\pm 2\%$ (see "Resistance Tolerance" on next page for resistance range)
- F = $\pm 1\%$ (100 ohms - 1 megohm)
- D = $\pm 0.5\%$ (100 ohms - 1 megohm)

Terminations _____


- All electrical configurations EXCEPT 104:
LF = Tin-plated (RoHS compliant version)
- ONLY electrical configuration 104:
L = Tin-plated (RoHS compliant version)
- Blank = Tin/Lead-plated

Consult factory for other available options.

Ambient Temperature (°C)	4311R (Watts)	4310R (Watts)	4309R (Watts)	4308R (Watts)	4306R (Watts)
0	1.45	1.35	1.25	1.15	0.75
25	1.45	1.35	1.25	1.15	0.75
70	1.45	1.35	1.25	1.15	0.75
125	0.00	0.00	0.00	0.00	0.00

4306R.....	0.75 watts
4308R.....	1.00 watts
4309R.....	1.13 watts
4310R.....	1.25 watts
4311R.....	1.38 watts

Represents total content. Layout may vary. Marking may be truncated on shorter versions due to size constraints.



For Standard Values Used in Capacitors, Inductors, and Resistors, [click here](#).

Technical drawing of a connector assembly showing dimensions and tolerances. The drawing includes a side view and a top view.

Side View Dimensions:

- Overall length: 27.53 MAX. (1.084)
- Distance from left face to center of PIN #1 REF.: 24.99 MAX. ($.984$)
- Distance from left face to center of PIN #1 REF. (alternative): 22.45 MAX. ($.884$)
- Distance from left face to center of PIN #1 REF. (alternative): 19.92 MAX. ($.784$)
- Distance from left face to center of PIN #1 REF. (alternative): 14.83 MAX. ($.584$)
- Distance from center of PIN #1 REF. to right face: 4.95 MAX. ($.195$)
- Left face dimension: $.407 + .102 / - .000$ ($.016 + .004 / - .000$)
- Right face dimension: $3.43 + .38 / - .25$ ($.135 + .015 / - .010$)
- Distance from left face to center of PIN #1 REF. (alternative): 1.02 .12 ($.040 \text{ .005}$)
- Distance from left face to center of PIN #1 REF. (alternative): $.483 \text{ .050 TYP.}$ ($.020 \text{ .002}$)
- Distance from left face to center of PIN #1 REF. (alternative): 2.54 .07 ($.100 \text{ .003}^*$) TYP. NON-ACCUM.

Top View Dimensions:

- Overall width: 2.16 .10 ($.085 \text{ .004}$)
- Distance from left face to center of PIN #1 REF.: 1.02 .05 ($.0425 \text{ .002}$)
- Distance from left face to center of PIN #1 REF. (alternative): $.254 \text{ .050}$ ($.010 \text{ .002}$)

*Terminal centerline to centerline measurements made at point of emergence of the lead from the body.

For information on specific applications,
download Bourns' application notes:


- [DRAM Applications](#)
- [Dual Terminator Resistor Networks](#)
- [R/2R Ladder Networks](#)
- [SCSI Applications](#)

4300R Series - Thick Film Molded SIPs

BOURNS®

Isolated Resistors (102 Circuit)

Model 4306R-102-RC (6 Pin)
Model 4308R-102-RC (8 Pin)
Model 4310R-102-RC (10 Pin)



These models incorporate 3, 4 or 5 isolated thick-film resistors of equal value, each connected between two pins.


Resistance Tolerance

10 ohms to 49 ohms..... ± 1 ohm
50 ohms to 5 megohms..... $\pm 2\%$ *
Above 5 megohms..... $\pm 5\%$

Power Rating per Resistor


At 70 °C 0.30 watt

Power Temperature Derating Curve



Bussed Resistors (101 Circuit)

Model 4306R-101-RC (6 Pin)
Model 4308R-101-RC (8 Pin)
Model 4309R-101-RC (9 Pin)
Model 4310R-101-RC (10 Pin)
Model 4311R-101-RC (11 Pin)



These models incorporate 5, 7, 8, 9 or 10 thick-film resistors of equal value, each connected between a separate pin.


Resistance Tolerance

10 ohms to 49 ohms..... ± 1 ohm
50 ohms to 5 megohms..... $\pm 2\%$ *
Above 5 megohms..... $\pm 5\%$

Power Rating per Resistor


At 70 °C 0.20 watt

Power Temperature Derating Curve



Dual Terminator (104 Circuit)

Model 4306R-104-R1/R2
Model 4308R-104-R1/R2 (shown)
Model 4309R-104-R1/R2
Model 4310R-104-R1/R2
Model 4311R-104-R1/R2



4308R-104 (shown above) is an 8-pin configuration and terminates 6 lines. Pins 1 and 8 are common for ground and power, respectively. Twelve thick-film resistors are paired in series between the common lines (pins 1 and 8).


Resistance Tolerance

Below 100 ohms ± 2 ohms
100 ohms to 5 megohms..... $\pm 2\%$ *
Above 5 megohms..... $\pm 5\%$

Power Rating per Resistor

At 70 °C 0.20 watt

Power Temperature Derating Curve



Popular Resistance Values (101, 102 Circuits)**

Ohms	Code	Ohms	Code	Ohms	Code	Ohms	Code	Ohms	Code
10	100	180	181	1,800	182	15,000	153	120,000	124
22	220	220	221	2,000	202	18,000	183	150,000	154
27	270	270	271	2,200	222	20,000	203	180,000	184
33	330	330	331	2,700	272	22,000	223	220,000	224
39	390	390	391	3,300	332	27,000	273	270,000	274
47	470	470	471	3,900	392	33,000	333	330,000	334
56	560	560	561	4,700	472	39,000	393	390,000	394
68	680	680	681	5,600	562	47,000	473	470,000	474
82	820	820	821	6,800	682	56,000	563	560,000	564
100	101	1,000	102	8,200	822	68,000	683	680,000	684
120	121	1,200	122	10,000	103	82,000	823	820,000	824
150	151	1,500	152	12,000	123	100,000	104	1,000,000	105

* Add "F" after resistance code for $\pm 1\%$ tolerance available from 100 Ω through 1M Ω , or add "D" after resistance code for $\pm 0.5\%$ tolerance available from 100 Ω through 1M Ω .

Part number suffix examples: -103 = 10K Ω , $\pm 2\%$; -103F = 10K Ω , $\pm 1\%$; -103D = 10K Ω , $\pm 0.5\%$

** Non-standard values available, within resistance range.

Popular Resistance Values (104 Circuit)**

Resistance			
Ohms		Code	
R ₁	R ₂	R ₁	R ₂
160	240	161	241
180	390	181	391
220	270	221	271
220	330	221	331
330	390	331	391
330	470	331	471
3,000	6,200	302	622

REV. 05/12

Specifications are subject to change without notice.
Customers should verify actual device performance in their specific applications.