


LED Assemblies



Bi-Color Assemblies




- Low Cost and Space Saving Design
- Standard Footprint
- Additional Configurations, See Pages 38-39
- Interlocking Versions Available

94V-0

U.L. RATED
MATERIALS

H-101CBC SERIES


T-1 (3mm) 90° Assembly



PART NO.	COLOR	PEAK(nm)	TYP VF	TYP IF	TYP mcd
H101CBC	RED	635	2.0	20mA	25.0
	GREEN	565	2.2	20mA	30.0
H101CBC-Y/G	YELLOW	585	2.1	20mA	20.0
	GREEN	565	2.2	20mA	30.0

H-178CBC SERIES


T-1 3/4 (5mm) 90° Assembly



PART NO.	COLOR	PEAK(nm)	TYP VF	TYP IF	TYP mcd
H178CBC	RED	635	2.0	20mA	35.0
	GREEN	565	2.2	20mA	45.0
H178CBC-Y/G	YELLOW	585	2.1	20mA	30.0
	GREEN	565	2.2	20mA	45.0

H-201CBC SERIES


T-1 (3mm) Bi-Level Assembly



PART NO.	COLOR	PEAK(nm)	TYP VF	TYP IF	TYP mcd
H201CBC	RED	635	2.0	20mA	25.0
	GREEN	565	2.2	20mA	30.0
H201CBC-Y/G	YELLOW	585	2.1	20mA	20.0
	GREEN	565	2.2	20mA	30.0

H-278CBC SERIES

T-1 3/4 (5mm) Bi-Level Assembly



PART NO.	COLOR	PEAK(nm)	TYP VF	TYP IF	TYP mcd
H278CBC	RED	635	2.0	20mA	35.0
	GREEN	565	2.2	20mA	45.0
H278CBC-Y/G	YELLOW	585	2.1	20mA	30.0
	GREEN	565	2.2	20mA	45.0

