



Bi-Level Variable T-1 (3mm) Centerline



- 5 Centerline Combinations
- Available With Recessed LEDs
- Design Your Own LED Assembly! See Page 64
- Additional Configurations, See Page 39

94V-0

U.L. RATED
MATERIALS

FOR TECHNICAL SPECIFICATIONS SEE PAGE 38

PART NO.	COLOR	PEAK (nm)	TYP VF	TYP IF	TYP mcd
H301CRD-XXX	RED	660	1.7	20mA	8.0
H301CGD-XXX	GREEN	565	2.1	20mA	15.0
H301CYD-XXX	YELLOW	585	2.2	20mA	18.0
H301CSR-XXX	SUPER RED	660	1.8	20mA	60.0
H301CHD-XXX	HE RED	635	1.8	20mA	40.0
H301CBWD-XXX	BLUE	430	5.0	20mA	15.0
LOW CURRENT					
H301CHDL-XXX	HE RED	635	1.8	2mA	2.5
H301CGDL-XXX	GREEN	565	1.8	2mA	2.5
H301CYDL-XXX	YELLOW	585	1.8	2mA	2.5
5 VOLT					
H301CHD5V-XXX	HE RED	635	5.0	10mA	15.0
H301CGD5V-XXX	GREEN	565	5.0	10mA	15.0
H301CYD5V-XXX	YELLOW	585	5.0	10mA	14.0

Available Centerlines

XXX	C/L 1	C/L 2	H
100	.100 (2.5)	.300 (7.6)	.415 (10.5)
120	.120 (3.0)	.320 (8.1)	.435 (11.0)
140	.140 (3.6)	.340 (8.6)	.455 (11.6)
160	.160 (4.1)	.360 (9.1)	.475 (12.1)
180	.180 (4.6)	.380 (9.7)	.495 (12.6)

EXAMPLES:

H301C GDL-120*

Centerline "C/L"
of .120(3.0mm)*
Low Current Green
Diffused LED

Series

*XXX= Centerline "C/L"

PART NO.	COLOR	PEAK (nm)	TYP VF	TYP IF	TYP mcd
H300CRD-XXX	RED	660	1.7	20mA	8.0
H300CGD-XXX	GREEN	565	2.1	20mA	15.0
H300CYD-XXX	YELLOW	585	2.2	20mA	18.0
H300CSR-XXX	SUPER RED	660	1.8	20mA	60.0
H300CHD-XXX	HE RED	635	1.8	20mA	40.0
H300CBWD-XXX	BLUE	430	5.0	20mA	15.0
LOW CURRENT					
H300CHDL-XXX	HE RED	635	1.8	2mA	2.5
H300CGDL-XXX	GREEN	565	1.8	2mA	2.5
H300CYDL-XXX	YELLOW	585	1.8	2mA	2.5
5 VOLT					
H300CHD5V-XXX	HE RED	635	5.0	10mA	15.0
H300CGD5V-XXX	GREEN	565	5.0	10mA	15.0
H300CYD5V-XXX	YELLOW	585	5.0	10mA	14.0

Available Centerlines

XXX	C/L 1	C/L 2	H
100	.100 (2.5)	.300 (7.6)	.415 (10.5)
120	.120 (3.0)	.320 (8.1)	.435 (11.0)
140	.140 (3.6)	.340 (8.6)	.455 (11.6)
160	.160 (4.1)	.360 (9.1)	.475 (12.1)
180	.180 (4.6)	.380 (9.7)	.495 (12.6)

EXAMPLES:

H300C GD-100*


Centerline "C/L"
of .100(2.5mm)*
Green Diffused LED

Series

*XXX= Centerline "C/L"

H301C SERIES

T-1 (3mm) Bi-Level Variable Centerline



H300C SERIES

T-1 (3mm) Bi-Level Variable Centerline

