



Features


- High inductance up to 47 mH
- High Q level
- RoHS compliant*

FSR1013 Series - Radial Shielded Inductors

Materials

Core	Ferrite POT core
Wire	Enameled copper wire
Bobbin	Phenolic
Terminal	Cu/Sn
Adhesive	Epoxy resin
Temperature Rise	40 °C max. at rated current
Operating Temperature	-40 °C to +105 °C
Storage Temperature	-40 °C to +105 °C
Packaging	110 pcs. per bag

Dimensions



Electrical Characteristics

BOURNS Part No.	Inductance (mH)	Q min.	Test freq. (Hz)		SRF (kHz) min.	RDC (Ω) max.	Rated Curr. IDC (mA)
			L	Q			
FSR 1013-102KL	1.0 ± 10 %	40	1 k	252.0 k	740	4.0	150
FSR 1013-122KL	1.2 ± 10 %	40	1 k	252.0 k	670	5.0	140
FSR 1013-152KL	1.5 ± 10 %	40	1 k	252.0 k	500	6.0	130
FSR 1013-182KL	1.8 ± 10 %	40	1 k	252.0 k	480	7.0	115
FSR 1013-222KL	2.2 ± 10 %	40	1 k	252.0 k	410	10.0	100
FSR 1013-272KL	2.7 ± 10 %	40	1 k	252.0 k	390	11.0	95
FSR 1013-332KL	3.3 ± 10 %	30	1 k	252.0 k	350	12.0	85
FSR 1013-392KL	3.9 ± 10 %	30	1 k	252.0 k	340	13.0	80
FSR 1013-472KL	4.7 ± 10 %	30	1 k	252.0 k	320	23.0	70
FSR 1013-562KL	5.6 ± 10 %	30	1 k	252.0 k	310	25.0	65
FSR 1013-682KL	6.8 ± 10 %	20	1 k	252.0 k	280	30.0	60
FSR 1013-822KL	8.2 ± 10 %	20	1 k	252.0 k	260	32.0	50
FSR 1013-103KL	10.0 ± 10 %	50	1 k	79.6 k	240	35.0	45
FSR 1013-123KL	12.0 ± 10 %	50	1 k	79.6 k	210	50.0	40
FSR 1013-153KL	15.0 ± 10 %	50	1 k	79.6 k	190	58.0	38
FSR 1013-183KL	18.0 ± 10 %	50	1 k	79.6 k	180	63.0	35
FSR 1013-223KL	22.0 ± 10 %	40	1 k	79.6 k	140	90.0	30
FSR 1013-273KL	27.0 ± 10 %	40	1 k	79.6 k	130	100.0	28
FSR 1013-333KL	33.0 ± 10 %	40	1 k	79.6 k	125	115.0	25
FSR 1013-393KL	39.0 ± 10 %	30	1 k	79.6 k	120	185.0	23
FSR 1013-473KL	47.0 ± 10 %	30	1 k	79.6 k	110	205.0	22

REV. 09/09

*RoHS Directive 2002/95/EC Jan 27 2003 including Annex

Specifications are subject to change without notice.

Customers should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[FSR1013-153K](#) [FSR1013-392K](#) [FSR1013-332K](#) [FSR1013-472K](#) [FSR1013-222K](#) [FSR1013-473K](#) [FSR1013-152K](#)
[FSR1013-122KL](#) [FSR1013-562KL](#) [FSR1013-393KL](#) [FSR1013-682KL](#) [FSR1013-272KL](#) [FSR1013-182KL](#) [FSR1013-](#)
[273KL](#) [FSR1013-102KL](#) [FSR1013-103KL](#) [FSR1013-123KL](#) [FSR1013-152KL](#) [FSR1013-153KL](#) [FSR1013-183KL](#)
[FSR1013-222KL](#) [FSR1013-223KL](#) [FSR1013-332KL](#) [FSR1013-333KL](#) [FSR1013-392KL](#) [FSR1013-472KL](#) [FSR1013-](#)
[473KL](#) [FSR1013-822KL](#) [FSR1013-102K](#) [FSR1013-183K](#) [FSR1013-103K](#) [FSR1013-223K](#) [FSR1013-822K](#)
[FSR1013-123K](#) [FSR1013-333K](#)