


| REV. | DATE     | DESCRIPTION                                | BY  | C'K'D. |
|------|----------|--------------------------------------------|-----|--------|
| 24   | 03-23-93 | DELETED FIG. 2, REDRAWN TO CAD PER PCN 872 | DGF | RER    |

FIGURE 1



|                   |                |                               | HAND TOOL OR HYDRAULIC<br>7 CONNECTOR PROGRAM  |                                        |                                       |                                        |                                       |                                        | HYDRAULIC TOOL ONLY<br>4 CONNECTOR PROGRAM |                                       |                                        |                                        |                                        |       |
|-------------------|----------------|-------------------------------|------------------------------------------------|----------------------------------------|---------------------------------------|----------------------------------------|---------------------------------------|----------------------------------------|--------------------------------------------|---------------------------------------|----------------------------------------|----------------------------------------|----------------------------------------|-------|
| CATALOG NUMBER    |                |                               | YH0-100                                        | YH0-150                                | YHD-200                               | YHD-250                                | YHD-300                               | YHD-350                                | YHD-400                                    | YH0-125                               | YHD-250                                | YHD-350                                | YHD-400                                |       |
| FIGURE NUMBER     |                |                               | 1                                              | 1                                      | 1                                     | 1                                      | 1                                     | 1                                      | 1                                          | 1                                     | 1                                      | 1                                      | 1                                      |       |
| ACCOMMODATES      | GROOVE A (RUN) | ACSR                          | #6 - #2                                        | #3 - 1/0                               | 1/0 - 2/0                             | 3/0 - 4/0                              | #1 - 2/0                              | 3/0 - 4/0                              | 3/0 - 4/0                                  | #6 - 1/0                              | #1 - 4/0                               | #1 - 4/0                               | 2/0 - 4/0                              |       |
|                   |                | STR. CU. OR AL.               | #6-#4-#1-7STR                                  | #3 3STR - 2/0                          | 2/0 - 3/0                             | 4/0                                    | #1 3STR - 3/0                         | 3/0 - 4/0                              | 3/0 - 4/0                                  | #6 - 1/0                              | #13STR - 4/0                           | #13STR - 4/0                           | 3/0 - 4/0                              |       |
|                   |                | SOL. CU. OR AL.               | #6-#4-#3-#1                                    | #1 - 2/0                               | 3/0 -4/0                              | 250 -300                               | 2/0 - 4/0                             | 250 - 300                              | 250 - 300                                  | #6 - 2/0                              | 2/0 - 300                              | 2/0 - 300                              | 4/0 - 300                              |       |
|                   |                | COMPACT ACSR                  | #6-#4-#1                                       | #2 - 1/0                               | 2/0 - 3/0                             | 4/0-266 18/1                           | 1/0 - 3/0                             | 3/0-266 18/1                           | 3/0-266 18/1                               | #6 - 1/0                              | 1/0-266 18/1                           | 1/0-266 18/1                           | 3/0-266 18/1                           |       |
|                   |                | COMPACT STR CU OR AL          | #6-#4-#3-#1                                    | #2 - 2/0                               | 3/0                                   | 4/0 - 266                              | 1/0 - 3/0                             | 4/0 - 266                              | 4/0 - 266                                  | #6 - 2/0                              | 1/0 - 266                              | 1/0 - 266                              | 3/0 - 266                              |       |
|                   |                | METRIC CABLE RANGE CU. OR AL. | 16mm <sup>2</sup> - 35mm <sup>2</sup>          | 25mm <sup>2</sup> - 70 mm <sup>2</sup> | 60mm <sup>2</sup> - 85mm <sup>2</sup> | 85mm <sup>2</sup> - 120mm <sup>2</sup> | 50mm <sup>2</sup> - 85mm <sup>2</sup> | 85mm <sup>2</sup> - 120mm <sup>2</sup> | 85mm <sup>2</sup> - 120mm <sup>2</sup>     | 16mm <sup>2</sup> - 60mm <sup>2</sup> | 50mm <sup>2</sup> - 120mm <sup>2</sup> | 50mm <sup>2</sup> - 120mm <sup>2</sup> | 70mm <sup>2</sup> - 120mm <sup>2</sup> |       |
|                   |                | WIRE DIA. RANGE (in)          | .332 - .162                                    | .419 - .260                            | .470 - .398                           | .563 - .475                            | .470 - .336                           | .563 - .461                            | .563 - .461                                | .398-.162                             | .563 - .336                            | .563 - .336                            | .563 - .414                            |       |
|                   |                | WIRE DIA. RANGE (mm)          | [8.4 -4.1]                                     | [10.6 - 6.6]                           | [11.9 - 10.1]                         | [14.3 - 11.7]                          | [11.9 - 8.5]                          | [14.3 - 11.7]                          | [14.3 - 11.7]                              | [10.1 - 4.13]                         | [14.3 - 8.5]                           | [14.3 - 8.5]                           | [14.3 - 10.5]                          |       |
|                   | GROOVE B (TAP) | ACSR                          | #6 - #2                                        | #6 - #2                                | #6 - #2                               | #6 - #2                                | #1 - 2/0                              | #1 - 2/0                               | 3/0 - 4/0                                  | #6 - #2                               | #6 - #2                                | #1 - 2/0                               | 2/0 - 4/0                              |       |
|                   |                | STR. CU. OR AL.               | #6-#4-#1-7STR                                  | #6-#1 19STR                            | #6-#1 19STR                           | #6-#1 19STR                            | #1 3STR - 2/0                         | #1 3STR - 2/0                          | 3/0 - 4/0                                  | #6-#1 19STR                           | #6-#1 19STR                            | #13STR - 2/0                           | 3/0 - 4/0                              |       |
|                   |                | SOL. CU. OR AL.               | #6-#4-#3-#1                                    | #6 - 1/0                               | #6 - 1/0                              | #6 - 1/0                               | 2/0 - 3/0                             | 2/0 - 3/0                              | 250 - 300                                  | #6 - 1/0                              | #6 - 1/0                               | 2/0 - 3/0                              | 4/0 - 300                              |       |
|                   |                | COMPACT ACSR                  | #6-#4-#1                                       | #6 - #1                                | #6 - #1                               | #6 - #1                                | 1/0 - 2/0                             | 1/0 - 2/0                              | 3/0-266 18/1                               | #6 - #1                               | #6 - #1                                | 1/0 - 2/0                              | 3/0-266 18/1                           |       |
|                   |                | COMPACT STR CU OR AL          | #6-#4-#3-#1                                    | #6 - #1                                | #6 - #1                               | #6 - #1                                | 1/0 - 3/0                             | 1/0 - 3/0                              | 4/0 - 266                                  | #6 - #1                               | #6 - #1                                | 1/0 - 3/0                              | 3/0 - 266                              |       |
|                   |                | METRIC CABLE RANGE CU. OR AL. | 16mm <sup>2</sup> - 35mm <sup>2</sup>          | 16mm <sup>2</sup> - 35mm <sup>2</sup>  | 16mm <sup>2</sup> - 35mm <sup>2</sup> | 16mm <sup>2</sup> - 35mm <sup>2</sup>  | 50mm <sup>2</sup> - 80mm <sup>2</sup> | 50mm <sup>2</sup> - 80mm <sup>2</sup>  | 85mm <sup>2</sup> - 120mm <sup>2</sup>     | 16mm <sup>2</sup> - 35mm <sup>2</sup> | 16mm <sup>2</sup> - 35mm <sup>2</sup>  | 50mm <sup>2</sup> - 80mm <sup>2</sup>  | 70mm <sup>2</sup> - 120mm <sup>2</sup> |       |
| INSTALLATION DATA | Y45            | WIRE DIA. RANGE (in)          | .332 - .162                                    | .332 - .162                            | .332 - .162                           | .332 - .162                            | .447 - .336                           | .447 - .336                            | .563 - .461                                | .333 - .162                           | .333 - .162                            | .447 - .336                            | .563 - .414                            |       |
|                   |                | WIRE DIA. RANGE (mm)          | [8.4 -4.1]                                     | [8.4 -4.1]                             | [8.4 -4.1]                            | [8.4 -4.1]                             | [11.4 - 8.5]                          | [11.4 - 8.5]                           | [14.3 - 11.7]                              | [8.4 - 4.1]                           | [8.4 - 4.1]                            | [11.4 - 8.5]                           | [14.3 - 10.5]                          |       |
|                   |                | H                             | 1.12 [28.4]                                    | 1.12 [28.4]                            | 1.44 [36.6]                           | 1.45 [36.8]                            | 1.42 [36.1]                           | 1.42 [36.1]                            | 1.40 [35.6]                                | 1.15 [29.2]                           | 1.47 [37.3]                            | 1.42 [36.1]                            | 1.40 [35.6]                            |       |
|                   |                | L                             | 1.50 [38.1]                                    | 1.75 [44.5]                            | 1.88 [47.8]                           | 1.88 [47.8]                            | 1.88 [47.8]                           | 2.50 [63.5]                            | 2.50 [63.5]                                | 1.62 [41.1]                           | 1.88 [47.8]                            | 2.50 [63.5]                            | 2.50 [63.5]                            |       |
|                   | Y46            | W                             | .70 [17.8]                                     | .70 [17.8]                             | .89 [22.6]                            | .89 [22.6]                             | .89 [22.6]                            | .89 [22.6]                             | .84 [21.3]                                 | .70 [17.78]                           | .89 [22.6]                             | .89 [22.6]                             | .89 [22.6]                             |       |
|                   |                | DIE INDEX                     | 0                                              | 0                                      | D3                                    | D3                                     | D3                                    | D3                                     | D3                                         | -----                                 | -----                                  | -----                                  | -----                                  |       |
|                   |                | DIE SET                       | PERMANENT DIES IN MD6-8 TOOL INSTALL ALL SIZES |                                        |                                       |                                        |                                       |                                        |                                            |                                       | -----                                  | -----                                  | -----                                  | ----- |
|                   |                | NO. OF CRIMPS                 | 4                                              | 5                                      | 5                                     | 5                                      | 5                                     | 6                                      | 7                                          | -----                                 | -----                                  | -----                                  | -----                                  |       |
|                   |                | DIE INDEX                     | 0                                              | 0                                      | D3                                    | D3                                     | D3                                    | D3                                     | D3                                         | 0                                     | D3                                     | D3                                     | D3                                     |       |
|                   |                | DIE SET                       | U-0                                            | U-0                                    | U-D3                                  | U-D3                                   | U-D3                                  | U-D3                                   | U-D3                                       | U-0                                   | U-D3                                   | U-D3                                   | U-D3                                   |       |
|                   |                | NO. OF CRIMPS                 | 2                                              | 2                                      | 2                                     | 2                                      | 2                                     | 3                                      | 3                                          | 2                                     | 2                                      | 3                                      | 3                                      |       |
|                   |                | DIE INDEX                     | 0                                              | 0                                      | D3                                    | D3                                     | D3                                    | D3                                     | D3                                         | 0                                     | D3                                     | D3                                     | D3                                     |       |
|                   |                | DIE SET                       | U-0                                            | U-0                                    | U-D3                                  | U-D3                                   | U-D3                                  | U-D3                                   | U-D3                                       | U-0                                   | U-D3                                   | U-D3                                   | U-D3                                   |       |
|                   |                | NO. OF CRIMPS                 | 2                                              | 2                                      | 2                                     | 2                                      | 2                                     | 3                                      | 3                                          | 2                                     | 2                                      | 3                                      | 3                                      |       |

1. MATERIAL: ALUMINUM

2. FOR CONDUCTOR COMBINATIONS OF AL TO AL OR AL TO CU.

3. U-DIES MAY BE USED WITH ADAPTER CAT. # 'PT6515' FOR Y45 &amp; 'P-UADP-1' FOR Y46.

4. FOR MD6 TOOL USE W-0 DIE INSERT, D3 DIE GROOVE IS PERMANENT.

5. EACH CONNECTOR INDIVIDUALLY BOXED.

6. ALL DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS.

| HYCRIMP TAP                                                                           |  |                        |                    |
|---------------------------------------------------------------------------------------|--|------------------------|--------------------|
| CAT NO: YH--- (TABLE)                                                                 |  |                        | SCALE<br>FULL SIZE |
| DRAWN: W.A.H                                                                          |  | 03-28-72               |                    |
| DSGN APPVL: 03-30-72                                                                  |  | CHECKED: OKR 03-28-72  |                    |
| Q.A. APPVL: .                                                                         |  | MFG APPVL: ESR 3-30    |                    |
| CAD FILE: SD73376-SHT01                                                               |  | MKTG APPVL: .          |                    |
|  |  | PM REF: N/A            |                    |
|                                                                                       |  | MDL REF: N/A           |                    |
| U.S. ELECTRICAL DIVISION<br>MANCHESTER, NH 03108                                      |  | PROJECT: .             |                    |
|                                                                                       |  | DRAWING NO.<br>SD73376 |                    |
|                                                                                       |  | SHEET 1 OF 2           | REV<br>24          |

| REV. | DATE    | DESCRIPTION                   | BY  | C'K'D. |
|------|---------|-------------------------------|-----|--------|
| 24   | 3-23-93 | REDRAWN TO CAD<br>PER PCN 872 | DGF | REB    |




FIG. 1




FIG. 2




FIG. 3

|                                                                                                       |                                                                                         |                      | 'N' DIE CONNECTORS |               |               |               |                  | 'R' DIE CONNECTORS                                                                    |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                     |
|-------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|----------------------|--------------------|---------------|---------------|---------------|------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------|
| CATALOG NUMBER       |                                                                                         |                      | YHN-450            | YHN-500       | YHN-525       | YHN-550       | YHN-600          | YHR-700                                                                               | YHR-750                                                                               | YHR-800                                                                               | YHR-850                                                                               | YHR-900                                                                               | YHR-950             |
| FIGURE NUMBER                                                                                         |                                                                                         |                      | 1                  | 1             | 3             | 1             | 2                | 1                                                                                     | 1                                                                                     | 1                                                                                     | 1                                                                                     | 1                                                                                     | 3                   |
| ACCOMMODATES         | GROOVE A (RUN)                                                                          | ACSR                 | 4/0-397.5 18/1     | 4/0-477 18/1  | 4/0-477 18/1  | 266-477 18/1  | 266-477 18/1     | 300-556 18/1                                                                          | 300-556 18/1                                                                          | 556.5 18/1-795 26/7                                                                   | 556.5 18/1-795 26/7                                                                   | 556.5 18/1-795 26/7                                                                   | 336.4 18/1-954 45/7 |
|                                                                                                       |                                                                                         | STR. CU. OR AL.      | 4/0 - 400          | 4/0 - 500     | 4/0 - 500     | 250 - 500     | 250 - 500        | 336 - 600                                                                             | 336 - 600                                                                             | 600 - 900                                                                             | 600 - 900                                                                             | 600 - 900                                                                             | 336.4 - 1000        |
|                                                                                                       |                                                                                         | SOL. CU. OR AL.      | -----              | -----         | -----         | -----         | -----            | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----               |
|                                                                                                       |                                                                                         | COMPACT ACSR         | 266.8-477 18/1     | 266.8 - 556.5 | 266.8 - 556.5 | 300 - 556.5   | 300 - 556.5      | 397 - 636                                                                             | 397 - 636                                                                             | 795 - 954                                                                             | 795 - 954                                                                             | 795 - 954                                                                             | -----               |
|                                                                                                       |                                                                                         | COMPACT STR CU OR AL | 250 - 500          | 250 - 556     | 250 - 556     | 300 - 556     | 300 - 556        | 477 - 636                                                                             | 477 - 636                                                                             | 795 - 954                                                                             | 795 - 954                                                                             | 795 - 954                                                                             | -----               |
|                                                                                                       |                                                                                         |                      |                    |               |               |               |                  |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                     |
|                                                                                                       |                                                                                         | WIRE DIA. RANGE (in) | .743 - .522        | .814 - .522   | .814 - .522   | .814 - .573   | .814 - .574      | .893 - .666                                                                           | .893 - .666                                                                           | 1.108 - .879                                                                          | 1.108 - .879                                                                          | 1.108 - .879                                                                          | 1.165 - .666        |
|                                                                                                       | WIRE DIA. RANGE (mm)                                                                    | [18.9 - 13.3]        | [20.7 - 13.3]      | [20.7 - 13.3] | [20.7 - 14.6] | [20.7 - 14.6] | [22.7 - 16.9]    | [22.7 - 16.9]                                                                         | [28.1 - 22.3]                                                                         | [28.1 - 22.3]                                                                         | [28.1 - 22.3]                                                                         | [29.6 - 16.9]                                                                         |                     |
|                                                                                                       | GROOVE B (TAP)                                                                          | ACSR                 | 4/0-397.5 18/1     | #6 - 2/0      | 4/0-477 18/1  | 2/0 - 4/0     | 266.8-336.4 18/1 | 1/0-336.4 18/1                                                                        | 300-556 18/1                                                                          | 1/0-336.4 18/1                                                                        | 300-556 18/1                                                                          | 556.5 18/1-795 26/7                                                                   | 336.4 18/1-954 45/7 |
|                                                                                                       |                                                                                         | STR. CU. OR AL.      | 4/0 - 400          | #6 - 2/0      | 4/0 - 500     | 2/0 - 4/0     | 250 - 350        | 2/0 - 350                                                                             | 336 - 600                                                                             | 2/0 - 350                                                                             | 336 - 600                                                                             | 600 - 900                                                                             | 336.4 - 1000        |
|                                                                                                       |                                                                                         | SOL. CU. OR AL.      | 336 - 477          | #6 - 3/0      | -----         | 3/0 - 300     | 336 - 400        | 3/0 - 350                                                                             | -----                                                                                 | 3/0 - 350                                                                             | -----                                                                                 | -----                                                                                 | -----               |
|                                                                                                       |                                                                                         | COMPACT ACSR         | 266.8 477 18/1     | #6 - 2/0      | 266.8 - 556.5 | 2/0 - 266.8   | 300 - 397.5      | 2/0-397.5 18/1                                                                        | 397 - 636                                                                             | 2/0-397.5 18/1                                                                        | 397 - 636                                                                             | 795 - 954                                                                             | -----               |
|                                                                                                       |                                                                                         | COMPACT STR CU OR AL | 250 - 500          | #6 - 3/0      | 250 - 556     | 3/0 - 266.8   | 300 - 397.5      | 3/0 - 397.5                                                                           | 477 - 636                                                                             | 3/0 - 397.5                                                                           | 477 - 636                                                                             | 795 - 954                                                                             | -----               |
|                                                                                                       |                                                                                         |                      |                    |               |               |               |                  |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                                                                                       |                     |
| WIRE DIA. RANGE (in)                                                                                  |                                                                                         | .743 - .522          | .447 - .162        | .814 - .522   | .563 - .410   | .684 - .574   | .684 - .398      | .893 - .666                                                                           | .684 - .398                                                                           | .893 - .666                                                                           | 1.108 - .879                                                                          | 1.165 - .666                                                                          |                     |
| WIRE DIA. RANGE (mm)                                                                                  | [18.9 - 13.3]                                                                           | [11.4 - 4.1]         | [20.7 - 13.3]      | [14.3 - 10.4] | [17.4 - 14.6] | [17.4 - 10.1] | [22.7 - 16.9]    | [17.4 - 10.1]                                                                         | [22.7 - 16.9]                                                                         | [28.1 - 22.3]                                                                         | [29.6 - 16.9]                                                                         |                                                                                       |                     |
| H                                                                                                     |                                                                                         |                      | 2.05 [11.1]        | 2.00 [50.8]   | 1.824 [46.3]  | 1.96 [49.8]   | 2.00 [50.8]      | 3.04 [77.2]                                                                           | 3.04 [77.2]                                                                           | 3.05 [77.5]                                                                           | 3.04 [77.2]                                                                           | 2.97 [75.4]                                                                           | 3.14 [79.8]         |
| L                                                                                                     |                                                                                         |                      | 3.50 [88.9]        | 2.00 [50.8]   | 4.50 [114.3]  | 2.00 [50.8]   | 3.50 [88.9]      | 3.50 [88.9]                                                                           | 4.62 [117.3]                                                                          | 3.50 [88.9]                                                                           | 4.62 [117.3]                                                                          | 4.62 [117.3]                                                                          | 6.00 [152.4]        |
| W                                                                                                     |                                                                                         |                      | 1.25 [31.8]        | 1.28 [32.5]   | 1.23 [31.2]   | 1.28 [32.5]   | 1.28 [32.5]      | 1.74 [44.2]                                                                           | 1.74 [44.2]                                                                           | 1.74 [44.2]                                                                           | 1.74 [44.2]                                                                           | 1.74 [44.2]                                                                           | 1.66 [42.2]         |
| INSTALLATION DATA  | Y45  | DIE INDEX            | N                  | N             | N             | N             | N                | KR                                                                                    | KR                                                                                    | KR                                                                                    | KR                                                                                    | KR                                                                                    | KR                  |
|                                                                                                       |                                                                                         | DIE SET              | P-N                | P-N           | P-N           | P-N           | P-N              | P-KR                                                                                  | P-KR                                                                                  | P-KR                                                                                  | P-KR                                                                                  | P-KR                                                                                  | P-KR                |
|                                                                                                       |                                                                                         | NO. OF CRIMPS        | 3                  | 2             | 3             | 2             | 3                | 3                                                                                     | 4                                                                                     | 3                                                                                     | 4                                                                                     | 4                                                                                     | 5                   |
|                                                                                                       | Y46  | DIE INDEX            | N                  | N             | N             | N             | N                | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----               |
|                                                                                                       |                                                                                         | DIE SET              | U-N                | U-N           | U-N           | U-N           | U-N              | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----               |
|                                                                                                       |                                                                                         | NO. OF CRIMPS        | 3                  | 2             | 3             | 2             | 3                | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----                                                                                 | -----               |
|                                                                                                       | Y45  | DIE INDEX            | N                  | N             | N             | N             | N                | KR, T OR Z                                                                            | KR, T OR Z                                                                            | KR, T OR Z                                                                            | KR, T OR Z                                                                            | KR, T OR Z                                                                            | KR                  |
|                                                                                                       |                                                                                         | DIE SET              | S-N                | S-N           | S-N           | S-N           | S-N              | S-KR, S-T, S-Z                                                                        | S-KR, S-T, S-Z                                                                        | S-KR, S-T, S-Z                                                                        | S-KR, S-T, S-Z                                                                        | S-KR, S-T, S-Z                                                                        | S-KR                |
|                                                                                                       |                                                                                         | NO. OF CRIMPS        | 3                  | 2             | 3             | 2             | 3                | 3  | 4  | 3  | 4  | 4  | 5                   |

1. MATERIAL: ALUMINUM

2. FOR CONDUCTOR COMBINATIONS OF AL TO AL OR AL TO CU.

3. U-DIES MAY BE USED WITH ADAPTER CAT. # 'PT6515' FOR Y45 &amp; 'P-UADP-1' FOR Y46.

4. FOR MD6 TOOL USE W-0 DIE INSERT, D3 DIE GROOVE IS PERMANENT.

5. EACH CONNECTOR INDIVIDUALLY BOXED.

6. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS.

REFERENCE: FD73192

| HYCRIMP TAP             |          |                 |          |
|-------------------------|----------|-----------------|----------|
| CAT NO. YH--            | (TABLE)  | SCALE           | NTS      |
| DRAWN: W.A.H.           | 03-28-72 | CHECKED: A.K.R. | 03-29-72 |
| DSGN APPVL: E.S.R.      | 03-30-72 | MFG APPVL:      |          |
| Q.A. APPVL:             |          | MKTG APPVL:     |          |
| CAD FILE: SD73376-SHT02 |          | PM REF: N/A     |          |
|                         |          | MDL REF: N/A    |          |
|                         |          | PROJECT:        |          |
| DRAWING NO.             |          | REV             |          |
| SD73376                 |          | 24              |          |
| SHEET 2 OF 2            |          |                 |          |