


# 2M-Series

## MINIATURE TOGGLES

The 2M family of miniature toggle switches is composed of three switch series; the **2M1-Series** miniature toggle switch, the **2MS-Series** sealed miniature toggle switch, and the **2M1H-Series** premium sealed miniature toggle switch. These series all feature PC mounting and offer a variety of ratings, circuits, contact materials, terminal platings, toggle styles and lengths, and optional color caps.



2M1H-Series



2MS-Series



2M1-Series

### Product Highlights:

- IP67 Sealing
- 8 Single and Double Pole Circuits
- Long, Short and Flatted Bushing Options
- Large Variety of Termination Options
- Available Gold, Silver and Tin Platings
- UL Approved
- Sleek Black Finish

### Typical Applications:

- Telecommunications
- Instrumentation
- Networking
- Medical Equipment
- Military Communications

### Resources:

[Configure a Complete Part](#)

[\*\*Download CAD & Sales Drawing >\*\*](#)



**Carling Technologies®**


Innovative Designs. Powerful Solutions.

**Carling Technologies, Inc.**  
60 Johnson Avenue, Plainville, CT 06062  
Email: [sales@carlingtech.com](mailto:sales@carlingtech.com)  
Application Support: [team2@carlingtech.com](mailto:team2@carlingtech.com)  
Phone: 860.793.9281 Fax: 860.793.9231


[www.carlingtech.com](http://www.carlingtech.com)



**2M1H-Series**  
Premium Sealed  
Miniature  
Toggle Switch



**2MS-Series**  
Sealed  
Miniature  
Toggle Switch



**2M1-Series**  
Miniature  
Toggle Switch

## Electrical

|                       |                                                                              |
|-----------------------|------------------------------------------------------------------------------|
| Contact Rating        | refer to ordering scheme                                                     |
| Electrical Life       | 50,000 make & break cycles @ full load                                       |
| Contact Resistance    | 10 mΩ max. initial @ 2-4 VDC<br>100mA for both silver & gold plated contacts |
| Insulation Resistance | 1000 MΩ min.                                                                 |
| Dielectric Strength   | 1500 Volts RMS @ sea level                                                   |

## Physical

|                        |                                                     |
|------------------------|-----------------------------------------------------|
| Operating Temperature  | -30°C to +85°C                                      |
| Index of Protection    | <i>2M1H-Series:</i> IP67<br><i>2MS-Series:</i> IP67 |
| Solder Heat Resistance | MIL-STD-202, Method 210                             |
| Actuator Travel        | 25°                                                 |

## Material

|                         |                                                                                                                                                                                               |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Case                    | <i>2M1H-Series &amp; 2M1-Series:</i> Dially phthalate (DAP) (UL 94V-0)<br><i>2MS-Series:</i> Glass filled nylon 6/6, flame retardant, heat stabilized (UL 94V-0)                              |
| Toggle                  | <i>2M1H-Series:</i> Brass, black finish with o-ring seal<br><i>2MS-Series:</i> Brass, chrome plated, internal o-ring sealed<br><i>2M1-Series:</i> Brass, chrome plated                        |
| Bushing                 | <i>2M1H-Series:</i> Brass, black finish with o-ring seal<br><i>2MS-Series:</i> Glass filled nylon 6/6, flame retardant, heat stabilized (UL 94V-0)<br><i>2M1-Series:</i> Brass, nickel plated |
| Housing                 | Stainless Steel                                                                                                                                                                               |
| Bracket                 | <i>2MS-Series:</i> Nylon (UL 94V-0)<br><i>2M1-Series:</i> Stainless Steel                                                                                                                     |
| Actuator Pivot Retainer | <i>2MS-Series:</i> Stainless Steel                                                                                                                                                            |
| Switch Support          | Brass, tin plated                                                                                                                                                                             |
| Terminal Seal           | Epoxy                                                                                                                                                                                         |

**2M1H** - **DP1** - **TJ** - **BK** - **M2** **R** **E**

1 Series      2 Pole / Circuit      3 Actuator Style      4 Bushing      5 Termination      6 Contacts      7 Seal

### 1 SERIES

**2M1H** Premium Sealed Miniature Toggle Switch

### 2 POLE / CIRCUIT

( ) - momentary

| Position: | 1        | 2                   | 3        |
|-----------|----------|---------------------|----------|
|           | 2-3, 5-6 | Connected Terminals | 2-1, 5-4 |
| SP1       | ON       | NONE                | ON       |
| SP2       | ON       | NONE                | (ON)     |
| SP3       | ON       | OFF                 | ON       |
| SP4       | (ON)     | OFF                 | (ON)     |
| SP5       | ON       | OFF                 | (ON)     |
| DP1       | ON       | NONE                | ON       |
| DP2       | ON       | NONE                | (ON)     |
| DP3       | ON       | OFF                 | ON       |
| DP4       | (ON)     | OFF                 | (ON)     |
| DP5       | ON       | OFF                 | (ON)     |
| DP6 *     | ON       | ON                  | ON       |
| DP7 *     | (ON)     | ON                  | (ON)     |
| DP8 *     | ON       | ON                  | (ON)     |

\*Center position connects 2-3, 5-4

### 3 ACTUATOR STYLE

**TJ** .709" [18 mm] length      **TK** .512" [13.00 mm] length

### 4 BUSHING

**BK** .386" [9.80 mm] threaded, flat

### 5 TERMINATION <sup>7</sup>

|           |               |            |                                    |
|-----------|---------------|------------|------------------------------------|
| <b>M1</b> | Solder Lug    | <b>M51</b> | Wire Wrap, .750" [19.05mm] length  |
| <b>M2</b> | PCB           | <b>M52</b> | Wire Wrap, .964" [24.48mm] length  |
| <b>M3</b> | Quick Connect | <b>M53</b> | Wire Wrap, .425" [10.80mm] length  |
|           |               | <b>M54</b> | Wire Wrap, 1.062" [25.97mm] length |

### 6 CONTACTS / TERMINALS

|          | Contact Material    | Terminal Plating    | Rating                        | Approvals |
|----------|---------------------|---------------------|-------------------------------|-----------|
| <b>G</b> | silver <sup>1</sup> | gold over silver    | 5A 125VAC or 28VDC, 2A 250VAC | IP67      |
| <b>K</b> | gold 2,5            | tin 4,7             | 0.4VA max 20V max (AC/DC)     | IP67      |
| <b>P</b> | silver 1,6          | tin 4,7             | 5A 125VAC or 28VDC, 2A 250VAC | IP67      |
| <b>Q</b> | silver <sup>1</sup> | silver <sup>1</sup> | 5A 125VAC or 28VDC, 2A 250VAC | IP67      |
| <b>R</b> | gold <sup>2</sup>   | gold <sup>3</sup>   | 0.4VA max 20V max (AC/DC)     | IP67      |

### 7 EPOXY SEAL

**E** Epoxy Seal

#### Notes:

Switches supplied with (1) 2M1-HDW4 hex nut and (1) 3MNH-WCP-0872 O-Ring

- Movable contact and terminal platings: silver over copper alloy
- Movable contact and terminal platings: gold over nickel over copper alloy
- Terminal platings: gold over nickel over copper alloy
- Terminal platings: tin over copper alloy
- Terminal contact platings: gold over nickel alloy
- Terminal contact platings: silver over nickel alloy
- Tin option not available with M1 & M3 terminations.

\*Manufacturer reserves the right to change product specification without prior notice.

# 2MS - WSP 1 - T1 - B4 - M1 G E

1  
Series2  
Poles3  
Circuit4  
Actuator Style5  
Bushing6  
Termination7  
Contacts8  
Seal**1 SERIES****2MS** Sealed Miniature Toggle Switch**2 POLES****WSP** Single pole - uses terminals 1, 2 & 3**WDP** Double pole - uses terminals 1, 2, 3, 4, 5 & 6**W3P** Three pole - uses terminals 1, 2, 3, 4, 5, 6, 7, 8 & 9**3 CIRCUIT**

( ) - momentary

| Position: | 1             | 2                   | 3             |
|-----------|---------------|---------------------|---------------|
|           | 2-3, 5-6, 8-9 | Connected Terminals | 2-1, 5-4, 8-7 |
| 1         | ON            | NONE                | ON            |
| 2         | ON            | NONE                | (ON)          |
| 3         | ON            | OFF                 | ON            |
| 4         | (ON)          | OFF                 | (ON)          |
| 5         | ON            | OFF                 | (ON)          |

**4 ACTUATOR STYLE**

|                           |                                            |
|---------------------------|--------------------------------------------|
| <b>T1</b> Round Bat       | <b>T9</b> Long Black Plastic .492" length  |
| <b>T2</b> Round Short Bat | <b>P1</b> Plastic Anti-Static .496" length |
|                           | <b>P2</b> Plastic Anti-Static .299" length |

**5 BUSHING**

|                            |                                           |
|----------------------------|-------------------------------------------|
| <b>B1</b> Threaded, Keyway | <b>B4</b> Unthreaded, Short, Keyway, Flat |
|----------------------------|-------------------------------------------|

## Notes:

B1 Bushing switches supplied with (2) 2M1-HDW2 nuts, (1) 2M1-HDW11 washer and (1) 2M1-HDW15 locking ring. See page 76-77.

1 Movable contact &amp; terminal platings: silver over copper alloy

2 Movable contact &amp; terminal platings: gold over nickel over copper alloy

3 Terminal platings: tin over nickel over copper alloy

4 Tin option not available with M1 terminal

**6 TERMINATION**

|                                               |                                                |
|-----------------------------------------------|------------------------------------------------|
| <b>M1</b> <sup>4</sup> Solder Lug             | <b>VS21</b> Vertical, Snap-In, .460" [11.70mm] |
| <b>M2</b> PCB                                 | <b>VS3</b> Vertical, .630" [16mm]              |
| <b>M3</b> Quick Connect                       | <b>VS31</b> Vertical, Snap-In, .630" [16mm]    |
| <b>M51</b> Wire Wrap, .750" [19.05mm]         | <b>U2</b> Vertical, .551" [14mm] - only 3PDT   |
| <b>M52</b> Wire Wrap, .964" [24.48mm]         | <b>VS4</b> Vertical, .461" [11.70mm]           |
| <b>M53</b> Wire Wrap, .425" [10.80mm]         | <b>VS41</b> Vertical, Snap-In, .461" [11.70mm] |
| <b>M54</b> Wire Wrap, 1.062" [25.97mm]        | <b>U4</b> Vertical, .551" [14mm] - only 3PDT   |
| <b>M6</b> Right Angle, PC Thru-Hole           | <b>VS5</b> Vertical, .630" [16mm]              |
| <b>M61</b> Right Angle, Snap-In               | <b>VS51</b> Vertical, Snap-In, .630" [16mm]    |
| <b>M7</b> Vertical, Right Angle, PC Thru-Hole |                                                |
| <b>M71</b> Vertical, Right Angle, Snap-In     |                                                |
| <b>VS2</b> Vertical, .461" [11.70mm]          |                                                |

**7 CONTACTS / TERMINALS**

| Contact Material             | Terminal Plating   | Rating                        | Approvals |
|------------------------------|--------------------|-------------------------------|-----------|
| <b>G</b> silver <sup>1</sup> | gold over silver   | 5A 125VAC or 28VDC, 2A 250VAC | us, IP67  |
| <b>K</b> gold <sup>2</sup>   | tin <sup>3,4</sup> | 0.4VA max 20V max (AC/DC)     | IP67      |
| <b>P</b> silver <sup>1</sup> | tin <sup>3,4</sup> | 5A 125VAC or 28VDC, 2A 250VAC | us, IP67  |
| <b>R</b> gold <sup>2</sup>   | gold <sup>2</sup>  | 0.4VA max 20V max (AC/DC)     | IP67      |

**8 EPOXY SEAL**

|                     |                             |
|---------------------|-----------------------------|
| <b>E</b> Epoxy Seal | <b>0</b> without Epoxy Seal |
|---------------------|-----------------------------|

# 2M1 - SP 1 - T1 - B1 - M1 Q E

1  
Series2  
Poles3  
Circuit4  
Actuator Style5  
Bushing6  
Termination7  
Contacts8  
Seal**1 SERIES****2M1** Miniature Toggle Switch**2 POLES****SP** Single pole - uses terminals 1, 2 & 3**DP** Double pole - uses terminals 1, 2, 3, 4, 5 & 6**3P** Three pole - uses terminals 1, 2, 3, 4, 5, 6, 7, 8 & 9**4P** Four pole - uses terminals 1, 2, 3, 4, 5, 6, 7, 8, 9, 10, 11 & 12**3 CIRCUIT**

( ) - momentary

| Position: | 1                    | 2                   | 3                    |
|-----------|----------------------|---------------------|----------------------|
|           | 2-3, 5-6, 8-9, 11-12 | Connected Terminals | 2-1, 5-4, 8-7, 11-10 |
| 1         | ON                   | NONE                | ON                   |
| 2         | ON                   | NONE                | (ON)                 |
| 3         | ON                   | OFF                 | ON                   |
| 4         | (ON)                 | OFF                 | (ON)                 |
| 5         | ON                   | OFF                 | (ON)                 |
| 6*        | ON                   | ON                  | ON                   |
| 7*        | (ON)                 | ON                  | (ON)                 |
| 8*        | ON                   | ON                  | (ON)                 |

\*Available with DP and 4P switches only. Center position connects 2-3, 5-4, 8-9, 11-10

**4 ACTUATOR STYLE**

|                                    |                                    |
|------------------------------------|------------------------------------|
| <b>T1</b> Round Bat                | <b>T7</b> Large Bat (B0 bushing)   |
| <b>T2</b> Round Short Bat          | <b>T8</b> X-Large Bat (B0 bushing) |
| <b>T3</b> Paddle                   | <b>T9</b> Black Plastic            |
| <b>T4</b> Medium Paddle            | <b>T0</b> Rectangular              |
| <b>T5</b> Long Paddle              | <b>TA</b> Locking Lever            |
| <b>T6</b> Flat (B1,B2,B5,BA,BB,BE) | <b>TI</b> Locking Lever            |
|                                    | <b>TL</b> Locking Lever            |

**5 BUSHING**

|                                         |                                                                  |
|-----------------------------------------|------------------------------------------------------------------|
| <b>B1</b> Threaded Standard, keyway     | <b>B8</b> Metric                                                 |
| <b>B2</b> Non-Threaded Standard, keyway | <b>B9</b> Splashproof                                            |
| <b>B3</b> Threaded Short, keyway        | <b>B0</b> 15/32" Threaded (Standard for T7 & T8 actuator styles) |
| <b>B4</b> Non-Threaded Short, keyway    | <b>BA</b> Threaded for T6                                        |
| <b>B5</b> High Torque, 7.5mm, flat      | <b>BB</b> Non-Threaded for T6                                    |
| <b>B6</b> High Torque, 8.0mm, keyway    | <b>BE</b> Threaded Hi Torque for T6                              |
| <b>B7</b> Long threaded                 | <b>BL</b> Threaded, Locking                                      |

**6 TERMINATION**

|                                               |                                                |
|-----------------------------------------------|------------------------------------------------|
| <b>M1</b> <sup>4</sup> Solder Lug             | <b>M71</b> Vertical, Right Angle, Snap-In      |
| <b>M2</b> PCB                                 | <b>VS2</b> Vertical, .461" [11.70mm]           |
| <b>M3</b> Quick Connect                       | <b>VS21</b> Vertical, Snap-In, .461" [11.70mm] |
| <b>M51</b> Wire Wrap, .750" [19.05mm]         | <b>VS3</b> Vertical, .630" [16mm]              |
| <b>M52</b> Wire Wrap, .964" [24.48mm]         | <b>VS31</b> Vertical, Snap-In, .630" [16mm]    |
| <b>M53</b> Wire Wrap, .425" [10.80mm]         | <b>VS4</b> Vertical, .461" [11.70mm]           |
| <b>M54</b> Wire Wrap, 1.062" [25.97mm]        | <b>VS41</b> Vertical, Snap-In, .461" [11.70mm] |
| <b>M6</b> Right Angle, PC Thru-Hole           | <b>VS5</b> Vertical, .630" [16mm]              |
| <b>M61</b> Right Angle, Snap-In               | <b>VS51</b> Vertical, Snap-In, .630" [16mm]    |
| <b>M7</b> Vertical, Right Angle, PC Thru-Hole |                                                |

**7 CONTACTS / TERMINALS**

| Contact Material             | Terminal Plating    | Rating                        | Approvals |
|------------------------------|---------------------|-------------------------------|-----------|
| <b>G</b> silver <sup>1</sup> | gold over silver    | 5A 125VAC or 28VDC, 2A 250VAC | us, IP67  |
| <b>K</b> gold <sup>2</sup>   | tin <sup>3,4</sup>  | 0.4VA max 20V max (AC/DC)     | N/A       |
| <b>P</b> silver <sup>1</sup> | tin <sup>3,4</sup>  | 5A 125VAC or 28VDC, 2A 250VAC | us, IP67  |
| <b>Q</b> silver <sup>1</sup> | silver <sup>1</sup> | 5A 125VAC or 28VDC, 2A 250VAC | us, IP67  |
| <b>R</b> gold <sup>2</sup>   | gold <sup>2</sup>   | 0.4VA max 20V max (AC/DC)     | N/A       |

**8 EPOXY SEAL**

|                     |                             |
|---------------------|-----------------------------|
| <b>E</b> Epoxy Seal | <b>0</b> without Epoxy Seal |
|---------------------|-----------------------------|

## Notes:

B1 Bushing switches supplied with (2) 2M1-HDW2 nuts, (1) 2M1-HDW11 washer and (1) 2M1-HDW15 locking ring.

1 Movable contact &amp; terminal platings: silver over copper alloy

2 Movable contact &amp; terminal platings: gold over nickel over copper alloy

3 Terminal platings: tin over nickel over copper alloy

4 Tin option not available with M1 terminal

2M-Series Accessories

To order accessories assembled on a switch, specify the switch number followed by the accessory part number and the word “assembled”. Ex: 2M1-SP1-T1-B1-M1QE-T12 ASSEMBLED. To order accessories in bulk, specify the Series, followed by the accessory. Ex: 2M1-T12. See page 76 for dimensional specifications.

Optional Toggle Cap

2M1

-

T1

2

1

Series

2

Toggle Cap Size

3

Color

|                                                     |                                                                                    |
|-----------------------------------------------------|------------------------------------------------------------------------------------|
| <b>1 SERIES</b><br>2M1 Fits 2M1H, 2MS or 2M1        | <b>3 CAP COLOR</b><br>1 White<br>2 Black<br>3 Red<br>5 Yellow<br>6 Green<br>7 Blue |
| <b>2 TOGGLE CAP SIZE</b><br>T1 10.6 mm<br>T2 7.6 mm |                                                                                    |

Optional Dress and Knurled Nuts

2M1

-

HDW3

1

Series

2

Nut

|                                              |                                                                                                          |
|----------------------------------------------|----------------------------------------------------------------------------------------------------------|
| <b>1 SERIES</b><br>2M1 Fits 2M1H, 2MS or 2M1 | <b>2 NUT</b><br>HDW3 Dress nut for 1/4" bushing<br>HDW5 Knurled nut for 15/32" bushing (2M1-Series only) |
|----------------------------------------------|----------------------------------------------------------------------------------------------------------|

Optional Rubber Seals

2M1

-

E1A

1

Series

2

Rubber Boot Seal

|                                              |                                                                                                                                                                                                                                                                                     |
|----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>1 SERIES</b><br>2M1 Fits 2M1H, 2MS or 2M1 | <b>2 RUBBER BOOT SEAL</b><br>E1A 1/4 - 40" UNS bushing (Not available for B0 bushing option)<br>K1 Metric M6 bushing (B8 bushing only)<br>YE1D 15/32 - 32" UNS bushing (TJ, TK and B0 bushings only)<br>YE1E 15/32 - 32" UNS bushing 1/2 boot (T7, T8, TJ, TK and B0 bushings only) |
|----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

3MNH

-

WCP-0872

1

Series


2

Rubber O-Ring


|                                           |                                                             |
|-------------------------------------------|-------------------------------------------------------------|
| <b>1 SERIES</b><br>3MNH Fits 3MNH or 2M1H | <b>2 RUBBER O-RING</b><br>WCP-0872 For 15/32 bushing option |
|-------------------------------------------|-------------------------------------------------------------|

## 2M1H-Series Dimensional Specifications: in. [mm]


### Single Pole



### Double Pole




### Actuator Options



| OPTION CODE | DIM. "A"     |
|-------------|--------------|
| TJ          | .709 [18.00] |
| TK          | .512 [13.00] |


### Bushing Options & Mounting




| OPTION CODE | DIM. "A"    |
|-------------|-------------|
| BK          | .386 [9.80] |

### Termination Options


#### M1 Standard Solder Lug




#### M2 PC Thru-Hole



#### M3 Quick Connect




#### M5 Wire Wrap




| OPTION CODE | DIM. "A"      |
|-------------|---------------|
| M5-1        | .750 [19.05]  |
| M5-2        | .964 [24.48]  |
| M5-3        | .425 [10.80]  |
| M5-4        | 1.062 [26.97] |

## 2MS-Series Dimensional Specifications: in. [mm]


### Single Pole



### Double Pole




### Three Pole




### Actuator Options


#### T1



#### T2




#### T9 with Plastic Cap





| NO. | COLOR       |
|-----|-------------|
| 1   | White       |
| 2   | Black(std.) |
| 3   | Red         |
| 4   | Orange      |
| 5   | Yellow      |
| 6   | Green       |
| 7   | Blue        |
| 8   | Brown       |
| 9   | Gray        |

#### P1 Plastic Toggle





#### P2 Plastic Toggle







\* Shown with B4 bushing. Subtract .075" (1.90 mm) from actuator height for B1 bushing.

## 2MS-Series Dimensional Specifications: in. [mm]

















### Bushing Options

**B1**

**B4**


### Termination Options

**M1 Standard Solder Lug**

**M2 PC Thru-Hole**

**M3 Quick Connect**

**M5 Wire Wrap**





| OPTION CODE | DIM. 'A'      |
|-------------|---------------|
| <b>M5-1</b> | .750 [19.05]  |
| <b>M5-2</b> | .964 [24.48]  |
| <b>M5-3</b> | .425 [10.80]  |
| <b>M5-4</b> | 1.062 [26.97] |

**M6 Single Pole**

**P.C.MOUNTING**

**M6 Double Pole**

**P.C.MOUNTING**

**M6 Three Pole**

**P.C.MOUNTING**

**M7 Single Pole**

**P.C.MOUNTING**



## 2MS-Series Dimensional Specifications: in. [mm]

### Termination Options




#### M7 Double Pole




#### P.C.MOUNTING





#### M7 Three Pole



#### P.C.MOUNTING




#### VS2-VS3 Single Pole





| OPTION CODE | DIM.'A'      |
|-------------|--------------|
| <b>VS2</b>  | .461 [11.70] |
| <b>VS3</b>  | .630 [16.00] |

#### P.C.MOUNTING




#### VS2-VS3 Double Pole





| OPTION CODE | DIM.'A'      |
|-------------|--------------|
| <b>VS2</b>  | .461 [11.70] |
| <b>VS3</b>  | .630 [16.00] |

#### P.C.MOUNTING




#### U2-VS3 Three Pole



| OPTION CODE | DIM.'A'      |
|-------------|--------------|
| <b>U2</b>   | .551 [14.00] |
| <b>VS3</b>  | .630 [16.00] |

#### P.C.MOUNTING







## 2MS-Series Dimensional Specifications: in. [mm]


### Termination Options

#### VS4-VS5 Single Pole





| OPTION CODE | DIM.'A'      |
|-------------|--------------|
| <b>VS4</b>  | .461 [11.70] |
| <b>VS5</b>  | .630 [16.00] |

#### P.C.MOUNTING




#### VS4-VS5 Double Pole





| OPTION CODE | DIM.'A'      |
|-------------|--------------|
| <b>VS4</b>  | .461 [11.70] |
| <b>VS5</b>  | .630 [16.00] |

#### P.C.MOUNTING




#### U4-VS5 Three Pole




| OPTION CODE | DIM.'A'      |
|-------------|--------------|
| <b>U4</b>   | .551 [14.00] |
| <b>VS5</b>  | .630 [16.00] |

#### P.C.MOUNTING




### Snap-In Termination Options


#### M61




#### VS21, VS31



#### M71




#### VS41, VS51




\* PC Mounting for M61, M71, VS21, VS31, VS41, VS51 refer to M6, M7, VS2, VS3, VS4, VS5 respectively.


## 2M1-Series Dimensional Specifications: in. [mm]




### Actuator Options for Panel Rear Mount



\* T6 actuator is available with B1, B2, B5, B6, BA, BB & BE bushing. Actuator length shown for T1 – T5, T9 and T10 is with B1 bushing. T7, P7, T8 & P8 does not require a bushing code.




### Bushing Options




## 2M1-Series Dimensional Specifications: in. [mm]

### Bushing Options


B7 Long




B8 Metric




B9 Splash-Proof




BL Locking Lever




BA Threaded for T6



BB Non-Threaded for T6






BB High Torque for T6





### Panel Mounting

1/4 INCH BUSHING




15/32 INCH BUSHING




### Termination Options


M1 Standard Solder Lug




M2 PC Thru-Hole



M3 Quick Connect






M5 Wire Wrap




| OPTION CODE | DIM.'A'       |
|-------------|---------------|
| M5-1        | .750 [19.05]  |
| M5-2        | .964 [24.48]  |
| M5-3        | .425 [10.80]  |
| M5-4        | 1.062 [26.97] |




M6 Single Pole




P.C.MOUNTING



M6 Double Pole






P.C.MOUNTING




## 2M1-Series Dimensional Specifications: in. [mm]

### Termination Options




**M6 Three Pole**




**P.C.MOUNTING**






**M7 Single Pole**




**P.C.MOUNTING**






**M7 Double Pole**




**P.C.MOUNTING**






**M7 Three Pole**




**P.C.MOUNTING**





**M7 Four Pole**



**P.C.MOUNTING**




**VS2-VS3 Single Pole**



| OPTION CODE | DIM. 'A'     |
|-------------|--------------|
| VS2         | .461 [11.70] |
| VS3         | .630 [16.00] |



**P.C.MOUNTING**



## 2M1-Series Dimensional Specifications: in. [mm]


### Termination Options

#### VS2-VS3 Double Pole





| OPTION CODE | DIM. 'A'     |
|-------------|--------------|
| VS2         | .461 [11.70] |
| VS3         | .630 [16.00] |

#### P.C.MOUNTING




#### VS4-VS5 Single Pole





| OPTION CODE | DIM. 'A'     |
|-------------|--------------|
| VS4         | .461 [11.70] |
| VS5         | .630 [16.00] |

#### P.C.MOUNTING




#### VS4-VS5 Double Pole




| OPTION CODE | DIM. 'A'     |
|-------------|--------------|
| VS4         | .461 [11.70] |
| VS5         | .630 [16.00] |

#### P.C.MOUNTING




### Snap-In Termination Options


#### M61 (available with SP & DP)




#### VS21, VS31



#### M71 (available with SP & DP)



#### VS41, VS51



\* PC Mounting for M61,M71,VS21,VS31,VS41,VS51 refer to M6,M7,VS2,VS3,VS4,VS5 respectively.

## Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit [www.carlingtech.com/findarep](http://www.carlingtech.com/findarep).



## About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With four ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit [www.carlingtech.com/company-profile](http://www.carlingtech.com/company-profile).

To view all of Carling's environmental, quality, health & safety certifications please visit [www.carlingtech.com/environmental-certifications](http://www.carlingtech.com/environmental-certifications)

### **Worldwide Headquarters**

Carling Technologies, Inc.  
60 Johnson Avenue, Plainville, CT 06062  
**Phone:** 860.793.9281 **Fax:** 860.793.9231  
**Email:** sales@carlingtech.com

**Northern Region Sales Office:** nrsm@carlingtech.com  
**Southeast Region Sales Office:** sersm@carlingtech.com  
**Midwest Region Sales Office:** mrsm@carlingtech.com  
**West Region Sales Office:** wrsm@carlingtech.com  
**Latin America Sales Office:** larsm@carlingtech.com

### **Asia-Pacific Headquarters**

Carling Technologies, Asia-Pacific Ltd.,  
Suite 1607, 16/F Tower 2, The Gateway,  
Harbour City, 25 Canton Road,  
Tsimshatsui, Kowloon, Hong Kong  
**Phone:** Int + 852-2737-2277 **Fax:** Int + 852-2736-9332  
**Email:** sales@carlingtech.com.hk

**Shenzhen, China:** shenzhen@carlingtech.com  
**Shanghai, China:** shanghai@carlingtech.com  
**Pune, India:** india@carlingtech.com  
**Kaohsiung, Taiwan:** taiwan@carlingtech.com  
**Yokohama, Japan:** japan@carlingtech.com

### **Europe | Middle East | Africa Headquarters**

Carling Technologies LTD  
4 Airport Business Park, Exeter Airport,  
Clyst Honiton, Exeter, Devon, EX5 2UL, UK  
**Phone:** Int + 44 1392.364422 **Fax:** Int + 44 1392.364477  
**Email:** ltd.sales@carlingtech.com

**Germany:** gmbh@carlingtech.com  
**France:** sas@carlingtech.com



**Carling Technologies®**

Innovative Designs. Powerful Solutions.