



Features

- RoHS compliant* versions available
- Overvoltage/lightning protection to ITU-T K.20/K.21/K.45
- Resettable overcurrent protection
- Typical application is secondary protection on telecom line cards

4B06B-504-RC - Surge Line Protection Module

Electrical Characteristics

Resistance Value, 50 Ohm	
R1=R2=42 ohms	±1 %
Ratio Tolerance R1/R2	±1 %
Resistance Value, 100 Ohm	
R1=R2=92 ohms	±1 %
Ratio Tolerance R1/R2	±1 %
PPTC, R3 & R4, 8 Ohms Nominal Value	
Resistance Range	.5 ohms to 15 ohms
Ratio Tolerance R3/R4	Matched to within 1.0 ohms
Trip Time at 1 Amp	2 seconds at 25 °C
Hold Current	130 ma
Temperature Range	-40 °C to +85 °C


Physical Characteristics

Body Style	Open Frame SIP
Substrate Material	96 % Alumina
Lead Frame Material	Copper, solder coated
Flammability	Conforms to UL94V-0

Functional Characteristics


Lightning Surge Test	10 x 700 µs, 1.5 kV
Power Induction	300 V rms
Power Contact	220 V rms

Product Dimensions



DIMENSIONS: $\frac{\text{MILLIMETERS}}{\text{(INCHES)}}$

Electrical Schematic



How To Order

Model	4B 06 B - 504 - XXX LF
(4B = Open Frame)	
Number of Pins	
Physical Configuration	
Electrical Configuration	504 = Matched pair of resistors plus PPTC
Resistance Code	
• 500 = 50 ohms	
• 101 = 100 ohms	
RoHS Compliant Option	
Blank = Standard Product	
LF = RoHS Compliant Product	



Asia-Pacific:

TEL +886- (0)2 25624117
FAX +886- (0)2 25624116

Europe:

TEL +41-41 7685555
FAX +41-41 7685510

The Americas:

TEL +1-951 781-5500
FAX +1-951 781-5700

www.bourns.com

*RoHS Directive 2002/95/EC Jan 27, 2003 including Annex. Specifications are subject to change without notice. Customers should verify actual device performance in their specific applications.