



Carling Technologies®
/// NOW PART OF



Littelfuse®

Tippette®

Full Sized Rocker Switches

PRODUCT WEBPAGE

request sample, configure part



The Tippetto Series is a traditionally styled rocker switch, available in sealed or unsealed versions. These switches are appropriate for use in general purpose applications which may or may not require a modicum of environmental protection.

1-4

Poles

10-20

Amps

125-250

VAC Max

12-30

VDC Max

Typical Applications

- General Purpose Applications
- Commercial Food
- Recreational Vehicles
- Industrial Automation

Tech Specs

Electrical

Contact Rating	15 amps, 125 VAC 10 amps, 250 VAC 3/4 HP 125-250 VAC 15 amps, 12-30 VDC
Life	25,000 cycles circuit dependent 50,000 cycles circuit dependent consult factory for applicable circuits.
Contact	Fine silver, silver cad-oxide
Terminals	Brass or copper/silver plate 1/4" (6.3mm) Quick Connect terminations standard. Solder lug - Brass Tin Plated Wire Lead 16 gauge standard 105°C 600VAC Screw Terminals - Brass

Agency Certifications


UL, CSA and VDE

Select circuits and constructions with VDE/IEC approvals are available. Consult factory

Physical

Lighted	Incandescent - rated 10,000 hours Neon - rated 25,000 hours
Seals	Bracket - Actuator WBL/MBL optional external gasket panel seal
Operating Temperature	Up to 85° C Consult Factory for Specific Applications

Mounting



*Angled corners are suggested for optimum fit.
Standard rectangular cutout is acceptable.

Ordering Scheme

Sample Part Number **TIGA51 - 6M - BL - MBL**

Selection 1 2 3 4

1. SERIES

10A 250VAC, 15A 125VAC, 3/4 HP 125-250VAC, 15A 6-28VDC

Single Pole in Double Pole base ²

solder	.250	screw	wire
lug	tab	term.	leads
TIGA50	TIGA51	TIGA54	TIGA55
TIGA5A	TIGA5B	TIGA5E	TIGA5F
TIGA5L	TIGA5M	TIGA5S	TIGA5T
TIGB50	TIGB51	TIGB54	TIGB55
TIGB5A	TIGB5B	TIGB5E	TIGB5F
TIGC50	TIGC51	TIGC54	TIGC55
TIGC5A	TIGC5B	TIGC5E	TIGC5F
TIGC5L	TIGC5M	TIGC5S	TIGC5T

Three Pole

solder	.250	screw	wire
lug	tab	term.	leads
TIHK50	TIHK51	TIHK54	TIHK55
TIHK5A	TIHK5B	TIHK5E	TIHK5F
TIHK5L	TIHK5M	TIHK5S	TIHK5T
TIHL50	TIHL51	TIHL54	TIHL55
TIHL5A	TIHL5B	TIHL5E	TIHL5F
TIHM50	TIHM51	TIHM54	TIHM55
TIHM5A	TIHM5B	TIHM5E	TIHM5F
TIHM5L	TIHM5M	TIHM5S	TIHM5T

VDE APPROVED

10A 250VAC, 15A 125VAC, 12(6)A 250VAC T85

Single Pole in Double Pole base ²

solder	.250	wire
lug	tab	lead
TIGA90	TIGA91	TIGA95
TIGB90	TIGB91	TIGB95
TIGC90	TIGC91	TIGC95

Double Pole

solder	.250	screw	wire
lug	tab	term.	leads
TIGK50	TIGK51	TIGK54	TIGK55
TIGK5A	TIGK5B	TIGK5E	TIGK5F
TIGK5L	TIGK5M	TIGK5S	TIGK5T
TIGL50	TIGL51	TIGL54	TIGL55
TIGL5A	TIGL5B	TIGL5E	TIGL5F
TIGM50	TIGM51	TIGM54	TIGM55
TIGM5A	TIGM5B	TIGM5E	TIGM5F
TIGM5L	TIGM5M	TIGM5S	TIGM5T

Four Pole

solder	.250	screw	wire
lug	tab	term.	leads
TIHK50	TIHK51	TIHK54	TIHK55
TIHK5A	TIHK5B	TIHK5E	TIHK5F
TIHK5L	TIHK5M	TIHK5S	TIHK5T
TIIL50	TIIL51	TIIL54	TIIL55
TIIL5A	TIIL5B	TIIL5E	TIIL5F
TIIM50	TIIM51	TIIM54	TIIM55
TIIM5A	TIIM5B	TIIM5E	TIIM5F
TIIM5L	TIIM5M	TIIM5S	TIIM5T

Double Pole

solder	.250	wire
lug	tab	lead
TIGK90	TIGK91	TIGK95
TIGL90	TIGL91	TIGL95
TIGM90	TIGM91	TIGM95

Additional ratings up to 20A 125-277VAC, 1 1/2HP 125 VAC, 2HP 250VAC are available. Consult factory for specifics.

2. ACTUATOR STYLE

1S	Angular/Smooth Face Gloss ¹²
1C	Angular/Cross Serrations Gloss ¹²
1F	Flatted/Smooth Face Gloss ¹²
1L	Angular/Longline Serrations Gloss ^{1,12}
2L	Long Smooth/Narrow ¹
6M	Curved/Smooth Face Matte ³
6S	Curved/Smooth Face Gloss ³
7S	Rounded Paddle/Smooth Face Gloss ¹
7N	Witch's Hat/Narrow ¹⁴
7P	Witch's Hat/Wide ¹⁴

3. ACTUATOR COLOR

BL	Black
WH	White
RD	Red

4. BRACKET STYLE

A	Screw Mount ⁵
B	Screw Mount ^{5,12}
C	Screw Mount ⁵
H	Screw Mount ⁵
NBL	Nylon Black
WBL	Water shedding Black ⁴
MBL	Marine Style Black ^{4,6}
FN	Metal Snap-In ⁵
FN BLK	Black Metal Snap-In ⁵
FN SS	Stainless Steel Snap-In ⁵
FW	Wide Stainless Steel Snap-In ⁵

Notes:

- 1 FN, & FW brackets only.
- 2 For single pole switch in a single pole base, specify TIL with single pole circuitry/rating/termination.
- 3 NBL, WBL, & MBL brackets only. With 6M actuator, brackets also will be matte finish.
- 4 6M & 6S actuators only
- 5 Not available with 6M & 6S actuators.
- 6 Consists of WBL bracket, neoprene seal, and dummy rivets at open holes. Consult factory for agency approval status.
- 7 All ratings are appropriate for usage in low voltage applications.
- 8 For additional special circuits, see catalog.
- 9 Custom colors are available, consult factory.
- 10 .187 tab and PC terminations are also available. Consult factory for catalog number callout.
- 11 () momentary
- 12 Not available with WBL or MBL style brackets.
- 13 Available with bracket A, C or H only.
- 14 Not available with MBL, WBL or H brackets. Can be supplied as a double rocker to control separate poles of a TIG, TIH or TII switch. Consult factory for details.

[Configure Complete Part Number >](#)

[Browse Standard Parts >](#)

Ordering Scheme

Sample Part Number LTILA51 - 6M - BL - RC - MBL - 12V

Selection 1 2 3 4 5 6

1. SERIES

10A 250VAC, 15A 125VAC, 3/4 HP 125-250VAC, 15A 15-28VDC

illuminated Single Pole in Double Pole base

solder lug	.250 tab	screw term.	wire leads	
LTILA50	LTILA51	LTILA54	LTILA55	On-None-Off
LTILA5A	LTILA5B	LTILA5E	LTILA5F	(On)-None-Off
LTILA5L	LTILA5M	LTILA5S	LTILA5T	On-None-(Off)
LTILB50	LTILB51	LTILB54	LTILB55	On-None-On
LTILB5A	LTILB5B	LTILB5E	LTILB5F	On-None-(On)
LTILC50	LTILC51	LTILC54	LTILC55	On-Off-On
LTILC5A	LTILC5B	LTILC5E	LTILC5F	On-Off-(On)
LTILC5L	LTILC5M	LTILC5S	LTILC5T	(On)-Off-(On)

illuminated Double Pole

solder lug	.250 tab	screw term	wire leads	
LTIGK50	LTIGK51	LTIGK54	LTIGK55	
LTIGK5A	LTIGK5B	LTIGK5E	LTIGK5F	
LTIGK5L	LTIGK5M	LTIGK5S	LTIGK5T	
LTIGL50	LTIGL51	LTIGL54	LTIGL55	
LTIGL5A	LTIGL5B	LTIGL5E	LTIGL5F	
LTIGM50	LTIGM51	LTIGM54	LTIGM55	
LTIGM5A	LTIGM5B	LTIGM5E	LTIGM5F	
LTIGM5L	LTIGM5M	LTIGM5S	LTIGM5T	

Additional ratings up to 12A 250VAC, 17A 125 VAC, 3/4 HP 125 VAC, 1HP 250VAC are available. Consult factory for specifics. Three pole switch is also available: Substitute H for fourth digit of part number. ex. LTIHK51

2. ACTUATOR STYLE 4

1S	Angular/Smooth Face Gloss ¹
1C	Angular/Cross Serrations Gloss ¹
1L	Angular/Longline Serrations Gloss ¹
6M	Curved/Smooth Face Matte ³
6S	Curved/Smooth Face Gloss ³
7S	Rounded Paddle/Smooth Face Gloss ²

5. BRACKET STYLE 11

NBL	Nylon Black
WBL	Water shedding Black ⁵
MBL	Marine Style Black ^{5,8}
FN	Metal Snap-In ^{4,6}
FN BLK	Black Metal Snap-In ^{4,6}
FN SS	Stainless Steel Snap-In ^{4,6}

3. ACTUATOR COLOR 11

BL	Black
WH	White
RD	Red

4. LENS COLOR 13

AM	Amber
LU	Blue ⁷
RC	Red
CL	Clear
GN	Green ⁷
WH	White

6. LAMP VOLTAGE

neon ⁹				
125N	125 volt	250N	250 volt	
incandescent				
6V	6 volt	12V	12 volt	18V 18 volt
24V	24 volt	28V	28 volt	

Notes:

- 1 NBL, FN, & FW brackets only. Double pole circuits provided with 3 pole base.
- 2 LTIL-Series with NBL, FN, & FW brackets only.
- 3 NBL, WBL, & MBL brackets only. With 6M actuator, bracket will also be matte finish.
- 4 1S, 1C, 1L & 7S with NBL bracket only available with LTIL-Series.
- 5 6M, 6S actuators only.
- 6 Not available with 6M and 6S actuators.
- 7 Not recommended with neon lamps.
- 8 Consists of WBL bracket, neoprene seal, dummy rivets at open holes. Consult factory for agency approval status.
- 9 Not recommended with blue or green lenses.
- 10 All ratings are appropriate for usage in low voltage applications.
- 11 Custom colors and additional bracket styles are available, consult factory.
- 12 () - momentary
- 13 All double throw circuits supplied with two lenses. To specify two different lens colors, specify second color, after first color. (ex. LTIGM51-6S-BL-RC/GN-WBL-12V)
- 14 .187 tab and PC terminations are also available. Consult factory for catalog number callout.


 [Configure Complete Part Number >](#)

 [Browse Standard Parts >](#)

Dimensional Specs


inches [millimeters]

1C
CROSS-LINE W/ONE LENS




WITH .250 TAB
TERMINALS
AND NBL BRACKET

1L
LONG-LINE W/ONE LENS




WITH SOLDER LUG
TERMINAL
AND NBL BRACKET

1S
SMOOTH W/ONE LENS




WITH .250 TAB
TERMINALS
AND NBL BRACKET

1F
FLATTED STYLE NO LENS




WITH .250 TAB
TERMINALS
AND FN BRACKET

6M, 6S
CURVED W/ONE LENS



WITH SOLDER LUG
TERMINALS
AND NBL BRACKET


7S
TOGGLE-STYLE W/ONE LENS



WITH .250 TAB
TERMINALS
AND FN BRACKET

Dimensional Specs


inches [millimeters]



SOLDER LUG	.250 TAB (Q.C.)	.187 TAB (Q.C.)
TERMINAL TYPE		
SCREW (ASSEMBLED)	WIRE LEAD	PRINTED CIRCUIT

MOUNTING HOLE
(Nylon Snap-in Brackets)
Panel Thickness:
.030 min. - .250 max.
Switch should be mounted at 90°
for maximum water shedding
(45° to 90° acceptable)

* Angled corners are
suggested for optimum fit.
Standard rectangular
cutout is acceptable.




SPECIAL CIRCUITS FOR TIPPETTE ROCKER SWITCHES


Circuit	Position 1	Position 2	Position 3
Progressive Two Circuit			
GG	Both Circuits ON	One Circuit ON	OFF
GG	Both Circuits (ON)	One Circuit ON	OFF
Single Pole Triple Throw			
GE	ON	ON	ON
Two Circuit			
GH	Circuit 1 ON	Both Circuits ON	Circuit 2 ON
GP	Circuit 2 ON	Circuit 1 ON	OFF
Reversing Double Pole Double Throw			
GO	ON	OFF	ON
GX	ON	NONE	ON

Dimensional Specs


inches [millimeters]



TAPPED HOLE
Standard with
A & B Brackets




CLEARANCE HOLE
Standard with
C Bracket




MOUNTING HOLE
(Nylon Snap-in Brackets)
Panel Thickness:
.030 min. - .250 max.

* Angled corners are suggested for optimum fit. Standard rectangular cutout is acceptable.


TIL	TIG	TII	TIH



FN
TIL, TIG, TIH, TII
METAL, SNAP-IN



FW
TIL, TIG, TIH, TII
METAL, SNAP-IN



MBL, NBL, WBL
TIG
BLACK NYLON, SNAP-IN

Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit www.carlingtech.com/findarep.



About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With six ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit www.carlingtech.com/company-profile.

To view all of Carling's environmental, quality, health & safety certifications please visit www.carlingtech.com/environmental-certifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Carling Technologies:

[TIGC51-6S-BL-NBL](#) [LTILC5B-6S-BL-RC-NBL-12V](#) [LTILB5B-6S-BL-RC-NBL-12V](#) [LTILB51-6S-BL-RC-NBL-12V](#)
[LTILC51-6S-BL-RC-NBL-12V](#) [TIGK5B-6S-BL-NBL](#) [TIGK5M-6S-BL-NBL](#) [TILA51-1L-BL-FN](#) [TIGL5B-6S-BL-NBL](#)
[LTIGK51-6S-BL-RC-NBL/125N](#) [TIGL51-6S-BL-NBL](#) [TIGM51-6S-BL-NBL](#) [TIGM5B-6S-BL-NBL](#) [TIGM5M-6S-BL-NBL](#)
[TILC6M-1L-WH-A](#) [TIGK51-6S-BL-NBL](#) [TIGC5M-1C-RD-NBL](#) [LITGM54-1L-BL-AM-FN/125N/INDP](#) [LTILA51-6S-BL-](#)
[AM-NBL/125N](#) [TIGA50-6S-BL-NBL](#) [TIGA51-6M-BL-MBL](#) [TIGA51-6S-BL-NBL](#) [TIGA54-6S-BL-WBL](#) [TIGA5B-6S-BL-](#)
[NBL](#) [TIGA5M-6S-BL-NBL](#) [TIGB51-6S-BL-NBL](#) [TIGB51-6S-BL-WBL](#) [TIGB5B-6S-BL-NBL](#) [TIGC5B-6S-BL-NBL](#)
[TIGC5M-6S-BL-NBL](#) [TIGC5M-6S-BL-WBL](#) [TIGH51-6S-BL-NBL](#) [TIGK50-6S-BL-NBL](#) [TIGK51-6S-WH-NBL](#) [TIGK54-](#)
[6S-BL-WBL](#) [TIGK720-6M-BL-NBL](#) [TIGK721-6S-BL-NBL](#) [TIGK721-6S-BL-WBL](#) [TIGM51-6S-WH-NBL](#) [TIGM5M-6S-](#)
[WH-NBL](#) [TIGM721-6S-BL-NBL](#) [TILB50-1L-BL-FN](#) [TILC61-1L-BL-FN](#) [LTILC5M-6S-BL-RC-NBL-12V](#) [TIGK57-6S-BL-](#)
[NBL](#) [TILA50-1L-BL-A](#) [LTILC5L-6S-BL-GN/AM-NBL-12V](#) [TIGC6M-1L-BL-FN](#) [LTILC5M-1L-BL-GN-NBL/12V](#) [TIGG5E-](#)
[1S-WH-FN](#) [LTILB51-6S-BL-RC-NBL/125N](#) [TIGL51-6M-BL-WBL](#) [TIGP5E-6S-BL-NBL](#) [TIGE51-6S-BL-WBL](#) [TIGM6B-](#)
[1L-BL-A](#) [TIGP51-6M-BL-MBL-XJC3](#) [TIGK51-6S-WH-NBL/ON-OFF](#) [TIGA5B-6S-BL-MBL](#) [TIGK54-1S-RD-B](#) [TIGL5E-](#)
[1L-WH-FN](#) [LTIGK51-6S-WH-AM-NBL/125N](#) [TIGC54-1S-BL-FN](#) [TIGB51-6S-WH-MBL](#) [TIGC5E-6S-BL-NBL](#) [LTIGK51-](#)
[6S-WH-RC-NBL/125N](#) [LTILA51-6S-WH-RC-NBL/125N](#) [LTILA51-6S-WH-RC-NBL/12V](#) [TIHM5M-1S-BL-FN](#) [TIGG5B-](#)
[6S-BL-NBL](#) [TIGK51-1C-BL-FN](#) [TIGB51-7S-BL-NBL](#) [TIGC51-6S-BL-WBL](#) [TIGC51-6S-WH-NBL](#) [TIGC54-6S-BL-NBL](#)
[TIGC5M-6S-BL-MBL](#) [TIGC5S-6S-BL-WBL](#) [TIGC721-7S-BL-NBL](#) [TIGE5M-6S-BL-NBL](#) [TIGG51-6S-BL-NBL](#) [TIGA51-](#)
[6S-BL-MBL](#) [TIGA51-6S-BL-WBL](#) [TIGA51-6S-WH-NBL](#) [TIGA5E-6S-BL-NBL](#) [TIGB51-6S-BL-MBL](#) [TIGM51-6M-BL-NBL](#)
[TIGM51-6S-BL-WBL](#) [TIGL51-6S-BL-WBL](#) [TIGM5M-6M-BL-MBL](#) [TIGM51-1S-BL-FN BLK](#) [TIGM51-6S-BL-MBL](#)
[TIGM51-1L-BL-A](#) [TIGM51-6M-BL-MBL](#) [TIGG54-6S-BL-WBL](#) [TIGC5L-6M-BL-WBL](#) [TIGK05-6S-BL-WBL](#) [TIGA6M-6S-](#)
[BL-NBL](#) [TIGB63-6S-BL-NBL](#) [TIGE5M-6M-BL-MBL](#) [TIGA721-1S-RD-NBL](#) [TIGC54-6S-BL-MBL](#)