

SEARCH OUR
PRODUCTS

aluminum
electrolytic &
organic
semiconductor

film

power film

tantalum
ceramic

TECH TOOLS



NEW PRODUCTS

Aluminum Electrolytic Capacitors

+105°C High Frequency Low Impedance Radial Lead Aluminum Electrolytic Capacitor

Part Number: 476KXM025M

[General Specifications \(PDF\)](#)

[Special Order Options](#)

[KXM document \(PDF\)](#)



Electrical Specifications

Capacitance: 47.0 μ F
Tolerance: -20 %, +20 %
Dissipation Factor: 0.14 at 120 Hz
ESR: 4.938 Ohms at 20° C and 120 Hz
Impedance:
 0.3 Ohms at 20°C 100 kHz
 1.0 Ohms at -10°C 100 kHz

Impedance Ratios:

2.0 at -25°C/20°C
 3.0 at -40°C/20°C

Load Life:

2000 Hours at 105°C with 100% of rated voltage and
 with 100% of rated ripple current

Temperature Range: -40°C to +105°C

WVDC: 25 volts DC

SVDC: 32. volts DC

Leakage Current:

11.75 μ A after 2 Minutes

Ripple Current:

250.0 mA at 100 kHz and 105°C

Physical Specifications

Diameter (D): 5.0 mm + 0.5 mm
Length (L): 11.0 mm + 2.0 mm
Lead Wire Diameter (d): 0.5 mm + 0.05 mm
Lead Spacing: 2.0 mm +/- 0.5 mm
Lead Length: 15 mm

