



Flyback Transformer

For National Semiconductor
LM5000 DC/DC Regulator

This surface mount flyback transformer is designed for use with National Semiconductor LM5000 DC/DC regulator. The core completely encloses the windings to minimize EMI interference. The transformer features very low DCR, 500 V isolation and a leakage inductance

rating of just 1.0 μH . Coilcraft can also custom engineer a transformer to meet your specific requirements.

For free evaluation samples, contact Coilcraft or order them on-line at www.coilcraft.com.

Part number ¹	Inductance ² $\pm 20\%$ (μH)		Input voltage (V)	Output	DCR max (Ohms)	Leakage Inductance ³ max (μH)	Turns ratio in : out : aux	Isolation ⁴ (Vrms)
	Pins 1 – 4	Pins 2 – 3						
A0009-AL_	100	100	18 – 55	3.3 V @ 3 A	0.150 (1 – 4) 0.150 (2 – 3) 0.012 (5,6 – 7,8)	1.0	1 : 0.33 : 1	500

1. When ordering, please specify a **packaging** code:

A0009-AL D

Packaging: **D** = 13" machine ready reel. EIA-481 embossed plastic tape (150 per full reel).

B = Less than full reel. In tape, but not machine ready. To have a leader and trailer added (\$25 charge), use code letter D instead.

- Inductance measured at 100 kHz, 0.1 Vrms, 0 Adc.
 - Leakage inductance measured at 100 kHz, 0.1 Vrms from pins 1 to 4 with all other pins shorted.
 - Isolation measured from pin 1 to pins 5 and 6; from 2 to 5 and 6; and from pins 1, 2, 5 and 6 to the core.
 - Electrical specifications at 25°C.
- Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

Core material Ferrite

Terminations RoHS tin-silver over tin over nickel over phosphor bronze. Other terminations available at additional cost.

Weight 7.86 g

Ambient temperature -40°C to $+85^{\circ}\text{C}$

Storage temperature Component: -40°C to $+85^{\circ}\text{C}$.
Packaging: -40°C to $+80^{\circ}\text{C}$



Resistance to soldering heat Max three 40 second reflows at $+260^{\circ}\text{C}$, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at $<30^{\circ}\text{C}$ / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)
38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

Packaging 150 per 13" reel Plastic tape: 44 mm wide, 0.5 mm thick, 28 mm pocket spacing, 13.8 mm pocket depth

PCB washing Only pure water or alcohol recommended



Coilcraft[®]

Specifications subject to change without notice.
Please check our website for latest information.

Document 309 Revised 10/28/08

1102 Silver Lake Road Cary, Illinois 60013 Phone 847/639-6400 Fax 847/639-1469

E-mail info@coilcraft.com Web <http://www.coilcraft.com>